




PANDUIT PART NO	BUNDLE DIAM		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	LOOP TENSILE lbs (N)	CROSS SECTION	WEIGHT lbs(g)/100 pcs	TIP STYLE
	MIN in (mm)	MAX in (mm)										
S4-18	.06 (1.5)	.87 (22)	.044 (1.1)	.10 (2.5)	.19 (4.8)	.154 (3.9)	.181 (4.6)	3.94 (100)	18 (80)	MINIATURE	0.054 (24.3)	CURVED
S6-18	.06 (1.5)	1.57 (40)	.044 (1.1)	.10 (2.5)	.19 (4.8)	.154 (3.9)	.188 (4.8)	6.29 (160)	18 (80)	MINIATURE	0.100 (45.5)	CURVED
S8-18	.06 (1.5)	2.09 (53)	.045 (1.2)	.10 (2.5)	.19 (4.8)	.157 (4.0)	.19 (4.8)	7.87 (200)	18 (80)	MINIATURE	0.124 (56.2)	CURVED
S6-40	.08 (2.0)	1.30 (33)	.045 (1.2)	.14 (3.6)	.26 (6.6)	.19 (4.8)	.268 (6.8)	5.51 (140)	40 (178)	INTERMEDIATE	0.148 (67.4)	CURVED
S8-40	.08 (2.0)	2.09 (53)	.045 (1.2)	.14 (3.6)	.256 (6.5)	.19 (4.8)	.268 (6.8)	7.87 (200)	40 (178)	INTERMEDIATE	0.195 (88.7)	CURVED
S12-40	.08 (2.0)	2.99 (76)	.045 (1.2)	.14 (3.6)	.26 (6.6)	.181 (4.6)	.264 (6.7)	11.81 (300)	40 (178)	INTERMEDIATE	.299 (135.9)	CURVED
S15-40	.08 (2.0)	4.02 (102)	.051 (1.3)	.14 (3.6)	.232 (5.9)	.181 (4.6)	.248 (6.3)	14.57 (370)	40 (178)	INTERMEDIATE	.377 (171.1)	CURVED

NOTE:
SEE WWW.PANDUIT.COM FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE, PART MATERIAL,
PART COLOR AND ANY THIRD PARTY RECOGNITION OR COMPLIANCE.

						TITLE	
						STRONGHOLD MINIATURE AND INTERMEDIATE TIES	
						CUSTOMER DRAWING	
						ITEM REVISION NAME	
						00092FBI/00	
						DATASET FILE NAME	
						00092FBI_DC/00	
						UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]	
						.x ± .1 [2.54] .xxx ± .020 [.51]	
						.xx ± .02 [.5] ANGLES ± 5 °	
						THIRD ANGLE PROJECTION	
						MATERIAL:	
						NYLON 6.6	
						DRAWING NUMBER:	
						00092FBI_DC	
00	3-15-17	ACC	JSWA	JADE	DRAWING RELEASED	012502	
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[S12-40-M0](#)