


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



1. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
2. PRIMARY DIMENSIONS ARE IN MILLIMETERS.
3. RAIL ADJUSTMENTS MEASUREMENTS ARE TAKEN FROM THE FRONT FACE OF EACH EQUIPMENT RAIL. INDEPENDENT ADJUSTABLE REAR EQUIPMENT MOUNTING RAILS (E1A) ADJUST FROM 141mm [5.5in] TO 532mm [20.9in] AND FROM 583mm [22.9in] TO 1085mm [42.7in] WITH PDU BRACKETS AND CABLE MANAGEMENT FINGERS IN PLACE.
4. CAN BE USED WITH ANY 19" E1A STANDARD COMPONENT IN ADDITION TO ALL PANDUIT HORIZONTAL CABLE MANAGEMENT AND PATCH PANEL PRODUCTS.
5. E1A UNIVERSAL STANDARD HOLE PROGRESSION ON EQUIPMENT RAILS
15.88mm [.625in], 15.88mm [.625in], 12.70mm [.5in], 15.88mm [.625in], 15.88mm [.625in], 12.7mm [.5in]...ETC.
6. PARTS SUPPLIED:
-BASE CABINET
-FRONT PERFORATED SINGLE HINGE DOOR (SEE CHART ON SHEET 2)
-REAR PERFORATED SPLIT DOOR (SEE CHART ON SHEET 2)
-EQUIPMENT RAILS FRONT & REAR (SEE CHART ON SHEET 2)
-PDU BRACKETS (SEE CHART ON SHEET 2)
-CASTERS (SEE CHART ON SHEET 2)
-INSTRUCTION SHEET
7. RACK UNIT SPACING NUMERALS ARE CLEARLY PRINTED ON EQUIPMENT MOUNTING RAILS.
8. FULLY BONDED STRUCTURE WHEN ASSEMBLED PER INSTRUCTIONS.
9. STATIC LOAD RATING. 1360 Kg (3000 LBS)
10. ROLLING LOAD RATING. 1133 Kg (2500 LBS)
11. SINGLE POINT GROUND LOCATIONS AT TOP AND BOTTOM OF CABINET.
12. ALL CABINET RAILS ARE INSTALLED NUMBERS UP.
13. MAXIMUM EQUIPMENT DEPTH, 1111mm [43.75].

							TITLE NET-ACCESS S-TYPE CABINET 800mm WIDE X 1200mm DEEP FAMILY CONTROL DRAWING						
							ITEM REVISION NAME 12V305TM/02				PANDUIT		
							DATASET FILE NAME 12V305TM_DC/02A						
02A	11-14-14	PBS	ADP	TCN	FLOOR MOUNT DIMENSIONS UPDATED	V09000BX	THIRD ANGLE PROJECTION				MATERIAL: N/A		
00B	5-21-13	MDCA	JDW	JDWE	REVISED CHART	12V305TM-DC					DRAWING NUMBER: 12V305TM-DC		
00A	8-29-12	TWV	JDW	PBD	RELEASED TO PRODUCTION	12V305TM-DC							
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY TWV	DATE 8-29-12	CHK JDW	SCALE NONE	SHT 1 OF 5		SIZE A


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NO.	DESCRIPTION	SINGLE HINGE FRONT DOOR	SPLIT REAR DOOR	SPLIT SIDE PANEL	FRONT CAGE NUT E-RAIL	REAR CAGE NUT FINGER MGMT E-RAIL	REAR CAGE NUT VERTICAL PATCH E-RAIL	STANDARD PDU BRACKETS	CASTERS	CABLE MGMT FINGERS	VERTICAL PATCHING	CABINET WEIGHT FULLY UNPACKAGED	CABINET WEIGHT SHIPPING WEIGHT
S8222*	NET-ACCESS S-TYPE CABINET 800mm X 42RU X 1200mm DEEP	01	01	02	02	02	00	02	04	00	00	152 Kg/EACH 335 LBS/EACH	172 Kg/EACH 380 LBS/EACH
S8522*	NET-ACCESS S-TYPE CABINET 800mm X 45RU X 1200mm DEEP	01	01	02	02	02	00	02	04	00	00	165 Kg/EACH 365 LBS/EACH	186 Kg/EACH 410 LBS/EACH
S8822*	NET-ACCESS S-TYPE CABINET 800mm X 48RU X 1200mm DEEP	01	01	02	02	02	00	02	04	00	00	179 Kg/EACH 395 LBS/EACH	199 Kg/EACH 440 LBS/EACH
S8229*	NET-ACCESS S-TYPE CABINET 800mm X 42RU X 1200mm DEEP	01	01	00	02	02	00	02	04	00	00	112 Kg/EACH 248 LBS/EACH	133 Kg/EACH 293 LBS/EACH
S8529*	NET-ACCESS S-TYPE CABINET 800mm X 45RU X 1200mm DEEP	01	01	00	02	02	00	02	04	00	00	119 Kg/EACH 263 LBS/EACH	140 Kg/EACH 308 LBS/EACH
S8829*	NET-ACCESS S-TYPE CABINET 800mm X 48RU X 1200mm DEEP	01	01	00	02	02	00	02	04	00	00	126 Kg/EACH 278 LBS/EACH	146 Kg/EACH 323 LBS/EACH
S8222*F	NET-ACCESS S-TYPE CABINET 800mm X 42RU X 1200mm DEEP	01	01	02	02	02	00	02	04	01	00	153 Kg/EACH 337 LBS/EACH	173 Kg/EACH 382 LBS/EACH
S8522*F	NET-ACCESS S-TYPE CABINET 800mm X 45RU X 1200mm DEEP	01	01	02	02	02	00	02	04	01	00	166 Kg/EACH 367 LBS/EACH	187 Kg/EACH 412 LBS/EACH
S8822*F	NET-ACCESS S-TYPE CABINET 800mm X 48RU X 1200mm DEEP	01	01	02	02	02	00	02	04	01	00	180 Kg/EACH 397 LBS/EACH	200 Kg/EACH 442 LBS/EACH
S8229*F	NET-ACCESS S-TYPE CABINET 800mm X 42RU X 1200mm DEEP	01	01	00	02	02	00	02	04	01	00	113 Kg/EACH 250 LBS/EACH	134 Kg/EACH 295 LBS/EACH
S8529*F	NET-ACCESS S-TYPE CABINET 800mm X 45RU X 1200mm DEEP	01	01	00	02	02	00	02	04	01	00	120 Kg/EACH 265 LBS/EACH	141 Kg/EACH 310 LBS/EACH
S8829*F	NET-ACCESS S-TYPE CABINET 800mm X 48RU X 1200mm DEEP	01	01	00	02	02	00	02	04	01	00	127 Kg/EACH 280 LBS/EACH	147 Kg/EACH 325 LBS/EACH
S8222*S	NET-ACCESS S-TYPE CABINET 800mm X 42RU X 1200mm DEEP	00	00	02	02	02	00	02	04	00	00	127 Kg/EACH 280 LBS/EACH	147 Kg/EACH 325 LBS/EACH
S8522*S	NET-ACCESS S-TYPE CABINET 800mm X 45RU X 1200mm DEEP	00	00	02	02	02	00	02	04	00	00	141 Kg/EACH 310 LBS/EACH	161 Kg/EACH 355 LBS/EACH
S8822*S	NET-ACCESS S-TYPE CABINET 800mm X 48RU X 1200mm DEEP	00	00	02	02	02	00	02	04	00	00	154 Kg/EACH 340 LBS/EACH	175 Kg/EACH 385 LBS/EACH
S8229*S	NET-ACCESS S-TYPE CABINET 800mm X 42RU X 1200mm DEEP	00	00	00	02	02	00	02	04	00	00	87 Kg/EACH 193 LBS/EACH	108 Kg/EACH 238 LBS/EACH
S8529*S	NET-ACCESS S-TYPE CABINET 800mm X 45RU X 1200mm DEEP	00	00	00	02	02	00	02	04	00	00	94 Kg/EACH 208 LBS/EACH	115 Kg/EACH 253 LBS/EACH
S8829*S	NET-ACCESS S-TYPE CABINET 800mm X 48RU X 1200mm DEEP	00	00	00	02	02	00	02	04	00	00	101 Kg/EACH 223 LBS/EACH	121 Kg/EACH 268 LBS/EACH

* DENOTES COLOR

""B"" = BLACK

W = WHITE


							TITLE NET-ACCESS S-TYPE CABINET 800mm WIDE X 1200mm DEEP FAMILY CONTROL DRAWING					
							ITEM REVISION NAME 12V305TM/02					
							DATASET FILE NAME 12V305TM_DC/02A					
02A	11-14-14	PBS	ADP	TCN	SEE SHEET 1 OF 5 FOR REVISIONS	V09000BX	 THIRD ANGLE PROJECTION			MATERIAL: N/A		
00B	5-21-13	MDCA	JDW	JDWE	SEE SHEET 1 OF 5 FOR REVISIONS	12V305TM-DC				DRAWING NUMBER: 12V305TM-DC		
00A	8-29-12	TWV	JDW	PBD	SEE SHEET 1 OF 5 FOR REVISIONS	12V305TM-DC						
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY TWV	DATE 8-29-12	CHK JDW	SCALE NONE	SHT 2 OF 5	SIZE A

2


1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


B




LEFT VIEW



FRONT VIEW



RIGHT VIEW




REAR VIEW

B



A

02A	11-14-14	PBS	ADP	TCN	SEE SHEET 1 OF 5 FOR REVISIONS		V09000BX
00B	5-21-13	MDCA	JDW	JDWE	SEE SHEET 1 OF 5 FOR REVISIONS		12V305TM-DC
00A	8-29-12	TWV	JDW	PBD	SEE SHEET 1 OF 5 FOR REVISIONS		12V305TM-DC
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	

TITLE				NET-ACCESS S-TYPE CABINET 800mm WIDE X 1200mm DEEP FAMILY	
CONTROL DRAWING					
ITEM REVISION NAME			12V305TM/02		
DATASET FILE NAME			12V305TM_DC/02A		
			MATERIAL:		
			N/A		
			DRAWING NUMBER:		
			1 2V305TM-DC		
DRAWN BY	DATE	CHK	SCALE	SIZE	
TWV	8-29-12	JDW	NONE	SHT 3 OF 5	A


A


2

1


SI/700DA/16

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




							TITLE NET-ACCESS S-TYPE CABINET 800mm WIDE X 1200mm DEEP FAMILY CONTROL DRAWING					
							ITEM REVISION NAME 12V305TM/02					
							DATASET FILE NAME 12V305TM_DC/02A					
02A	11-14-14	PBS	ADP	TCN	SEE SHEET 1 OF 5 FOR REVISIONS	V09000BX	 THIRD ANGLE PROJECTION				MATERIAL: N/A	
00B	5-21-13	MDCA	JDW	JDWE	SEE SHEET 1 OF 5 FOR REVISIONS	12V305TM-DC					DRAWING NUMBER: 12V305TM-DC	
00A	8-29-12	TWV	JDW	PBD	SEE SHEET 1 OF 5 FOR REVISIONS	12V305TM-DC						
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY TWV	DATE 8-29-12	CHK JDW	SCALE NONE	SHT 4 OF 5	SIZE A

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



FLOOR MOUNTING HOLE LOCATIONS -
SOME PARTS REMOVED FOR CLARITY

							TITLE NET-ACCESS S-TYPE CABINET 800mm WIDE X 1200mm DEEP FAMILY CONTROL DRAWING					
							ITEM REVISION NAME 12V305TM/02					
							DATASET FILE NAME 12V305TM-DC/02A					
02A	11-14-14	PBS	ADP	TCN	SEE SHEET 1 OF 5 FOR REVISIONS	V09000BX	 THIRD ANGLE PROJECTION				MATERIAL: N/A	
00B	5-21-13	MDCA	JDW	JDWE	SEE SHEET 1 OF 5 FOR REVISIONS	12V305TM-DC					DRAWING NUMBER: 12V305TM-DC	
00A	8-29-12	TWV	JDW	PBD	SEE SHEET 1 OF 5 FOR REVISIONS	12V305TM-DC						
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY TWV	DATE 8-29-12	CHK JDW	SCALE NONE	SHT 5 OF 5	SIZE A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[S8222B](#)