


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.





PANDUIT PART NUMBER	MAXIMUM BUNDLE DIAMETER	PACKAGE QUANTITY	LENGTH = L ±.3 [7]
MLT2LH-LP	2.0" [51]	50	7.9" [201]
MLT4LH-LP	4.0" [102]	50	14.3" [362]
MLT6LH-LP	6.0" [152]	50	20.5" [521]
MLT8LH-LP	8.0" [203]	50	26.8" [679]



SECTION A - A
SCALE 8:1

NOTES:

1. APPLICATION TOOLS - GS4MT, PPTMT, ST2MT, ST3MT, AND HTMT
2. MINIMUM LOOP TENSILE STRENGTH - 250 LBS. (1112 NEWTONS)
WHEN TESTED ON A 1 1/2" MANDREL
3. BRACKETS [] DENOTE DIMENSIONS IN MILLIMETERS, AND ARE SHOWN FOR REFERENCE ONLY
4. TOLERANCES:
.XXX = ±.010 [.25] .XX = ±.02 [.5]
.X = ±.03 [.8] ANGLES = ±2°

							TITLE METAL LOCKING TIE LIGHT – HEAVY SERIES 304 STAINLESS CUSTOMER DRAWING					
							ITEM REVISION NAME N41126BS/05					
							DATASET FILE NAME N41126BS/05					
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .X ± .1 [2.54] .XXX ± .005 [.127] .XX ± .01 [.25] ANGLES ± 5 °  THIRD ANGLE PROJECTION					
5	09.30.15	BDK	SKB	RGRO	C. ADDED NEW TIP CONFIGURATION	N41126BS_DC				MATERIAL: 304 STAINLESS STEEL		
										DRAWING NUMBER: N41126BS_DC		
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY JAMB	DATE 6/03	CHK DPN	SCALE 2:1	SHT 1 OF 1	SIZE A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[MLT4H-LP](#) [MLT2.7H-LP](#) [MLT2H-LP](#) [MLT6H-LP](#) [MLT10H-LP](#) [MLT14H-Q](#) [MLT2H-TL](#) [MLT2LH-LP](#) [MLT4H-TL](#)
[MLT4LH-LP](#) [MLT6LH-LP](#) [MLT8H-LP](#) [MLT8LH-LP](#) [MLT12H-Q](#)