


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




PANDUIT P/N	MATERIAL	WEIGHT / PC
UCIB1-V316	316 STAINLESS STEEL	103.5 g [.228 lbs]
UCIB1-VC	COMMERCIAL STEEL / GALVANIZED	107.8 g [.238 lbs]



NOTES:

1. PRIMARY DIMENSIONS IN METRIC (mm). DIMENSIONS IN [] ARE ENGLISH (in).
2. THIS PRODUCT INTENDED FOR USE WITH I-BEAM STYLE LADDER RUNG IN GALVANIZED STEEL, STAINLESS STEEL, OR ALUMINUM CONSTRUCTIONS.
3. EACH ASSEMBLY INCLUDES:
 - (1) TALL BRACKET PIECE
 - (1) RETAINER CLIP
 - (1) M8 X 1.25 X 20mm CARRIAGE BOLT
 - (1) SERRATED-FLANGE HEX NUT



								TITLE				
								UNICLIP I-BEAM BRACKET UCIB1				
								CUSTOMER DRAWING				
								ITEM REVISION NAME		12L025AW/04	MATERIAL:	
								DATASET FILE NAME		12L025AW_DC/04B	SEE CHART	
								UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: mm (IN)				
								.x ± .3 [.01]	.xxx ± .127 [.005]			
								.xx ± .25 [.010]	ANGLES ± 5°			
										DRAWING NUMBER:		
										12L025AW-DC		
REV	DATE	BY	CHK	APR	DESCRIPTION			ECN	DRAWN BY	DATE	CHK	SCALE
									JBN	04-30-14	RMHI	N.T.S.
											SHT 1 OF 1	A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[UCIB1-V316](#)