


2

1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT P/N	MATERIAL	WEIGHT / PC
UCTH1-V316	316 STAINLESS STEEL	106.0 g [.234 lbs]
UCTH1-VC	COMMERCIAL STEEL / GALVANIZED	109.5 g [.241 lbs]

NOTES:

1. PRIMARY DIMENSIONS IN METRIC (mm).
DIMENSIONS IN [] ARE ENGLISH [in].
2. THIS PRODUCT INTENDED FOR USE WITH
TOP-HAT TYPE LADDER RACK IN GALVANIZED
STEEL, STAINLESS STEEL, OR ALUMINUM
CONSTRUCTIONS.
3. ADJUSTABLE TO 3 POSITIONS TO
ACCOMMODATE TOP-HAT WIDTHS AS FOLLOWS:
 - 38mm - 48mm [1.5" - 1.9"]
 - 48mm - 57mm [1.9" - 2.3"]
 - 57mm - 66mm [2.3" - 2.6"]
4. EACH ASSEMBLY INCLUDES:
 - (1) SHORT BRACKET PIECE
 - (1) RETAINER CLIP
 - (1) M8 X 1.25 X 20mm CARRIAGE BOLT
 - (1) SERRATED-FLANGE HEX NUT

							TITLE <div>UNICLIP TOP HAT BRACKET UCTH1</div> <div>CUSTOMER DRAWING</div>				<div><div></div></div>	
							ITEM REVISION NAME 12L025AU/03				<div><div>PANDUIT</div></div>	
							DATASET FILE NAME 12L025AU_DC/03B					
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: mm [IN] .x ± .3 [.01] .xxx ± .127 [.005] .xx ± .25 [.010] ANGLES ± 5 °				MATERIAL: SEE CHART	
-	-----	----	----	----	RELEASED TO PRODUCTION	-----	<div><div></div><div></div></div> THIRD ANGLE PROJECTION				DRAWING NUMBER: 12L025AU-DC	
1	06-12-14	RMHI	RMHI	RGRO	B. UPDATED WEIGHTS IN TABLE A. REVISED TITLE	12L025AU-DC						
R	04-30-14	JBN	RMHI		DRAWING RELEASED							
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY JBN	DATE 04-30-14	CHK RMHI	SCALE N.T.S.	SHT 1 OF 1	<div>A</div>

2

1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[UCTH1-V316](#)