

### Mini-Com® Water Resistant Faceplate

- Includes unique gaskets that prevent water from entering and damaging connections
- Meets the level of protection required for an IP56 enclosure
- Sloped design improves bend radius control
- Made of impact resistant material
- Optional icons available
- Two-piece hinged design
- Mounts to single gang opening
- Includes combo head screws to secure cover to base (tamper resistant screws also included)
- Accepts Mini-Com® Modules for STP and UTP, fiber optic, and audio/video, which snap in and out for easy moves, adds, and changes



Part Number	Part Description	Color‡	Std. Pkg. Qty.	Std. Ctn. Qty.
CFPWR4CIG	Single gang, vertical water resistant faceplate accepts four Mini-Com® Modules. Dimensions 5.8"H x 3.1"W x 1.5"D (147.32mm x 78.74mm x 38.10mm).	International Gray Base and Clear Cover	1	10

‡For other colors replace suffix CIG (International Gray base with Clear cover) with CL (Clear base and cover), IG (International Gray), IW (Off White), BL (Black), EI (Electric Ivory), or WH (White).

All faceplates supplied with mounting screws.

Fiber modules are not recommended for use in bottom two module spaces due to bend radius control requirements.

### Component Labels for Mini-Com® Water Resistant Faceplate



Suggested Label Solutions for TIA/EIA-606-A Compliance				
Faceplate Part Number	Laser/Ink Jet Desktop Printer Label	TDP43ME Thermal Transfer Desktop Printer Label	PanTher™ LS8E Hand-Held Printer Label	Cougar™ LS9 Hand-Held Printer Label
CFPWR4CIG	C125X030FJJ	C125X030YPT	C125X030FJC	T031X000FJC-BK

For complete labeling solutions and product information, reference charts on pages O.1 – O.22 of SA-NCCB51.

### Mini-Com® Ultimate ID® Stainless Steel Faceplates

- Ultimate ID® components are part of a complete system for identification designed to efficiently support TIA/EIA-606-A standard labeling requirements
- Accept Mini-Com® Modules for STP and UTP, fiber optic, and audio/video, which snap in and out for easy moves, adds, and changes
- Supplied with coordinated screw cover and clear station and port label covers, labels sold separately
- Impact-resistant 304 stainless steel suitable for light industrial environments



UICFP2S



UICFP4S



UICFP6S

Part Number	Part Description	Labels Required*	Std. Pkg. Qty.	Std. Ctn. Qty.
UICFP2S	Single gang, vertical faceplate holds up to two Mini-Com® Modules.	One 1-Port One 2-Port	1	10
UICFP4S	Single gang, vertical faceplate holds up to four Mini-Com® Modules.	One 1-Port Two 2-Port	1	10
UICFP6S	Single gang, vertical faceplate holds up to six Mini-Com® Modules. Requires minimum 1.9" wide in wall box or wallboard adapter for proper installation.	One 1-Port Two 3-Port	1	10

All faceplates supplied with mounting screws.

\*Ultimate ID® Labels can be found on pages O.11 and O.19 of SA-NCCB51.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[UICFP6S](#)