

IndustrialNet™ M12 X-Code Category 6A Overmolded Cordsets

PANDUIT®
SPECIFICATION SHEET

specifications

Industrial Ethernet cordsets shall be constructed of Category 6A, industrial grade, stranded, twisted pair cable for UTP and STP installations. Each cordset shall be pre-terminated and overmolded to include Category 6A M12 or RJ45 industrial plugs on each end which are wired according to the T568B and IEC 60603-7-41 standards.



technical information

| | |
|--|--|
| Category 6A/ Class E_A channel and component performance: | Exceeds channel and component requirements of ANSI/TIA-556-C.2 Category 6A and ISO11801 Class E _A standards at swept frequencies of 1 to 500 MHz |
| FCC and ANSI compliance: | Meets ANSI/TIA-1096-A; contacts plated with 50 micro-inches of gold for superior performance |
| IEC compliance: | <ul style="list-style-type: none">Interface conforms to IEC-61076-2-101ANSI/TIA 568-C.2: Category 6AISO 11801 Class E_A standards at swept frequencies up to 500 MHzANSI/TIA-1005-A: Telecommunications Infrastructure Standard for Industrial PremisesIEC 61076-2-109 Connectors for Electronic Equipment: Circular connectors – Detail specification for connectors with M 12 x 1 screw-locking, for data transmission frequencies up to 500 MHz |
| IP compliance: | Rated IP67/68 for dust protection and temporary liquid immersion. 10 million plus flex cycles |
| NEMA/UL compliance: | NEMA, 1, 3, 4, 6, 6P and IEC IP67/68, UL Type 12 |
| PoE compliance: | Meets IEEE 802.3af and IEEE 802.3at for PoE applications |
| RoHS compliance: | Compliant |
| Temperature rating: | -40° to +75°C (32° to +167°F) |
| Materials: | Constructed of 24 AWG UTP or STP stranded industrial grade and TPU and TPO cable and IP67/68 overmolded connectors; Coupling nut: nickel plated over copper-zinc alloy; Contact pins: gold plated over copper-zinc alloy |

key features and benefits

| | |
|------------------------------------|---|
| IP/NEMA/UL/CE rated | Withstands light wash down and temporary submerged conditions without loss of performance to ensure reliability in harsh factory environments |
| TPU and TPO jackets | Protect cable against weld splatter, chemicals and abrasions; suitable for high-flex applications for increased reliability |
| Factory terminated | Helps reduce termination errors in the field; assures reliability and saves time |
| Extended temperature range | Provides durable connection in extreme conditions to increase system reliability |
| Robust construction | Rated to 10 million flex cycles, providing durability and reliability |
| Optional RJ45 connector | Offers industry standard solution familiar to end users to speed deployment |

applications

IndustrialNet™ M12 X-Code Category 6A Overmolded Cordsets provide fast, reliable connections from machines and devices to switches and enclosures on the plant floor for Ethernet, PROFINET, Modbus and EtherCAT. The cordsets are rated to IP67/68, NEMA 1,3,4,6,6P, UL and M.I.C.E., ensuring high

performance and longevity under harsh environmental conditions. In mated conditions, these cordsets can withstand high temperature and high vibration commonly found in harsh industrial applications such as automotive, food and beverage, oil and gas, transportation and mining.

IndustrialNet™ M12 X-Code Category 6A Overmolded Cordsets

**M12 bulkhead female X-code,
STP, black:** ICX45T1NBL0.5M

**M12 bulkhead female X-code, RJ45
plug, STP, black:** *ICX44T1NBL1M

**M12 male X-code, straight connector,
STP, teal:** *ICX15T1NTL1M

**M12 male to male X-Code,
straight connector,
STP, teal:** *ICX11T1NTL1M

Accessories

**IndustrialNet™ Category 6A
M12 X-Code field
terminable plug:** ISPS6A88MFA

**IndustrialNet™ M12 X-Code
female to 90° RJ45 jack panel
mount adapter:** ICAM12X90DRJS

**IndustrialNet™ M12 X-Code
female to RJ45 jack panel
mount adapter:** ICAM12XRJS

IndustrialNet™ Copper Cable

**Category 6A S/FTP, 24/7 AWG stranded,
PUR 4-pair:** ISX6X04**-LED

**Category 6 S/FTP, 22/1 AWG stranded,
LSZH 4-pair:** PSM6004**-LED

**Category 7 S/FTP, 22/1 AWG stranded,
LSZH 4-pair:** PSMD7004BL-LED

**Category 6A SF/UTP, 24/7 AWG
stranded, CM 4-pair:** ISFCH6X04A**-UG

**Category 6A SF/UTP, 26/7 AWG
stranded, CM 4-pair:** ISFCH6X04B**-UG

**Category 6 U/UTP, 24/7 AWG stranded,
CM 4-pair, black:** IUC6C04ABL-CEG

**Category 6 F/UTP, 26/7 AWG stranded,
CM 4-pair, black:** IFC6C04BBL-CEG

**Category 6 S/FTP, 24/7 AWG stranded,
PUR 4-pair:** ISX6004A**-LED

**Category 6 U/UTP, 23/1 AWG stranded,
CMR 4-pair:** IURH6004**-UG


**Category 6 F/UTP, 23/1 AWG stranded,
CMR 4-pair:** IFRH6C04**-UG

*For other lengths, change the length designation (1M) of the part number to the desired standard length (2M, 3M, 5M, 10M, 15M or 20M).


** To designate color, add suffix TL (Teal), BL (Black), RD (Red), BU (Blue), GY (Gray), YL (Yellow), OR (Orange), or IG (International Gray). Contact Customer Service for complete list of colors.

IndustrialNet™ M12 X-Code Category 6A Overmolded Cordsets


ICX45T1NBL0.5M




ICX44T1NBL



ICX15T1NTL



ICX11T1NTL



WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT US/CANADA
Phone: 800.777.3300

PANDUIT EUROPE LTD.
London, UK
cs-emea@panduit.com
Phone: 44.20.8601.7200

PANDUIT SINGAPORE PTE. LTD.
Republic of Singapore
cs-ap@panduit.com
Phone: 65.6305.7575

PANDUIT JAPAN
Tokyo, Japan
cs-japan@panduit.com
Phone: 81.3.6863.6000

PANDUIT LATIN AMERICA
Guadalajara, Mexico
cs-la@panduit.com
Phone: 52.33.3777.6000

PANDUIT AUSTRALIA PTY. LTD.
Victoria, Australia
cs-aus@panduit.com
Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

For more information

Visit us at www.panduit.com

Contact Customer Service by email: cs@panduit.com
or by phone: 800.777.3300

PANDUIT®

©2018 Panduit Corp.
ALL RIGHTS RESERVED.
COSP426--WW-ENG
2/2018

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[ICX15T1NTL20M](#)