



Technical drawing of a roof section showing a cross-section of a roof with a corrugated metal deck and insulation. The drawing includes dimensions for the roof thickness, insulation thickness, and the width of the roof structure. The roof thickness is 23.93 [607.8], the insulation thickness is 7.18 [182.4], and the width of the roof structure is 8.63 [219.2]. The drawing also shows a detail of the roof edge with a width of 8.50 [215.9] and a height of 5.50 [139.7].


PANDUIT PART NO.	WEIGHT
GPKT724Y	9.95 LB/ea 4522.73g/ea



- NOTES:
1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE PACKAGE QUANTITY.
 2. 288 PAIR CATEGORY 6 TOWER ASSEMBLY IS DESIGNED FOR WALL MOUNT APPLICATIONS, PROVIDES VERTICAL CABLE MANAGEMENT, AND SUPPLIED JUMPER TROUGHS PROVIDE VERTICAL CABLE MANAGEMENT.
 3. ASSEMBLY COMES WITH FASTENER KIT WHICH INCLUDES THE FOLLOWING:
(2) #12 X 1/2" SHEET METAL SCREWS
(2) #12 LOCK WASHERS, (1) 1/4-20 X 3/4 MACHINE SCREW, (1) 1/4-20 HEX NUT, (2) 1/4" LOCK WASHERS.
 4. ALSO INCLUDED WITH TOWER IS A SCREW KIT USED TO MOUNT THE JUMPER TROUGHS AND BASES.
 5. 6 LABEL HOLDERS AND 6 LABELS ARE ALSO PROVIDED.
 6. SEE CHART FOR NUMBER OF CONNECTING BLOCKS INCLUDED FOR EACH PART NUMBER.
 7. DIMENSIONS IN PARENTHESES ARE IN METRIC.

MODEL FILENAME		SIZE	
DRAWING FILENAME		A	
M01537PK_DC44_00A.PRT			
GP6 PLUS STANDARD DENSITY 288 PAIR TOWER KIT CUSTOMER DRAWING			
 		1.1. NUMBER	
TINLEY PARK, ILL 60477		PRODUCT SPEC/ PKG SPEC	
		ASSY METHOD/ TEST METHOD	
ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ±.03 (.XXX) ±.005 (.XX) ±.01 ANGLES ± 1°		SCALE	
DRAWN BY		PART NO.	
MDJr		GPKT724Y	
DATE		DRAWING NO.	
3-08-07		01537-44	
CHK'D		SHT. 1 OF 2	
REVIEW DRAWING NUMBERS			
SEE NOTES			
MAT'L			


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



SIDE VIEW

BACK VIEW

MODEL FILENAME	SIZE
DRAWING FILENAME	A
M01537PK_DC44_00A.PRT	
GP6 PLUS STANDARD DENSITY 288 PAIR TOWER KIT CUSTOMER DRAWING	

 PANDUIT ™ CORP. TINLEY PARK, ILL 60477	I.I. NUMBER
	PRODUCT SPEC/ PKG SPEC
	ASSY METHOD/ TEST METHOD
	SCALE
 THIRD ANGLE PROJECTION	NONE
	PART NO.
	GPKT724Y
	DRAWING NO.
ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) ±.03 (.XXX) ±.005 (.XX) ±.01 ANGLES ± 1°	SEE NOTES
	MAT'L
	01537-44 SHT. 2 OF 2

DRAWN BY
MDJr

DATE
3-08-07

CHK'D

REVIEW DRAWING NUMBERS

SEE NOTES

REV

DATE

BY

CHK

DESCRIPTION

ECN - R

CUST

SUP

OTH

SEE SHEET 1 FOR REV. CHANGES.

01537-44

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[GPKT724Y](#)