


PANDUIT PART NO.	MAX.BUNDLE DIA.	PACKAGE QTY.	LENGTH +/- .3" [7]
⑧ MLT2EH-LP316	2" [51]	50	11.8" [300]
MLT4EH-LP316	4" [102]	50	17.1" [434]
MLT6EH-LP316	6" [152]	50	23.4" [594]
MLT8EH-LP316	8" [203]	50	29.7" [754]



NOTES:

1. APPLICATION TOOLS - ST3MT & RT2HT
2. MINIMUM LOOP TENSILE STRENGTH - 600 LBS. (2670 NEWTONS) WHEN TESTED ON A 3" MANDREL.
3. BRACKETS [] DENOTES DIMENSION IN MILLIMETERS
4. TOLERANCES:
 .XXX = $\pm .010$ [.25]
 .XX = $\pm .02$ [.5]
 .X = $\pm .03$ [.8]
 ANGLES = $\pm 2^\circ$
5. MATERIAL: 316 STAINLESS STEEL

① FULLY ROUNDED
EDGES ALONG STRAP BODY

SECTION A - A
SCALE: 4x

N41156BS_DC/02A

02A	10/08	JAMB	SKB	ORIG CAD FILE SPEC WAS S41156_02 NOTE 1: APPLICATION TOOL RTIHT REPLACED BY RT2HT				PANDUIT CORP. TINLEY PARK, ILLINOIS				
02	9/05	JAMB	EJD	Ⓑ ADDED PART NO. MLT2EH-LP316 TO TABLE		SS00061	---					---
01	8/04	JAMB	DPN	Ⓐ REMOVED "AISI NO.1 FULL RADIUSED" & REPLACED WITH "FULLY ROUNDED"		11907	CCH	JJB	METAL LOCKING TIE EXTRA HEAVY DUTY 316 STAINLESS STEEL - CUSTOMER DRAWING			
00	1/04	JAMB	DPN	RELEASED		11307	CCH	JJB				
REV	DATE	BY	CHK	DESCRIPTION		ECN #	PM	CUST	DRAWN BY JAMB	CHK'D DPN	SCALE 2x	DRAWING NO. N41156BS_DC

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[MLT2EH-LP316](#) [MLT8EH-LP316](#) [MLT6EH-LP316](#) [MLT4EH-LP316](#)