

PANDUIT PART NO.*	MAT'L SUFFIX	RECOMMENDED FASTENER	'A'	'B'	'C'	'D'	'E'	'F'	'G' (REF)	'H' (REF)	'I' (REF)	USE WITH THESE CABLE TIE CROSS SECTIONS	WEIGHT (g) lbs/100 pcs.
TM1S4	NONE -0 -30 -69	#4 (M2.5) SCREW	0.513 [13.0]	0.316 [8.0]	0.230 [5.8]	0.130 ±.020 (3.3) ±(.5)	0.067 ±.020 (1.7) ±(.5)	0.125 [3.2]	0.075 [1.9]	0.226	0.121	MINIATURE ONLY	0.064 (29.0)
TM1S6	NONE -0 -30 -69	#6 (M3) SCREW							0.080 [2.0]	0.277	0.146		0.057 (26.0)

Technical drawing of a mechanical part showing a front view and a cross-section A-A.

Front View:

- Dimension A is the total width.
- Dimension A' is the width of the central circular feature.
- Dimension B is the height of the part.
- A callout points to the central feature with the text "SEE NOTE 2".

Cross-section A-A:

- Dimension G is the total height.
- Dimension H is the height of the central cavity.
- Dimension F is the height of the base.
- Dimension C is the height of the top flange.
- Dimension I is the width of the base.

- *1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.
2. HOLE DIMENSIONS SHOULD ACCOMMODATE SPECIFIED RECOMMENDED FASTENER.

G00239CN_PB_TMS_A_08

TINLEY PARK, ILLINOIS

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± 0.05 (1.3) (.XXX) ± 0.010 (0.25)
(.XX) ± 0.02 (0.5) ANGLES $\pm 5^\circ$

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES. THIRD ANGLE PROJECTION.

SCALE	NONE
-------	------

SEE TABLE

GB0239CN

DWG
A
SIZE

8	6-8-05	TMSA		CHANGED RECOMMENDED FASTENER FROM M3.0 TO M2.5	GB0239CN	8				
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[TM1S6-M](#) [TM1S4-M30](#) [TM1S6-M0](#)