







PANDUIT PART NUMBER	TYPE	FOR USE WITH
FLCDS900BUY	SINGLEMODE	9/125 $\mu$ m FIBER
FLCDM900BLY	MULTIMODE	50/125 $\mu$ m FIBER
FLCDM900E1Y	MULTIMODE	62.5/125 $\mu$ m FIBER

## NOTES:

1. SEE CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITY.
2. ACCEPTS 9/125 $\mu$ m SINGLEMODE, 50/125 $\mu$ m MULTIMODE OR 62.5/125 $\mu$ m MULTIMODE, 900 $\mu$ m BUFFERED GLASS OPTICAL FIBER.
3. FULLY COMPLIES WITH THE FIBER OPTIC CONNECTOR PERFORMANCE REQUIREMENTS AS SPECIFIED BY TIA/EIA-568-B.3.
4. MATERIAL:  
BODY/HARDWARE: PLASTIC  
BOOT: THERMOPLASTIC RUBBER  
FERRULE: ZIRCONIA CERAMIC
5. DIMENSIONS IN BRACKETS ARE METRIC [mm].
6. WEIGHT PER 10 PIECES: .069 lb [31.3g]



											FIBER OPTIC SINGLEMODE/MULTIMODE DUPLEX LC CONNECTOR WITH 900um BOOT CUSTOMER DRAWING				
												 PANDUIT <sup>TM</sup> CORP. TINLEY PARK, ILL 60477			
											 THIRD ANGLE PROJECTION	ALL DIMENSIONS ARE GIVEN IN INCHES UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) (.XXX) ± .010 (0.3) (.XX) ± .03 (0.8) ANGLES		DRAWING FILENAME M01371AA_DC-Y_900/08A	
												SCALE NONE			
											DRAWN BY MC	REVIEW DRAWING NUMBERS		PART NO. FLCDS900BUY FLCDM900BLY/FLCDM900E1Y	
2	09-01-11	MC	MTV	RELEASED TO PRODUCTION	01371-46	MTV	RWB				DATE 03-07-07			DRAWING NO. 01371-46	SIZE A
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH	CHK'D PJI					

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[FLCDS900BUY](#) [FLCDM900BLY](#)