# **ESD Protection Diode**

# SC-74 Quad Monolithic Common Anode

This quad monolithic silicon voltage suppressor is designed for applications requiring transient overvoltage protection capability. It is intended for use in voltage and ESD sensitive equipment such as computers, printers, business machines, communication systems, medical equipment, and other applications. Its quad junction common anode design protects four separate lines using only one package. These devices are ideal for situations where board space is at a premium.

#### Features

- SC-74 Package Allows Four Separate Unidirectional Configurations
- Peak Power Min. 24 W @ 1.0 ms (Unidirectional), per Figure 5 Waveform
- Peak Power Min. 150 W @ 20 µs (Unidirectional), per Figure 6 Waveform
- Maximum Clamping Voltage @ Peak Pulse Current
- Low Leakage < 2.0 μA
- ESD Rating of Class 3B (exceeding 16 kV) per the Human Body Model
- SZ Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC–Q101 Qualified and PPAP Capable
- These Devices are Pb-Free and are RoHS Compliant\*



### **ON Semiconductor®**


www.onsemi.com

# SC-74 QUAD SURGE PROTECTION 24 WATTS PEAK POWER 5.6 – 33 VOLTS




SC-74 CASE 318F STYLE 1

#### **PIN ASSIGNMENT**



#### MARKING DIAGRAM



(Note: Microdot may be in either location)

#### DEVICE MARKING & ORDERING INFORMATION

See specific marking and ordering information in the device marking and ordering information table on page 6 of this data sheet.

\*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

Semiconductor Components Industries, LLC, 2015
October, 2017 – Rev. 12

#### THERMAL CHARACTERISTICS (T<sub>A</sub> = 25°C Unless Otherwise Noted)

Characteristic	Symbol	Value	Unit
Peak Power Dissipation @ 1.0 ms (Note 1) @ $T_A \le 25^{\circ}C$	P <sub>pk</sub>	24	W
Peak Power Dissipation @ 20 $\mu s$ (Note 2) @ $T_A \leq 25^\circ C$	P <sub>pk</sub>	150	W
Total Power Dissipation on FR-5 Board (Note 3) @ $T_A = 25^{\circ}C$	PD	225 1.8	MW mW/°C
Thermal Resistance from Junction-to-Ambient	$R_{ hetaJA}$	556	°C/W
Total Power Dissipation on Alumina Substrate (Note 4) @ T <sub>A</sub> = 25°C Derate above 25°C	PD	300 2.4	MW mW/°C
Thermal Resistance from Junction-to-Ambient	R <sub>θJA</sub>	417	°C/W
Junction and Storage Temperature Range	T <sub>J</sub> , T <sub>stg</sub>	-55 to +150	°C
Lead Solder Temperature – Maximum (10 Second Duration)	TL	260	°C

1. Non-repetitive current pulse per Figure 5 and derate above  $T_A = 25^{\circ}C$  per Figure 4. 2. Non-repetitive current pulse per Figure 6 and derate above  $T_A = 25^{\circ}C$  per Figure 4.

3. FR-5 = 1.0 x 0.75 x 0.62 in.

4. Alumina = 0.4 x 0.3 x 0.024 in., 99.5% alumina

#### **ELECTRICAL CHARACTERISTICS** ( $T_A = 25^{\circ}C$ Unless Otherwise Noted) UNIDIRECTIONAL

(Circuit tied to pins 1, 2, and 5; Pins 2, 3, and 5; Pins 2, 4, and 5; or Pins 2, 5, and 6) (V<sub>F</sub> = 0.9 V Max @ I<sub>F</sub> = 10 mA)

	E	Breakdowr	n Volta	ge	Ma Reve Leak Curr	erse age		Max	Max Reverse Voltage @ I <sub>RSM</sub>	Maximum	Capacitance @ 0 Volt Bias, 1 MHz	
		VzT (Note 6) (V)		@ I <sub>ZT</sub>	I <sub>R</sub>	VR	Max Zener Impedance (Note 7) Reverse Surge Current	(Note 8) (Clamping Voltage)	Temperature Coefficient of V <sub>Z</sub>	(pF)		
Device (Note 5)	Min	Nom	Max	(mA)	(nA)	(V)	Zzτ @ Izτ (Ω) (mA)	IRSM (A)	VRSM (V)	(mV/°C)	Min	Max
MMQA5V6T1G	5.32	5.6	5.88	1.0	2000	3.0	400	3.0	8.0	1.26	-	-
MMQA6V2T1G/T3G	5.89	6.2	6.51	1.0	700	4.0	300	2.66	9.0	10.6	-	-
MMQA6V8T1G	6.46	6.8	7.14	1.0	500	4.3	300	2.45	9.8	10.9	100	250
MMQA12VT1G	11.4	12	12.6	1.0	75	9.1	80	1.39	17.3	14	-	-
MMQA13VT1G	12.4	13	13.7	1.0	75	9.8	80	1.29	18.6	15	-	-
MMQA15VT1G	14.3	15	15.8	1.0	75	11	80	1.1	21.7	16	-	-
MMQA18VT1G	17.1	18	18.9	1.0	75	14	80	0.923	26	19	-	-
MMQA20VT1G/T3G	19	20	21	1.0	75	15	80	0.84	28.6	20.1	-	-
MMQA22VT1G	20.9	22	23.1	1.0	75	17	80	0.758	31.7	22	-	-
MMQA24VT1G	22.8	24	25.2	1.0	75	18	100	0.694	34.6	25	-	_
MMQA27VT1G	25.7	27	28.4	1.0	75	21	125	0.615	39	28	-	-
MMQA33VT1G	31.4	33	34.7	1.0	75	25	200	0.504	48.6	37	-	-

5. Includes SZ-prefix devices where applicable.

6. V<sub>Z</sub> measured at pulse test current I<sub>T</sub> at an ambient temperature of 25°C.

7. Z<sub>ZT</sub> is measured by dividing the AC voltage drop across the device by the AC current supplied. The specified limits are I<sub>Z(AC)</sub> = 0.1 I<sub>Z(DC)</sub>, with AC frequency = 1 kHz.

8. Surge current waveform per Figure 5 and derate per Figure 4.

### **TYPICAL CHARACTERISTICS**





Figure 3. Steady State Power Derating Curve

Figure 4. Pulse Derating Curve

### **TYPICAL CHARACTERISTICS**



Surge Power,  $P_{pk}$  versus  $V_Z$ 

Power, P<sub>pk</sub> versus PW

Power is defined as  $V_{RSM} \times I_Z(pk)$  where  $V_{RSM}$  is the clamping voltage at  $I_Z(pk)$ .

#### TYPICAL COMMON ANODE APPLICATIONS

A quad junction common anode design in a SC-74 package protects four separate lines using only one package. This adds flexibility and creativity to PCB design especially

when board space is at a premium. A simplified example of MMQA/SZMMQA Series Device applications is illustrated below.





Figure 9. Computer Interface Protection



MMQA/SZMMQA SE-RIES DEVICE



#### DEVICE MARKING AND ORDERING INFORMATION

Device*	Device Marking	Package	Shipping
MMQA5V6T1G	5A6		3,000/Tape & Reel
MMQA6V2T1G	6A2	SC-74 (Pb-Free)	3,000/Tape & Reel
MMQA6V2T3G	6A2		10,000/Tape & Reel
MMQA6V8T1G	6A8		3,000/Tape & Reel
MMQA12VT1G	12A		3,000/Tape & Reel
MMQA13VT1G	13A		3,000/Tape & Reel
MMQA15VT1G	15A		3,000/Tape & Reel
MMQA18VT1G	18A		3,000/Tape & Reel
MMQA20VT1G	20A		3,000/Tape & Reel
MMQA20VT3G	20A		10,000/Tape & Reel
MMQA22VT1G	22A		3,000/Tape & Reel
MMQA24VT1G	24A		3,000/Tape & Reel
MMQA27VT1G	27A		3,000/Tape & Reel
MMQA27VT3G	27A		10,000/Tape & Reel
MMQA33VT1G	33A		3,000/Tape & Reel

+For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specification Brochure, BRD8011/D.

\*IncludeS SZ-prefix devices where applicable.

#### **Mechanical Characteristics:**

CASE: Void-free, Transfer-molded, Thermosetting Plastic Case.

**FINISH:** Corrosion resistant finish, easily solderable.

Package designed for optimal automated board assembly.


Small package size for high density applications.

Available in 8 mm Tape and Reel.

Use the Device Number to order the 7 inch/3,000 unit reel.

Replace the "T1" with "T3" in the Device Number to order the 13 inch/10,000 unit reel.

# onsemi



onsemi, ONSEMI, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent\_Marking.pdf</u>. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or indental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification. Buyer shall indemnify and hold onsemi and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs,

#### ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation onsemi Website: www.onsemi.com

ONLINE SUPPORT: <u>www.onsemi.com/support</u> For additional information, please contact your local Sales Representative at <u>www.onsemi.com/support/sales</u>

# **Mouser Electronics**

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

onsemi:

MMQA12VT1MMQA12VT1GMMQA13VT1GMMQA15VT1GMMQA18VT1MMQA18VT1GMMQA20VT3MMQA22VT1GMMQA24VT1GMMQA27VT1MMQA27VT1GMMQA33VT1GMMQA5V6T1GMMQA6V2T1MMQA6V2T1GMMQA6V2T3GMMQA6V2T3GMMQA6V2T1GMMQA20VT3GMMQA5V6T3GSZMMQA6V2T1GSZMMQA27VT1GSZMMQA33VT1GSZMMQA5V6T1GSZMMQA6V8T1GSZMMQA15VT1G