


- NOTES:
1. PARTS ARE (c UL us) LISTED.
 2. FOR COPPER WIRE ONLY
 3. PANDUIT PART NUMBERS WITH A "T" ARE TIN PLATED
 4. PKG QTY: Q = 25
L = 50
C = 100
D = 500
 5. SEE LABEL FOR SCREW TURQUE VALUES

PANDUIT PART NUMBER	CONDUCTOR RANGE	APPROXIMATE DIMENSIONS					INSTALLATION TOOL
		BOLT SIZE	W	H	T	L	
ML8-CY	14 SOL. - 8 STR.	3/16	0.38	0.42	0.08	0.81	SLOT SCREWDRIVER
ML8T-CY	14 SOL. - 8 STR.	3/16	0.38	0.42	0.08	0.81	
ML4-CY	14 SOL. - 4 STR.	1/4	0.54	0.55	0.09	1.11	
ML4T-CY	14 SOL. - 4 STR.	1/4	0.54	0.55	0.09	1.11	
ML1/0-LY	14 SOL. - 1/0 STR.	5/16	0.73	0.79	0.09	1.57	1/4" HEX WRENCH
ML1/0T-LY	14 SOL. - 1/0 STR.	5/16	0.73	0.79	0.09	1.57	
ML250-QY	6 STR. - 250kcmil	3/8	0.94	1.06	0.12	1.94	
ML250T-QY	6 STR. - 250kcmil	3/8	0.94	1.06	0.12	1.94	

05	11/11	JHNU	RGB	REVISED ML1/0, ML1/0T WIRE RANGE: 14-1/0 WAS 8-1/0	N41569BB-C41569	RGB	RGB	<div> PANDUIT CORP. TINLEY PARK, ILLINOIS</div>							
04	04/09	JESH	JESH	UPDATED NOTE WIRE RANGE 8 SOL - 1/0 STR WAS 14 SOL - 1/0 STR											
03	03/09	JESH	JESH	UPDATED NOTE 1 PARTS ARE (c UL us) LISTED. WAS UL LISTED & CSA CERTIFIED											
				ADD NOTE 5. SEE LABEL FOR SCREW TORQUE VAULES				<div>ML SERIES COPPER MECHANICAL LUGS CUSTOMER DRAWING</div>							
02	03/09	JESH	JESH	UPDATED STAMP INFORMATION, AND APPROXIMATE DIMENSIONS											
----	-----	----	----	REMOVED ML500-3Y FROM DRAWING REMOVED RoHS NOTE; REMOVED MADE IN U.S.A. NOTE CONVERTED DRAWING TO SOLIDWORKS				UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCES ARE: (.X) ± --- (.XXX) ± --- (.XX) ± --- ANGLES ± ---		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION					
01	8/07	JHNU	JHNU					DRAWN BY JHNU	MAT'L: COPPER		SCALE NONE				
00	7/06	JHNU	LEM	DRAWING RELEASED - RoHS COMPLIANT	PC00487			DATE			DRAWING NO / CAD FILE		DWG B SIZE		
REV	DATE	BY	CHK	DESCRIPTION	ECN	-R	SUP	CHK'D			C41569_05				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[ML4-CY](#) [ML250T-QY](#) [ML1/0-LY](#) [ML1/0T-LY](#) [ML4T-CY](#)