

I/O extension module - NLC-IO-06I-04QTP-01A - 2701072

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



I/O extension module for use with Nanoline base unit. Equipped with 6 digital input and 4 PNP digital output channels. A maximum of three I/O extension modules can be attached to a base unit.

Your advantages

- ✓ Automatically recognized by the firmware
- ✓ I/O modules are electrically isolated
- ✓ Up to 3 modules can be added to the right side of a base unit
- ✓ Can be powered from a secondary power supply

RoHS

Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 325332
GTIN	4046356325332

Technical data

Dimensions

Width	40 mm
Height	103.5 mm
Depth	43 mm

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-25 °C ... 60 °C
Ambient temperature (storage/transport)	-25 °C ... 85 °C

Supply

Connection method	Screw connection
Supply voltage	24 V DC
Supply current	typ. 50 mA

I/O extension module - NLC-IO-06I-04QTP-01A - 2701072

Technical data

Supply

	max. 90 mA
--	------------

Digital inputs

Input name	Digital inputs
Description of the input	PNP/NPN
Connection method	Screw connection
Number of inputs	6
Typical response time	60 µs (on)
	70 µs (OFF)
Input voltage range "0" signal	0 V DC ... 5 V DC
Input voltage range "1" signal	15 V DC ... 30 V DC
Nominal input current at U _{IN}	5 mA DC (On)

Digital outputs

Output name	Digital outputs
Output description	PNP outputs
Connection method	Screw connection
Number of outputs	4
Type of protection	Short-circuit and overload protection
Maximum output current per channel	500 mA
Maximum output current per module / terminal block	2 A
Maximum output current per module	2 A
Nominal load, inductive	12 VA ((1.2H))
Nominal load, lamp	12 W
Nominal load, ohmic	12 W

General

Mounting type	DIN rail mounting
---------------	-------------------


Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"


Drawings

I/O extension module - NLC-IO-06I-04QTP-01A - 2701072

Dimensional drawing



Connection diagram



Approvals

Approvals

Approvals

UL Listed / EAC

Ex Approvals

Approval details

UL Listed



<http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm>

FILE E 238705

EAC



EAC-Zulassung

Phoenix Contact 2018 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

2701072