

## Feed-through header - GMVSTBW 2,5/ 6-ST-7,62 BK AU - 1710025

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)


PCB headers, nominal current: 12 A, rated voltage (III/2): 630 V, number of positions: 6, pitch: 7.62 mm, color: black, contact surface: Gold, mounting: Soldering




The figure shows a 10-position version of the product

### Your advantages

- ✓ Maximum flexibility when it comes to device design – one header for connectors with different connection technologies
- ✓ Items that can be aligned in various pitches support flexible and space-saving PCB assembly
- ✓ Well-known mounting principle allows worldwide use
- ✓ Larger pitch for increased voltage requirements
- ✓ Plug-in direction parallel to the PCB



### Key Commercial Data

Packing unit	50 pc
GTIN	 4 055626 139609
GTIN	4055626139609

### Technical data

#### Dimensions

Pitch	7.62 mm
Length of the solder pin	3.5 mm
Pin dimensions	1 x 1 mm

#### General

Range of articles	GMVSTBW 2,5/...-ST
Insulating material group	I
Rated voltage (III/2)	630 V
Nominal current $I_N$	12 A
Flammability rating according to UL 94	V0
Color	black

## Feed-through header - GMVSTBW 2,5/ 6-ST-7,62 BK AU - 1710025

### Technical data

#### General

Number of positions	6
---------------------	---

#### Standards and Regulations

Flammability rating according to UL 94	V0
----------------------------------------	----

#### Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

### Approvals


#### Approvals

#### Approvals

#### EAC

#### Ex Approvals

#### Approval details

EAC		B.01742
-----	-------------------------------------------------------------------------------------	---------

Phoenix Contact 2018 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

1710025