

# ESDM1031

## 3.3V ESD Protection Diodes

### Micro-packaged Diodes for ESD Protection

The ESDM1031 is designed to protect voltage sensitive components from ESD. Excellent clamping capability, low leakage, and fast response time provide best in class protection on designs that are exposed to ESD. Because of its small size, it is suited for use in smartphone, smart-watch, or many other portable / wearable applications where board space comes at a premium.

#### Features

- Low Capacitance (30 pF Typ, I/O to GND)
- Small Body Outline Dimensions – 01005 Size: 0.445 x 0.24 mm
- Protection for the Following IEC Standards:  
IEC 61000-4-2 (Level 4)
- Low ESD Clamping Voltage
- These Devices are Pb-Free, Halogen Free/BFR Free and are RoHS Compliant

#### Applications

- Audio Line Protection
- SIM Card Protection
- GPIO Protection

#### MAXIMUM RATINGS ( $T_J = 25^\circ\text{C}$ unless otherwise noted)

| Rating  | Symbol           | Value                | Unit             |
|---|------------------|----------------------|------------------|
| Operating Junction Temperature Range                    | $T_J$            | -55 to +150          | $^\circ\text{C}$ |
| Storage Temperature Range                               | $T_{\text{stg}}$ | -55 to +150          | $^\circ\text{C}$ |
| Lead Solder Temperature – Maximum (10 Seconds)          | $T_L$            | 260                  | $^\circ\text{C}$ |
| ESDM1031:<br>IEC 61000-4-2 Contact<br>IEC 61000-4-2 Air | ESD              | $\pm 30$<br>$\pm 30$ | kV<br>kV         |

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

See Application Note AND8308/D for further description of survivability specs.



**ON Semiconductor®**

[www.onsemi.com](http://www.onsemi.com)



X4DFN2 (01005)  
CASE 718AA

#### MARKING DIAGRAM



K = Device Code  
M = Date Code

#### PIN CONFIGURATION AND SCHEMATIC



#### ORDERING INFORMATION

See detailed ordering and shipping information on page 2 of this data sheet.

# ESDM1031

## ELECTRICAL CHARACTERISTICS ( $T_A = 25^\circ\text{C}$ unless otherwise specified)

| Parameter                        | Symbol    | Conditions  | Min | Typ   | Max | Unit          |
|----------------------------------|-----------|---|-----|-------|-----|---------------|
| Reverse Working Voltage          | $V_{RWM}$ | I/O Pin to GND  |     |       | 3.3 | V             |
| Breakdown Voltage                | $V_{BR}$  | $I_T = 1\text{ mA}$ , I/O Pin to GND  | 4.6 | 5.2   | 6.3 | V             |
| Reverse Leakage Current          | $I_R$     | $V_{RWM} = 3.3\text{ V}$ , I/O Pin to GND   |     | 0.005 | 0.5 | $\mu\text{A}$ |
| Reverse Peak Pulse Current       | $I_{PP}$  | IEC61000-4-5 (8x20 $\mu\text{s}$ )  | 12  | 14    |     | A             |
| Clamping Voltage                 | $V_C$     | $I_{PP} = 12\text{ A}$ , (8/20 $\mu\text{s}$ pulse)   |     | 8.6   | 9.6 | V             |
| Clamping Voltage<br>TLP (Note 1) | $V_C$     | $I_{PP} = 8\text{ A}$ } IEC 61000-4-2 Level 2 equivalent<br>( $\pm 4\text{ kV}$ Contact, $\pm 8\text{ kV}$ Air)   |     | 7.4   |     | V             |
|                                  |           | $I_{PP} = 16\text{ A}$ } IEC 61000-4-2 Level 2 equivalent<br>( $\pm 8\text{ kV}$ Contact, $\pm 16\text{ kV}$ Air) |     | 9.1   |     |               |
| Dynamic Resistance               | $R_{DYN}$ | I/O Pin to GND, 100 ns TLP  |     | 0.21  |     | $\Omega$      |
| Junction Capacitance             | $C_J$     | $V_R = 0\text{ V}$ , $f = 1\text{ MHz}$   |     | 30    | 33  | pF            |

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

1. ANSI/ESD STM5.5.1 – Electrostatic Discharge Sensitivity Testing using Transmission Line Pulse (TLP) Model.


TLP conditions:  $Z_0 = 50\ \Omega$ ,  $t_p = 100\text{ ns}$ ,  $t_r = 1\text{ ns}$ , averaging window;  $t_1 = 70\text{ ns}$  to  $t_2 = 90\text{ ns}$ .

## ORDERING INFORMATION


| Device         | Package             | Shipping <sup>†</sup> |
|----------------|---------------------|-----------------------|
| ESDM1031MX4T5G | X4DFN2<br>(Pb-Free) | 10,000 / Tape & Reel  |

<sup>†</sup>For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.


TYPICAL CHARACTERISTICS




**Figure 1. ESD Clamping Voltage  
Positive 8 kV Contact per IEC61000-4-2**




**Figure 2. ESD Clamping Voltage  
Negative 8 kV Contact per IEC61000-4-2**




**Figure 3. Positive TLP I-V Curve**



**Figure 4. Negative TLP I-V Curve**



**Figure 5. Positive Clamping Voltage vs. Peak  
Pulse Current ( $t_p = 8/20 \mu s$ )**



**Figure 6. Negative Clamping Voltage vs. Peak  
Pulse Current ( $t_p = 8/20 \mu s$ )**

TYPICAL CHARACTERISTICS




Figure 7. Breakdown Voltage




Figure 8. Reverse Leakage Current




Figure 9. Magnitude vs. Frequency

## IEC 61000-4-2 Spec.

| Level | Test Voltage (kV) | First Peak Current (A) | Current at 30 ns (A) | Current at 60 ns (A) |
|-------|-------------------|------------------------|----------------------|----------------------|
| 1     | 2                 | 7.5                    | 4                    | 2                    |
| 2     | 4                 | 15                     | 8                    | 4                    |
| 3     | 6                 | 22.5                   | 12                   | 6                    |
| 4     | 8                 | 30                     | 16                   | 8                    |




Figure 10. IEC61000-4-2 Spec

## Transmission Line Pulse (TLP) Measurement

Transmission Line Pulse (TLP) provides current versus voltage (I-V) curves in which each data point is obtained from a 100 ns long rectangular pulse from a charged transmission line. A simplified schematic of a typical TLP system is shown in Figure 11. TLP I-V curves of ESD protection devices accurately demonstrate the product's ESD capability because the 10s of amps current levels and under 100 ns time scale match those of an ESD event. This is illustrated in Figure 12 where an 8 kV IEC 61000-4-2 current waveform is compared with TLP current pulses at 8 A and 16 A. A TLP I-V curve shows the voltage at which the device turns on as well as how well the device clamps voltage over a range of current levels.




Figure 11. Simplified Schematic of a Typical TLP System





Figure 12. Comparison Between 8 kV IEC 61000-4-2 and 8 A and 16 A TLP Waveforms

# ESDM1031

## PACKAGE DIMENSIONS

**X4DFN2, 0.445x0.24, 0.27P**  
CASE 718AA  
ISSUE A




### NOTES:

1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
2. CONTROLLING DIMENSION: MILLIMETERS.
3. EXPOSED COPPER ALLOWED AS SHOWN.

| DIM | MILLIMETERS |       |       |
|-----|-------------|-------|-------|
|     | MIN         | NOM   | MAX   |
| A   | 0.15        | 0.18  | 0.21  |
| A1  | ---         | ---   | 0.03  |
| b   | 0.170       | 0.185 | 0.200 |
| D   | 0.415       | 0.445 | 0.475 |
| E   | 0.210       | 0.240 | 0.270 |
| e   | 0.270 BSC   |       |       |
| L   | 0.105       | 0.120 | 0.135 |

### RECOMMENDED MOUNTING FOOTPRINT\*



See Application Note AND8398/D for more mounting details

\*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at [www.onsemi.com/site/pdf/Patent-Marketing.pdf](http://www.onsemi.com/site/pdf/Patent-Marketing.pdf). ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

## PUBLICATION ORDERING INFORMATION

### LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor  
19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA  
Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada  
Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada  
Email: [orderlit@onsemi.com](mailto:orderlit@onsemi.com)

**N. American Technical Support:** 800-282-9855 Toll Free  
USA/Canada  
**Europe, Middle East and Africa Technical Support:**  
Phone: 421 33 790 2910

**ON Semiconductor Website:** [www.onsemi.com](http://www.onsemi.com)

**Order Literature:** <http://www.onsemi.com/orderlit>

For additional information, please contact your local Sales Representative

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[onsemi:](#)

[ESDM1031MX4T5G](#)