


AC Fan Speed Control Unit



Input Voltage:	120/220 VAC±15%
Input Protection:	2A Circuit Breaker
Output Protection:	2A Circuit Breaker (Each Channel)
4 Preset Settings:	Off, Low, Medium, & High
Speed Adjustment: (User accessible)	External 4 Detent Rotary Switch (Off, Low, Medium, High) Internal Potentiometers for each speed
Input Connector:	IEC C14
Output Connectors:	IEC C13
COMMENTS	
Contact Manufacturer for alternate circuit breaker configurations and higher current options by special orders.	

The Dual Channel Phase Control Unit allows the user to control fan speed for single or multiple fan assemblies. Effectively this allows the application engineer to specify and control fan noise, speed and air delivery very precisely according to specific application requirements. Four factory presets (user adjustable) allows for maximum flexibility with minimum setup time. This unit has been specially designed with fan trays and equipment racks in mind where noise vs airflow needs to be controlled according to immediate needs.

Knight Electronics
10557 Metric Drive
Dallas, Texas 75243
(Tel) 214-340-0265
(Fax) 214-340-5870
www.knightonline.com

Description:
Dual Channel Phase Controller

Part No:
OA11/22CB



KNIGHT
Electronics, Inc.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Orion Fans:

[OA11/22CB](#)