

# Dual Voltage Fans



115/230 Volts AC  
80mm - 120mm (3.15" - 4.7")

|  | Model Number<br>80 x 25 | Speed<br>(RPM) | Airflow<br>(CFM) | Noise (dB) | Volts AC | Voltage<br>Range | Watts | Max. Static<br>Pressure ("H2O) |
|-----------------------------------------------------------------------------------|-------------------------|----------------|------------------|------------|----------|------------------|-------|--------------------------------|
|                                                                                   | OA825AP-11/22-1WB       | 3000           | 25               | 28         | 115/230  | 100~240          | 9     | .21                            |
|                                                                                   | OA825AP-11/22-2WB       | 2300           | 18               | 24         | 115/230  | 100~240          | 6     | .14                            |
|                                                                                   | OA825AP-11/22-3WB       | 1900           | 16               | 19         | 115/230  | 100~240          | 4     | .11                            |

|  | Model Number<br>80 x 38 | Speed<br>(RPM) | Airflow<br>(CFM) | Noise (dB) | Volts AC | Voltage<br>Range | Watts | Max. Static Pres-<br>sure ("H2O) |
|-----------------------------------------------------------------------------------|-------------------------|----------------|------------------|------------|----------|------------------|-------|----------------------------------|
|                                                                                   | OA80AP-11/22-1WB        | 3000           | 31               | 29         | 115/230  | 100~240          | 12    | 0.24                             |
|                                                                                   | OA80AP-11/22-2WB        | 2300           | 23               | 22         | 115/230  | 100~240          | 9     | 0.15                             |
|                                                                                   | OA80AP-11/22-3WB        | 1600           | 17               | 18         | 115/230  | 100~240          | 5     | 0.10                             |


|  | Model Number<br>92 x 25 | Speed<br>(RPM) | Airflow<br>(CFM) | Noise (dB) | Volts AC | Voltage<br>Range | Watts | Max. Static<br>Pressure ("H2O) |
|-----------------------------------------------------------------------------------|-------------------------|----------------|------------------|------------|----------|------------------|-------|--------------------------------|
|                                                                                   | OA92AP-11/22-1WB        | 3000           | 35               | 30         | 115/230  | 100~240          | 13    | .20                            |
|                                                                                   | OA92AP-11/22-2WB        | 2300           | 27               | 22         | 115/230  | 100~240          | 10    | .14                            |
|                                                                                   | OA92AP-11/22-3WB        | 1900           | 22               | 19         | 115/230  | 100~240          | 6     | .09                            |

|  | Model Number<br>92 x 38 | Speed<br>(RPM) | Airflow<br>(CFM) | Noise (dB) | Volts AC | Voltage<br>Range | Watts | Max. Static<br>Pressure ("H2O) |
|-------------------------------------------------------------------------------------|-------------------------|----------------|------------------|------------|----------|------------------|-------|--------------------------------|
|                                                                                     | OA938AP-11/22-1WB       | 3100           | 50               | 32         | 115/230  | 100~240          | 9     | .22                            |
|                                                                                     | OA938AP-11/22-2WB       | 2400           | 39               | 23         | 115/230  | 100~240          | 5     | .17                            |
|                                                                                     | OA938AP-11/22-3WB       | 1800           | 26               | 19         | 115/230  | 100~240          | 3     | .10                            |

|  | Model Number<br>120 x 25 | Speed<br>(RPM) | Airflow<br>(CFM) | Noise (dB) | Volts AC | Voltage<br>Range | Watts | Max. Static<br>Pressure ("H2O) |
|-------------------------------------------------------------------------------------|--------------------------|----------------|------------------|------------|----------|------------------|-------|--------------------------------|
|                                                                                     | OA125AP-11/22-1WB        | 2900           | 81               | 32         | 115/230  | 100~240          | 13    | .23                            |
|                                                                                     | OA125AP-11/22-2WB        | 2300           | 60               | 27         | 115/230  | 100~240          | 10    | .18                            |
|                                                                                     | OA125AP-11/22-3WB        | 1600           | 42               | 22         | 115/230  | 100~240          | 6     | .12                            |

|  | Model Number<br>120 x 38 | Speed<br>(RPM) | Airflow<br>(CFM) | Noise (dB) | Volts AC | Voltage<br>Range | Watts | Max. Static<br>Pressure ("H2O) |
|-------------------------------------------------------------------------------------|--------------------------|----------------|------------------|------------|----------|------------------|-------|--------------------------------|
|                                                                                     | OA109AP-11/22-1WB        | 3000           | 110              | 42         | 115/230  | 100~240          | 15    | .28                            |
|                                                                                     | OA109AP-11/22-2WB        | 2300           | 71               | 35         | 115/230  | 100~240          | 11    | .24                            |
|                                                                                     | OA109AP-11/22-3WB        | 1600           | 51               | 25         | 115/230  | 100~240          | 8     | .15                            |

Dual voltage fans are connected via 4 power leads. They can be configured for switchable operation.



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Orion Fans:

[OA938AP-11/22-1WB](#) [OA938AP-11/22-3WB](#) [OA938AP-11/22-2WB](#)