

Electronic housing - ME MAX 22,5 2-2 KMGY VPE1 - 2201319

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Complete housing, length: 99 mm, with vents, Complete housing, Cross connection: DIN rail bus connector, color: light gray, width: 22.5 mm, height: 114.5 mm, number of positions cross connector: 5

Your advantages

- ✓ Item is from the ME-MAX product range
- ✓ Easy mounting
- ✓ Available in overall widths from 6.2 mm to 90 mm, modular extension is possible
- ✓ Inflammability class V0 according to UL 94
- ✓ Variety of connection technologies
- ✓ Can be mounted on the DIN rail
- ✓ Optional with bus connector for DIN rail mounting as well as power connection system
- ✓ DIN rail bus connector as an option
- ✓ Labels for additional labeling as an option
- ✓ Large PCB surface despite compact housing dimensions
- ✓ Large front surface for high-pos. plugs or operating and setting elements
- ✓ Easy module replacement without interrupting the contact chain
- ✓ The fitted cover is easy to adapt and print
- ✓ Fixed or plug-in connection technology can be combined on up to three connection levels, with different pitches
- ✓ Functional earth ground contact as an option
- ✓ Transparent front cover can be swiveled

RoHS

Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 766975
GTIN	4046356766975

Technical data

General

Housing type	Complete housing
--------------	------------------

Electronic housing - ME MAX 22,5 2-2 KMGY VPE1 - 2201319

Technical data

General

Housing material	Polyamide
Color (RAL)	light gray (7035)

Ambient conditions

Ambient temperature (storage/transport)	-40 °C ... 70 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)

Dimensions

Length	99 mm
Height	114.5 mm
Width	22.5 mm
Depth	99 mm

Technical data

Connection in acc. with standard	CUL
Indicator1	CUL1
Power dissipation without gap	6.1 W
Power dissipation with 20 mm gap	12.1 W
Number of positions	16

Standards and Regulations

Connection in acc. with standard	CUL
Flammability rating according to UL 94	V0

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Approvals

Approvals

Approvals

UL Recognized

Ex Approvals

Approval details

Electronic housing - ME MAX 22,5 2-2 KMGY VPE1 - 2201319

Approvals

UL Recognized



<http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm>

FILE E 240868

Phoenix Contact 2018 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[2201319](#)