


Relay Module - EMG 22-B1-REL-G 24/TRN24-AND - 2298014

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Relay module, with miniature switching relay, with integrated n-p-n transistor control, for low control currents, contact (AgNi 90/10): Medium to large loads, two N/O contacts, nominal control voltage 24 V DC

RoHS

Key Commercial Data

Packing unit	10 pc
GTIN	 4 017918 483807
GTIN	4017918483807

Technical data

Note

Utilization restriction	EMC: class A product, see manufacturer's declaration in the download area
-------------------------	---

Dimensions

Width	22.5 mm
Height	75 mm
Depth	100 mm

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
---------------------------------	------------------

Coil side

Nominal input voltage U_N	24 V DC
Input voltage range in reference to U_N	0.8 ... 1.1
Typical input current at U_N	21 mA
Typical response time	12 ms
Typical release time	7 ms
Protective circuit	Reverse polarity protection Polarity protection diode
	Free-wheeling diode Damping diode
Operating voltage display	LED
Power dissipation for nominal condition	0.5 W

Contact side

Contact type	Single contact, 2 N/O contact
Type of switch contact	Single contact

Relay Module - EMG 22-B1-REL-G 24/TRN24-AND - 2298014

Technical data

Contact side

Contact material	AgNi
Maximum switching voltage	250 V AC
Limiting continuous current	4 A
Interrupting rating (ohmic load) max.	96 W (at 24 V DC)
	85 W (at 48 V DC)
	60 W (at 60 V DC)
	44 W (at 110 V DC)
	57 W (at 220 V DC)
	1000 VA (for 250 V AC)

Connection data input side

Connection name	Coil side
Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Conductor cross section solid	0.2 mm ² ... 4 mm ²
Conductor cross section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross section AWG	24 ... 12

Connection data output side

Connection name	Contact side
Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Conductor cross section solid	0.2 mm ² ... 4 mm ²
Conductor cross section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross section AWG	24 ... 12

General

Degree of protection	IP20
Mechanical service life	3x 10 ⁷ cycles
Mounting position	any

Standards and Regulations

Designation	Air clearances and creepage distances, input/output
Standards/regulations	DIN EN 50178: 1998-04
Rated insulation voltage	260 V
Rated surge voltage	6 kV (1.2/50 µs)
Insulation	Reinforced insulation
Degree of pollution	2
Overvoltage category	III
Designation	Air and creepage distances, output/output
Standards/regulations	DIN EN 50178: 1998-04

Relay Module - EMG 22-B1-REL-G 24/TRN24-AND - 2298014

Technical data

Standards and Regulations

Rated insulation voltage	260 V
Rated surge voltage	2.2 kV (1.2/50 µs)
Insulation	Functional insulation
Degree of pollution	2
Overvoltage category	II

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Approvals


Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		RU C- DE.A*30.B.01082
-----	---	--------------------------

Phoenix Contact 2018 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

2298014