


3.0 mm×2.6 mm SMD Light Touch Switches

Type: **EVPAF**



■ Features

- External dimensions: 3.0 mm×2.6 mm, Height 0.65 mm
- High operability
Equipped with an actuator (push plate)
- Low temperature use

■ Recommended Applications

- Operation switches for portable electronic equipment
(Mobile phone, Portable audio)

■ Explanation of Part Numbers

1	2	3	4	5	6	7	8	9
E	V	P	A	F				
Product Code			Type			Height		

■ Specifications

Type		Snap action/Push-on type SPST
Electrical	Rating	10 μ A 2 Vdc to 20 mA 15 Vdc (Resistive load)
	Contact Resistance	500 m Ω max.
	Insulation Resistance	50 M Ω min. (at 100 Vdc)
	Dielectric Withstanding Voltage	250 Vac for 1 minute
	Bouncing	10 ms max. (ON, OFF)
Mechanical	Operating Force	1.3 N, 1.6 N, 2.4 N, 3.4 N
	Travel	0.15 mm
Endurance	Operating Life	1.3 N, 1.6 N, 3.4 N : 100000 cycles min., 2.4 N : 500000 cycles min.
Operating Temperature		−40 °C to +85 °C
Storage Temperature		−40 °C to +85 °C (Bulk)
		−20 °C to +60 °C (Taping)
Minimum Quantity/Packing Unit		8000 pcs. Embossed Taping (Reel Pack)
Quantity/Carton		40000 pcs.

Note: Non washable

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use.
Should a safety concern arise regarding this product, please be sure to contact us immediately.

00 Oct. 2012

■ Dimensions in mm (not to scale)

No. 1 EVPAF (Embossed Taping) With J-bent terminals 	3 4-0.5 2-1.8 2.6 (0.75) ø0.65 A B A' B' (Adhesive) (Push plate) 2-3.4 4-0.35 (EVPAFKB65) 4-0.35^{+0.15}_{-0.15} 3 4-0.5 2-1.8 2.6 (0.75) ø0.65 A B A' B' (Adhesive) (Push plate) 2-3.4 4-0.35 (EVPAFKB65) 4-0.35^{+0.15}_{-0.15} 3 4-0.5 2-1.8 2.6 (0.75) ø0.65 A B A' B' (Adhesive) (Push plate) 2-3.4 4-0.35 (EVPAFKB65) 4-0.35^{+0.15}_{-0.15} (Without the remainder of the gate) 0.65 0.44 A B A' B' Circuit diagram 2-3.5±0.05 2-2.4±0.05 1.6 2-1.2±0.05 2-2.4±0.05 2.6 A B A' B' PWB land pattern for reference Part of A-A' terminal is exposed at  area. Any land pattern or vias shall not be provided at  area.		
Part Numbers EVPAFKB65 EVPAFFB65	Operating Force 1.3 N 1.6 N	Height 0.65 mm 0.65 mm	Operating Life 100000 cycles 100000 cycles
No. 2 EVPAF (Embossed Taping) With J-bent terminals 	3 4-0.5 2-1.8 2.6 (0.75) ø0.65 A B A' B' (Adhesive) (Push plate) 2-3.4 4-0.35 3 4-0.5 2-1.8 2.6 (0.75) ø0.65 A B A' B' (Adhesive) (Push plate) 2-3.4 4-0.35 3 4-0.5 2-1.8 2.6 (0.75) ø0.65 A B A' B' (Adhesive) (Push plate) 2-3.4 4-0.35 (Without the remainder of the gate) 0.70 0.48 A B A' B' Circuit diagram 2-3.5±0.05 2-2.4±0.05 1.6 2-1.2±0.05 2-2.4±0.05 2.6 A B A' B' PWB land pattern for reference Part of A-A' terminal is exposed at  area. Any land pattern or vias shall not be provided at  area.		
Part Numbers EVPAF5B70 EVPAF7B70	Operating Force 3.4 N 2.4 N	Height 0.7 mm 0.7 mm	Operating Life 100000 cycles 500000 cycles

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use.
Should a safety concern arise regarding this product, please be sure to contact us immediately.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panasonic:

[EVP-0AFB65](#) [EVP-AF5B65](#) [EVP-AF7B65](#) [EVP-AFFB65](#)