

“PGS” Graphite Sheets

Type: **EYG**

PGS (Pyrolytic Graphite Sheet) is a heat sink sheet with high thermal conductivity and high flexibility. PGS is made of graphite with a structure that is close to a single crystal. This is achieved by highly oriented polymer film sheet, a process which has never been implemented before.




■ Features

- Excellent thermal conductivity: 600 to 800 W/(m·K)
(Twice as high as copper, three times as high as aluminum)
- Lightweight: Specific gravity: 1.0 g/cm³
(1/9 that of copper, 1/3 that of aluminum)
- Flexible and easy to be cut or trimmed.
(withstands repeated bending)
- Low thermal resistance

■ Recommended applications


- Notebook personal computers, DVDs, DVCs, mobile phones
- Semiconductor manufacturing equipment
(Sputtering, Dry etching, Steppers)
- Optical communications equipment

■ Explanation of Part Numbers



■ Dimensions in mm

Part No.	Dimension X (Short)	Dimension Y (Long)	Thickness
EYGS182310	18.0±0.5cm	23.0±0.5cm	0.10±0.05mm
EYGS121810	11.5±0.5cm	18.0±0.5cm	0.10±0.05mm
EYGS091210	9.0±0.5cm	11.5±0.5cm	0.10±0.05mm




■ Characteristics


Characteristics		Specification
Thickness		0.10 ± 0.05 mm
Density		1.0 g/cm ³
Thermal conductivity	a-b plane	600 to 800 W/(m·K)
Electrical conductivity		10000 S/cm
Extensional strength		19.6 MPa
Expansion coefficient	a-b plane	9.3 × 10 ⁻⁷ 1/K
	c axis	3.2 × 10 ⁻⁵ 1/K
Heat resistance		400 °C
Bending(angle 180,R5)		10000 cycles

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

Thermal conductivity of PGS compared to other materials



Layered structure of PGS



Dimensions in mm (not to scale)

	EYGS182310	EYGM121810SS	EYGM121810SW	EYGA091210K	EYGA091210A	EYGC091210C	EYGL□□□□□P2	EYGM091210CT
Type	PGS only	Silicon layered type		Polyimide tape attached	Doble-side-adhesive tape attached type	Acrylic adhesive (one side) attached type	PET-covered type	Conductive adhesive tape type
		One-sided type	Double-sided type					
Structure								
Thickness (μm)	100±50	200±50	300±50	130±50	130±50	110±50	150±50 (1 pcs.) 350±50 (3 pcs.)	130±50
Thermal* resistance (°C/W)	0.4	1.0	1.4	2.4	1.7	0.8	2.0	1.6
Thermal* conductivity (direction of the sheet surface) (W/m·k)	600 to 800	250 to 300	250 to 300	500 to 600	500 to 600	550 to 650	500 to 600	500 to 600
Withstand temperature max. (°C)	400	180	180	180	80	80	105	80
Standard To be separately consulted sample, (± 5 mm)	180×230	115×180	115×180	90×115	90×115	90×115	To be separately consulted	90×115
Features	· Usable up to 400°C · Low thermal resistance · Conductivity	· Cushioning properties · One-side insulation	· Cushioning properties · Both-side insulation	· High insulation · High heat resistance	· Insulation · Strong adhesion	· Low thermal resistance	· High insulation	· Conductivity

*The above values are only for reference. they can be changed without notice.

Part No., quantity and country of origin are designated on outer packages in English.

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panasonic:

[EYG-C121810C](#) [EYG-C091210C](#)