

Surface Mount Type

Discontinued

Series: TA Type : V

Country of Origin

Japan




- Features
- Endurance: 125°C 1000 h
 - For use near car engines.
 - Good for electronically controlled units (ECU, ABS etc).
 - Vibration-proof product is available upon request. (ø8 ≤)
 - RoHS directive not compliant.
 - TG series is recommended for RoHS compliant.

Specifications

Category temp. range	-40 to +125°C						
Rated W.V. Range	10 to 50 V .DC						
Nominal Cap. Range	10 to 330 μ F						
Capacitance Tolerance	±20 % (120Hz/+20°C)						
DC Leakage Current	I ≤ 0.01 CV or 3(μ A) after 2 minutes (Whichever is greater)						
tan δ	Please see the attached standard products list						
Characteristics at Low Temperature	W.V. (V)	10	16	25	35	50	(Impedance ratio at 120Hz)
	-25 / +20 °C	8	5	4	3	3	
	-40 / +20 °C	14	12	10	8	8	
Endurance	After applying rated working voltage for 1000 hours at +125±2°C and then being stabilized at +20°C, capacitors shall meet the following limits.						
	Capacitance change		±30 % of initial measured value				
	tan δ		≤ 300 % of initial specified value				
	DC leakage current		≤ initial specified value				
Shelf Life	After storage for 500 hours at +125±2°C with no voltage applied and then being stabilized at +20°C, capacitors shall meet the following limits. (With voltage treatment)						
	Capacitance change		±20% of initial measured value				
	tan δ		≤200 % of initial specified value				
	DC leakage current		≤initial specified value				
Resistance to Soldering Heat	After reflow soldering and then being stabilized at +20°C, capacitor shall meet the following limits.						
	Capacitance change		±10 % of initial measured value				
	tan δ		≤ initial specified value				
	DC leakage current		≤ initial specified value				

Marking


Example: 16V 100 μF (Polarized)



W.V. code

V	10	16	25	35	50
Code	A	C	E	V	H

Dimensions in mm (not to scale)



Size code	D	L	A,B	H	I	W	P	K
E	8.0	6.2	8.3	9.5MAX	3.4	0.65±0.1	2.2	0.35 -0.20 to +0.15
F	8.0	10.2	8.3	10.0MAX	3.4	0.90±0.2	3.1	0.70 ±0.2
G	10.0	10.2	10.3	12.0MAX	3.5	0.90±0.2	4.6	0.70 ±0.2

Case size

W.V.(V) Cap. (μF)	10 (1A)	16 (1C)	25 (1E)	35 (1V)	50 (1H)
10					E
22					E
33				E	F
47			E	F	G
100	E	F	F	G	
220	F	G			
330	G				

■ Standard Products

Discontinued

W.V. (V)	Cap. (±20%) (μF)	Case size			Specification		Part No. (RoHS: not compliant)	Min. Packaging Q'ty
		Dia. (mm)	Length (mm)	Size Code	Ripple current (100kHz) (+125°C) (mA)	tan δ (120Hz) (+20°C)		
10	100	8	6.2	E	62	0.32	EEVTA1A101P	(2) 1000
	220	8	10.2	F	93	0.32	EEVTA1A221P	(2) 500
	330	10	10.2	G	118	0.32	EEVTA1A331P	(2) 500
16	100	8	10.2	F	89	0.24	EEVTA1C101P	(2) 500
	220	10	10.2	G	113	0.24	EEVTA1C221P	(2) 500
25	47	8	6.2	E	56	0.21	EEVTA1E470P	(2) 1000
	100	8	10.2	F	84	0.21	EEVTA1E101P	(2) 500
35	33	8	6.2	E	53	0.18	EEVTA1V330P	(2) 1000
	47	8	10.2	F	79	0.18	EEVTA1V470P	(2) 500
	100	10	10.2	G	101	0.18	EEVTA1V101P	(2) 500
50	10	8	6.2	E	25	0.18	EEVTA1H100P	(2) 1000
	22	8	6.2	E	50	0.18	EEVTA1H220P	(2) 1000
	33	8	10.2	F	74	0.18	EEVTA1H330P	(2) 500
	47	10	10.2	G	94	0.18	EEVTA1H470P	(2) 500

The taping dimensions are explained on p.187 of our Catalog.

Please use it as a reference guide.

Endurance : 125°C 1000h

Reflow profile(Fig-1 to Fig-5) listed on the last page.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panasonic:

[EEV-TA1V470P](#) [EEV-TA1V101P](#) [EEV-TA1V330P](#) [EEV-TA1A101P](#) [EEV-TA1A221P](#) [EEV-TA1A331P](#) [EEV-TA1C101P](#) [EEV-TA1C221P](#) [EEV-TA1E470P](#) [EEV-TA1H220P](#) [EEV-TA1H330P](#) [EEV-TA1H470P](#) [EEV-TA1H100P](#)
[EEV-TA1E101P](#)