


5N Type 2R Light Touch Switches

Type: **EVQ2**

■ Features

- Wealth of product types: With or without a ground terminal, vertical type, snap-in terminals, etc.
- Can be automatically dip-soldered: Integral molding of the terminals and main body prevents the escape of flux.

■ Recommended Applications

- Operating switches for electronic equipment

■ Explanation of Part Numbers

1	2	3	4	5	6	7	8	9
E	V	Q	2	1/2				
Product Code			Type	Operating Force	Product Height		Push Plate Color	

■ Specifications

Type		Snap action/Push-on type SPST	
Electrical	Circuit Diagram		
	Rating	10 μ A 2 V DC to 20 mA 15 V DC (Resistive load)	
	Contact Resistance	50 m Ω max.	
	Insulation Resistance	50 M Ω min. (at 100 V DC)	
	Dielectric Withstanding Voltage	250 V AC for 1 minute	
	Bouncing	3 ms max. (ON) 8 ms max. (OFF)	
Mechanical	Operating Force	1.0 N $\pm$ 0.4 N 1.3 N $\pm$ 0.4 N 1.6 N $\pm$ 0.5 N	2.6 N $\pm$ 0.6 N
	Travel	0.25 mm $\pm$ 0.10 mm	
Endurance	Operating Life	100,000 cycles min.*	50,000 cycles min.
Operating Temperature		-20 °C to +70 °C	
Storage Temperature		-40 °C to +85 °C (Bulk) -20 °C to +40 °C (Taping)	
Minimum Quantity/Packing Unit		1,000 pcs. Radial Taping (Reel Pack)	
Quantity/Carton		10,000 pcs.	

*1 million cycles also available, consult our salesmen.

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use.
Should a safety concern arise regarding this product, please be sure to contact us immediately.


■ Dimensions in mm (not to scale)

EVQ2



With ground terminal

2-terminals type



Without ground terminal



General dimension tolerance : ± 0.2
() dimensions are reference dimensions.



JIS C0806-2 shall be applied to the items not specified here.



PWB mounting hole for reference
(Pitch tolerance: ± 0.1)
View from mounting side

Part Numbers	Operating Force	H=Height	Push Plate Color	Operating Life
EVQ21304M	1.0 N	4.3 mm	White	100,000 cycles
EVQ21305R	1.0 N	5.0 mm	Red	100,000 cycles
EVQ21307K	1.0 N	7.0 mm	Black	100,000 cycles
EVQ21309K	1.0 N	9.5 mm	Black	100,000 cycles
EVQ21404M	1.3 N	4.3 mm	White	100,000 cycles
EVQ21405R	1.3 N	5.0 mm	Red	100,000 cycles
EVQ21407K	1.3 N	7.0 mm	Black	100,000 cycles
EVQ21409K	1.3 N	9.5 mm	Black	100,000 cycles
EVQ21504M	1.6 N	4.3 mm	White	100,000 cycles
EVQ21505R	1.6 N	5.0 mm	Red	100,000 cycles
EVQ21507K	1.6 N	7.0 mm	Black	100,000 cycles
EVQ21509K	1.6 N	9.5 mm	Black	100,000 cycles
EVQ22704M	2.6 N	4.3 mm	White	50,000 cycles
EVQ22705R	2.6 N	5.0 mm	Red	50,000 cycles
EVQ22707K	2.6 N	7.0 mm	Black	50,000 cycles
EVQ22709K	2.6 N	9.5 mm	Black	50,000 cycles

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use.
Should a safety concern arise regarding this product, please be sure to contact us immediately.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panasonic:

[EVQ-21504M](#) [EVQ-21507K](#) [EVQ-21304M](#) [EVQ-21305R](#) [EVQ-21307K](#) [EVQ-21309K](#) [EVQ-21404M](#) [EVQ-21405R](#)
[EVQ-21407K](#) [EVQ-21409K](#) [EVQ-21505R](#) [EVQ-21509K](#) [EVQ-22704M](#) [EVQ-22705R](#) [EVQ-22707K](#) [EVQ-22709K](#)
[EVQ-21G04K](#)