




REVISIONS				
ZONE	REV.	DESCRIPTION	DATE	APPROVED
	A	RELEASE	JRM 2/11/21	

ALL DIMENSIONS ARE
FOR REFERENCE ONLY
DIMENSIONS ARE IN INCHES [MILLIMETERS]
UNLESS OTEHRWISE NOTED

SPECIFICATIONS

OVERALL HEIGHT..... 17.02 [432.81]
ROTATION..... 360 DEGREES
TURN..... 360 DEGREES
TILT..... 90 DEGREES
SHIPPING WEIGHT..... 6.75 LBS
VISE OPENING..... 9 1/4 [234.95] MAXIMUM
JAW PAD WIDTH..... 1.5 [38.10]
JAW PAD HEIGHT..... 1.875 [47.63]

- MATERIAL:
- 1. VISE HEAD ASSY*..... LOW CARBON STEEL, ZINC DIE CASTING
 - 2. BASE ASSY**..... #3 ZINC DIE CAST SILVER PAINT
 - 3. KNOB..... BLACK GLASS REINFORCED THERMAL COMPOSITE ALLOY
 - 4. BASE CLAMP***..... #3 ZINC DIE CAST SILVER PAINT
 - 5. JAW PADS..... BLACK NEOPRENE
 - 6. BUMPON..... BLACK RUBBER
 - 7. SCREW..... 1/4-20 X 1/2 PHILLIPS HEAD, STEEL

*VISE HEAD ASSEMBLY INCLUDES ADJUSTING SCREW, GUIDE ROD, GUIDE BLOCKS AND CRANK HANDLE.
**BASE ASSEMBLY INCLUDES HALF BALL HOUSINGS, RETAINER RING, SCREWS, STUD AND NUT.
***BASE CLAMP INCLUDES LEVER ROD AND LEVELING BUTTON.

		UNLESS OTHERWISE SPECIFIED:		NAME	DATE	PANAVISE® 7540 Colbert Drive, Reno, Nevada 89511-1225 Phone (775) 850-2900 Fax (775) 850-2929					
		DIMENSIONS ARE IN INCHES TOLERANCES: FRACTIONAL ± 1/64 ANGULAR: MACH ± 1/2° BEND ± TWO PLACE DECIMAL: ±.01 THREE PLACE DECIMAL: ±.005	DRAWN						TITLE: HD CLAMPING MULTIPURPOSE VISE SPEC SHEET		
			CHECKED								
			ENG APPR.								
			MFG APPR.								
		INTERPRET GEOMETRIC TOLERANCING PER: ASME 14.5M -2009 MATERIAL	Q.A.			SIZE DWG. NO. REV B 314-SP A					
			COMMENTS:								
NEXT ASSY	USED ON	FINISH				SCALE: 1:3 WEIGHT: SHEET 1 OF 1					
APPLICATION		DO NOT SCALE DRAWING									

PROPRIETARY AND CONFIDENTIAL
THE INFORMATION CONTAINED IN THIS
DRAWING IS THE SOLE PROPERTY OF
PANAVISE PRODUCTS INC. ANY
REPRODUCTION IN PART OR AS A WHOLE
WITHOUT THE WRITTEN PERMISSION OF
PANAVISE PRODUCTS INC IS
PROHIBITED.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panavise:](#)

[314](#)