




REVISIONS				
ZONE	REV.	DESCRIPTION	DATE	APPROVED
	A	RELEASE	JRM 2/15/21	

ALL DIMENSIONS ARE
FOR REFERENCE ONLY
DIMENSIONS ARE IN INCHES [MILLIMETERS]
UNLESS OTEHRWISE NOTED

SPECIFICATIONS

- OVERALL HEIGHT..... 7.20 [182.89]
ROTATION..... 360 DEGREES
TURN..... 360 DEGREES
TILT..... 210 DEGREES
SHIPPING WEIGHT..... 8.60 LBS
VISE OPENING..... 9 1/4 [234.95] MAXIMUM
JAW PAD WIDTH..... 1.5 [38.10]
JAW PAD HEIGHT..... 1.875 [47.63]

MATERIAL:

1. VISE HEAD ASSY*..... LOW CARBON STEEL,
ZINC DIE CASTING
2. BASE ASSY**..... #3 ZINC DIE CAST SILVER PAINT
3. KNOB..... BLACK GLASS REINFORCED
THERMAL COMPOSITE ALLOY
4. BASE CAST IRON, PAINTED BLACK
5. JAW PADS..... BLACK NEOPRENE
6. BUMPON..... BLACK RUBBER
7. SCREW..... 1/4-20 X 1/2 PHILLIPS HEAD, STEEL

*VISE HEAD ASSEMBLY INCLUDES ADJUSTING SCREW, GUIDE ROD, GUIDE
BLOCKS AND CRANK HANDLE.
**BASE ASSEMBLY INCLUDES HALF BALL HOUSINGS, RETAINER RING,
SCREWS, STUD AND NUT.

PROPRIETARY AND CONFIDENTIAL
THE INFORMATION CONTAINED IN THIS
DRAWING IS THE SOLE PROPERTY OF
PANAVISE PRODUCTS INC. ANY
REPRODUCTION IN PART OR AS A WHOLE
WITHOUT THE WRITTEN PERMISSION OF
PANAVISE PRODUCTS INC IS
PROHIBITED.

UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN INCHES TOLERANCES: FRACTIONAL ± 1/64 ANGULAR: MACH ± 1/2° BEND ± TWO PLACE DECIMAL: ± .01 THREE PLACE DECIMAL: ± .005		DRAWN	NAME	DATE	 7540 Colbert Drive, Reno, Nevada 89511-1225 Phone (775) 850-2900 Fax (775) 850-2929 TITLE: PORTABLE MULTI-PRUPOSE VISE SPEC SHEET	
		CHECKED				
		ENG APPR.				
		MFG APPR.				
		Q.A.				
INTERPRET GEOMETRIC TOLERANCING PER: ASME 14.5M -2009 MATERIAL		COMMENTS:			SIZE B	DWG. NO. 334-SP
NEXT ASSY		USED ON		FINISH	REV A	
APPLICATION		DO NOT SCALE DRAWING			SCALE: 1:2	WEIGHT:
					SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panavise:](#)

[334](#)