


Technical drawing of a 3D-printed part. The drawing shows a side view of a component with a central rectangular section and rounded ends. The dimensions are as follows:

- Overall width: 2.21 [56.1]
- Overall height: 1.97 [50.0]
- Height of the central section: 0.79 [20.1]



1.26
[32.0]

TO APPLY LATCHING WIRE CLIP:
(APPLY TO A CLEAN GREASE FREE SURFACE)

- NO WARRANTY, EXPRESSED OR IMPLIED, IS MADE BY PANDUIT WITH RESPECT TO ADHESIVE BOND PERFORMANCE. AMONG OTHER THINGS, THE CONDITIONS UNDER WHICH THESE MOUNTS MAY BE APPLIED, AND/OR THE SURFACE TO WHICH THEY MAY BE APPLIED, ARE BEYOND PANDUIT'S CONTROL.

PANDUIT PART NUMBER	MAXIMUM CABLE DIA. IN [mm]	WEIGHT LBS. (g) /100PCS
LWC100-A	1.0 [25.4]	2.51 [1140]

1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION, FOR PACKAGE SIZE
2. MOUNT IS DESIGNED TO TO SUPPORT 2.25lbs [1020g] MAX WEIGHT ON A CLEAN, SMOOTH, DRY SURFACE.

CAD_FILENAME/LAYERS

PANDUIT

CORP.

TINLEY PARK, ILLINOIS

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:

UNLESS OTHERWISE SPECIFIED,

ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY INS

INS

MAT'L:	
--------	--

DATE _____

NYLON 6/6

	SCALE
--	-------

NONE

DRAWING NO.

GB0329EZ

DWG
A
SIZE

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[LWC100-A-L14](#) [LWC100-A-C](#) [LWC100-A-L](#) [LWC100-A-C14](#) [LWC100-A-L20](#)