

SmartZone™ G5 Rope Fluid Leak Sensor

specifications

The rope fluid leak sensor is designed to provide early detection of fluid in a data center or network closet along the entire length of the sensor cable.

The rope fluid leak sensor extension is designed to lengthen the detection zone of the rope fluid leak sensor. Up to five rope fluid leak sensor extensions can be connected.



SmartZone™ G5 Rope Fluid Leak Sensor

Rope fluid leak sensor: ED001

Rope fluid leak extension cable: EG001

technical information

| | |
|--------------------|--|
| Dimensions: | Sensor: 2.36 x 2.36 inches [60mm x 60mm] |
| | Extension cable: 236.2 inches [6m] |
| | Standard Ethernet extension cable: 141.7 inches [3.6m] |
| Mounting: | Wire mount or adhesive backed mount |

*Mounting hardware included

key features and benefits

| | |
|------------------------------|---|
| Early fluid detection | Detects fluid in a data center or network closet along the entire length of the sensor cable |
| RJ45 Connection | Utilizes a RJ45 jack on the rope fluid leak sensor assembly to a sensor port on the G5 iPDU or sensor hub (EF001) |
| Versatile mounting | Offers versatile mounting options to accommodate easy deployment inside a rack or within a room within a data center or facility building |

applications

The SmartZone™ G5 Rope Fluid Leak Sensor and optional Rope Leak Sensor Extension are designed to provide early detection of fluid in a data center or network closet along the entire length of the sensor cable. Simply connect the RJ-45 jack on the rope fluid leak sensor assembly to a sensor port on the iPDU or sensor hub (EF001). Next thread the sensor cable through the rack and along the desired path of detection. Note: Up to 5 rope fluid leak sensor cables can be connected to lengthen the detection zone. Lastly, secure the sensor cable to the rack and ground using the cable ties and/or adhesive mounting strips provided.


SmartZone™ Rope Fluid Leak Sensor

technical specification

| Electrical | |
|---|--|
| Operational Voltage | 5V DC |
| Measuring Range | Liquids with resistance of < 2M Ohms per cm |
| Physical | |
| Length | From PDU to Sensor box: 1.8m Rope Fluid Leak Sensor Cable: 6m (could be extended to Max. 30m) |
| Environmental | |
| Elevation Above MSL (Operating/Storage) | 0-10000 feet (0-3048m)/0-50000 feet (0-15240 m) |
| Temperature (Operating/Storage) | 0°C~+65°C (32~ 149°F)/-20~ + 70°C (-4 ~ 158°F) |
| Humidity (Operating/Storage) | 0-95% RH, non-condensing (operating) |
| Compliance | |
| Environmental Verification | ROHS, WEEE |


dimensions

Rope Fluid Leak Sensor Assembly




Rope Fluid Leak Sensor Cable


6M in length




Wire Mount




Adhesive Backed Mount



Cable Ties



RJ45 Quick Disconnect Coupler Sold Separately
Panduit Part Number:
CC5E88BL



Standard Ethernet Extension Cable Sold Separately
3.0m length
Panduit
Part Number:
UTP28CH3MBL



Note: The Rope Fluid Leak Sensor is only designed to connect to a G5 iPDU. Connecting it to another device may result in damage.

WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT US/CANADA
Phone: 800.777.3300

PANDUIT EUROPE LTD.
London, UK
cs-emea@panduit.com
Phone: 44.20.8601.7200

PANDUIT SINGAPORE PTE. LTD.
Republic of Singapore
cs-ap@panduit.com
Phone: 65.6305.7575

PANDUIT JAPAN
Tokyo, Japan
cs-japan@panduit.com
Phone: 81.3.6863.6000

PANDUIT LATIN AMERICA
Guadalajara, Mexico
cs-la@panduit.com
Phone: 52.33.3777.6000

PANDUIT AUSTRALIA PTY. LTD.
Victoria, Australia
cs-aus@panduit.com
Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

For more information

Visit us at www.panduit.com

Contact Customer Service by email: cs@panduit.com
or by phone: 800.777.3300

PANDUIT®

©2018 Panduit Corp.
ALL RIGHTS RESERVED.
PUSP55--WW-ENG
1/2018

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[ED001](#) [EG001](#)