

Conforms to OSHA HazCom 2012 & CPR Standards

SAFETY DATA SHEET

Section 1: IDENTIFICATION

1.1 PRODUCT IDENTIFIER

Product Name: Panduit Multi-Tap Connector Series

Product Code: PCSB, PISR, PCSBMT & BLKPSB

1.2 RECOMMENDED USE OF CHEMICAL AND RESTRICTIONS ON USE

Use: Corrosion inhibitor.

1.3 DETAILS OF THE SUPPLIER OF THE SAFETY DATA SHEET

Manufactured for Panduit by: CONTINENTAL PRODUCTS, INC.
#6 Midwest Drive, P.O. Box 338
Pacific, Missouri 63069

Telephone Number: 636-257-4449

1.4 EMERGENCY TELEPHONE NUMBER

Emergency Telephone Number: Infotrac 1-800-535-5053

Section 2: HAZARD(S) IDENTIFICATION

2.1 CLASSIFICATION OF THE CHEMICAL ACCORDING TO OSHA HAZCOM 2012

Hazard class

Not hazardous by OSHA HazCom 2012 criteria.

2.2 LABEL ELEMENTS ACCORDING TO OSHA HAZCOM 2012

Hazard Pictogram: Not applicable.

Signal Word: Not applicable.

Hazard Statement: Not applicable.

Prevention: Not applicable.

Response: Not applicable.

Storage: Not applicable.

Disposal: Not applicable.

2.3 ADDITIONAL INFORMATION

Hazards not otherwise classified: Not applicable.

99 % of the mixture consists of ingredient(s) of unknown acute toxicity.

WHMIS Classification(s):
Not controlled.

Section 3: COMPOSITION/INFORMATION ON INGREDIENTS

3.1 MIXTURES

Ingredient	CAS No	Wt. %
None by WHMIS/OSHA criteria.		

SAFETY DATA SHEET

Section 4: FIRST- AID MEASURES

4.1 DESCRIPTION OF THE FIRST AID MEASURE

Eye:	In case of contact, immediately flush eyes with plenty of water. Remove contact lenses, if worn. If irritation persists, get medical attention.
Skin:	In case of contact, immediately flush skin with plenty of water. Call a physician if irritation develops and persists.
Inhalation:	Not a normal route of exposure. If symptoms develop, remove to fresh air. Get medical attention if condition worsens.
Ingestion:	If swallowed, do NOT induce vomiting unless directed to do so by medical personnel. Never give anything by mouth to an unconscious person. Get medical advice/attention.

4.2 MOST IMPORTANT SYMPTOMS AND EFFECTS, BOTH ACUTE AND DELAYED

Eye:	May cause eye irritation. Symptoms may include discomfort or pain, excess blinking and tear production, with possible redness and swelling.
Skin:	May cause skin irritation. Symptoms may include redness, drying, defatting and cracking of the skin.
Inhalation:	Not a normal route of exposure.
Ingestion:	May be harmful if swallowed. May cause stomach distress, nausea or vomiting.

4.3 INDICATION OF ANY IMMEDIATE MEDICAL ATTENTION AND SPECIAL TREATMENTS NEEDED

Note to Physicians:	Symptoms may not appear immediately.
Specific Treatments:	In case of accident or if you feel unwell, seek medical advice immediately (show the label or SDS where possible).

Section 5: FIRE-FIGHTING MEASURES

5.1 FLAMMABILITY

Flammability:	Not flammable by WHMIS/OSHA criteria.
----------------------	---------------------------------------

5.2 EXTINGUISHING MEDIA

Suitable Extinguishing Media:	Dry chemical, foam, carbon dioxide, water spray.
Unsuitable Extinguishing Media:	Not available.

5.3 SPECIAL HAZARDS ARISING FROM THE CHEMICAL

Products of Combustion:	May include, and are not limited to: oxides of carbon.
Explosion Data:	
Sensitivity to Mechanical Impact:	Not available.
Sensitivity to Static Discharge:	Not available.

5.4 SPECIAL PROTECTIVE EQUIPMENT AND PRECAUTIONS FOR FIRE FIGHTERS

Keep upwind of fire. Wear full fire fighting turn-out gear (full Bunker gear) and respiratory protection (SCBA).

SAFETY DATA SHEET

Section 6: ACCIDENTAL RELEASE MEASURES

6.1 PERSONAL PRECAUTIONS, PROTECTIVE EQUIPMENT AND EMERGENCY PROCEDURES

Use personal protection recommended in Section 8. Isolate the hazard area and deny entry to unnecessary and unprotected personnel.

6.2 METHODS AND MATERIALS FOR CONTAINMENT AND CLEANING - UP

Methods for Containment: Contain and/or absorb spill with inert material (e.g. sand, vermiculite), then place in a suitable container. Do not flush to sewer or allow to enter waterways. Use appropriate Personal Protective Equipment (PPE).

Methods for Cleaning-Up: Scoop up material and place in a disposal container.

Section 7: HANDLING AND STORAGE

7.1 PRECAUTIONS FOR SAFE HANDLING

Handling: Avoid contact with skin and eyes. Do not swallow. Do not breathe gas/fumes/vapor/spray. Handle and open container with care. When using do not eat or drink. (See section 8)

General Hygiene Advice: Launder contaminated clothing before reuse. Wash hands before eating, drinking, or smoking.

7.2 CONDITIONS FOR SAFE STORAGE, INCLUDING ANY INCOMPATIBILITIES

Storage: Keep out of the reach of children. Keep container tightly closed. (See section 10)

Section 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

8.1 CONTROL PARAMETERS

Exposure Guidelines

Occupational Exposure Limits		
Ingredient	OSHA-PEL	ACGIH-TLV
Not applicable.		

8.2 EXPOSURE CONTROLS

Engineering Controls: Use ventilation adequate to keep exposures (airborne levels of dust, fume, vapor, etc.) below recommended exposure limits.

8.3 INDIVIDUAL PROTECTIVE MEASURES

Personal Protective Equipment:

Eye/Face Protection: Safety glasses or goggles are recommended when using product.

Skin Protection:

Hand Protection: Wear chemical resistant gloves.

Body Protection: Wear suitable protective clothing.

Respiratory Protection: None necessary under normal conditions of use. In case of insufficient ventilation, wear suitable respiratory equipment.

SAFETY DATA SHEET

General Health and Safety Measures:

Handle according to established industrial hygiene and safety practices. Do not eat, smoke or drink where material is handled, processed or stored. Wash hands carefully before eating or smoking.

Section 9: PHYSICAL AND CHEMICAL PROPERTIES

9.1 INFORMATION ON BASIC PHYSICAL AND CHEMICAL PROPERTIES

Appearance:	Paste / Thick grease.
Color:	Blue.
Odor:	Not available.
Odor Threshold:	Not available.
Physical State:	Solid.
pH:	Not available.
Melting Point/Freezing Point:	Not available.
Initial Boiling Point and Boiling Range:	Not available.
Flash Point:	Not available.
Evaporation Rate:	Not available.
Flammability:	Not flammable.
Lower Flammability/Explosive Limit:	Not available.
Upper Flammability/Explosive Limit:	Not available.
Vapor Pressure:	Not available.
Vapor Density:	Not available.
Relative Density/Specific Gravity:	Not available.
Solubility:	Not available.
Partition coefficient: n-octanol/water:	Not available.
Auto-ignition Temperature:	Not available.
Decomposition Temperature:	Not available.
Viscosity:	Not available.
Explosive Properties:	Not available.
Oxidizing Properties:	Not available.

Section 10: STABILITY AND REACTIVITY

10.1 REACTIVITY

No dangerous reaction known under conditions of normal use.

10.2 CHEMICAL STABILITY

Stable under normal storage conditions.

10.3 POSSIBILITY OF HAZARDOUS REACTIONS

No dangerous reaction known under conditions of normal use.

SAFETY DATA SHEET

10.4 CONDITIONS TO AVOID

Heat.

10.5 INCOMPATIBLE MATERIALS

None known.

10.6 HAZARDOUS DECOMPOSITION PRODUCTS

May include, and are not limited to: oxides of carbon.

Section 11: TOXICOLOGICAL INFORMATION

11.1 INFORMATION ON TOXICOLOGICAL EFFECTS

Likely Routes of Exposure: Skin contact, eye contact, and ingestion.

Symptoms related to physical/chemical/toxicological characteristics:

Eye: May cause eye irritation. Symptoms may include discomfort or pain, excess blinking and tear production, with possible redness and swelling.

Skin: May cause skin irritation. Symptoms may include redness, drying, defatting and cracking of the skin.

Ingestion: May be harmful if swallowed. May cause stomach distress, nausea or vomiting.

Inhalation: Not a normal route of exposure.

Acute Toxicity:

Ingredient	LC50	LD50
Not applicable.		
Calculated overall Chemical Acute Toxicity Values		
LC50 (inhalation)	LD50 (oral)	LD50 (dermal)
Not available.	Not available.	Not available.
Ingredient		Chemical Listed as Carcinogen or Potential Carcinogen (NTP, IARC, OSHA, ACGIH, CP65)*
Not applicable.		

* See Section 15 for more information.

11.2 DELAYED, IMMEDIATE, AND CHRONIC EFFECTS OF SHORT- AND LONG-TERM EXPOSURE

Skin Corrosion/Irritation: Based on available data, the classification criteria are not met.

Serious Eye Damage/Irritation: Based on available data, the classification criteria are not met.

Respiratory Sensitization: Based on available data, the classification criteria are not met.

Skin Sensitization: Based on available data, the classification criteria are not met.

STOT-Single Exposure: Based on available data, the classification criteria are not met.

Chronic Health Effects:

Carcinogenicity: Based on available data, the classification criteria are not met.

Germ Cell Mutagenicity: Based on available data, the classification criteria are not met.

SAFETY DATA SHEET

Reproductive Toxicity:**Developmental:** Based on available data, the classification criteria are not met.**Teratogenicity:** Based on available data, the classification criteria are not met.**Embryotoxicity:** Based on available data, the classification criteria are not met.**Fertility:** Based on available data, the classification criteria are not met.**STOT-Repeated Exposure:** Based on available data, the classification criteria are not met.**Aspiration Hazard:** Based on available data, the classification criteria are not met.**Toxicologically Synergistic Materials:** Not available.**Other Information:** Not available.

Section 12: ECOLOGICAL INFORMATION

12.1 ECOTOXICITY**Acute/Chronic Toxicity:** May cause long-term adverse effects in the aquatic environment.**12.2 PERSISTENCE AND DEGRADABILITY**

Not available.

12.3 BIOACCUMULATIVE POTENTIAL**Bioaccumulation:** Not available.**12.4 MOBILITY IN SOIL**

Not available.

12.5 OTHER ADVERSE EFFECTS

Not available.

Section 13: DISPOSAL CONSIDERATIONS

13.1 WASTE TREATMENT METHODS**Disposal Method:** This material must be disposed of in accordance with all local, state, provincial, and federal regulations.**Other disposal recommendations:** Not available.

Section 14: TRANSPORT INFORMATION

14.1 UN NUMBER**DOT**

Not regulated.

TDG

Not regulated.

14.2 UN PROPER SHIPPING NAME**DOT**

Not applicable.

TDG

Not applicable.

14.3 TRANSPORT HAZARD CLASS (ES)**DOT**

Not applicable.

TDG

Not applicable.

SAFETY DATA SHEET

14.4 PACKING GROUP

DOT

Not applicable.

TDG

Not applicable.

14.5 ENVIRONMENTAL HAZARDS

Not available.

14.6 TRANSPORT IN BULK ACCORDING TO ANNEX II OF MARPOL 73/78 AND THE IBC CODE

Not available.

14.7 SPECIAL PRECAUTIONS FOR USER

Do not handle until all safety precautions have been read and understood.

Section 15: REGULATORY INFORMATION

15.1 SAFETY, HEALTH AND ENVIRONMENTAL REGULATIONS/ LEGISLATIONS SPECIFIC FOR THE CHEMICAL

Canada: This product has been classified in accordance with the hazard criteria of the Controlled Products Regulations and the SDS contains all the information required by the Controlled Products Regulations.

US: SDS prepared pursuant to the Hazard Communication Standard (CFR29 1910.1200) HazCom 2012

SARA Title III				
Ingredient	Section 302 (EHS) TPQ (lbs.)	Section 304 EHS RQ (lbs.)	CERCLA RQ (lbs.)	Section 313
Not applicable.				

State Regulations

California Proposition 65:

This product does not contain a chemical known to the State of California to cause cancer, birth defects or other reproductive harm.

Global Inventories:

Ingredient	Canada DSL/NDSL	USA TSCA
All ingredients are on DSL/NDSL and TSCA inventories.		

NFPA National Fire Protection Association:

Health:	1
Fire:	1
Reactivity:	0

HMIS-Hazardous Materials Identification System

Health:	1
Fire:	1
Physical Hazard:	0

Hazard Rating: 0 = minimal, 1 = slight, 2 = moderate, 3 = severe, 4 = extreme

SAFETY DATA SHEET

SOURCE AGENCY CARCINOGEN CLASSIFICATIONS:

CP65	California Proposition 65
OSHA (O)	Occupational Safety and Health Administration.
ACGIH (G)	American Conference of Governmental Industrial Hygienists. A1 - Confirmed human carcinogen. A2 - Suspected human carcinogen. A3 - Animal carcinogen. A4 - Not classifiable as a human carcinogen. A5 - Not suspected as a human carcinogen.
IARC (I)	International Agency for Research on Cancer. 1 - The agent (mixture) is carcinogenic to humans. 2A - The agent (mixture) is probably carcinogenic to humans; there is limited evidence of carcinogenicity in humans and sufficient evidence of carcinogenicity in experimental animals. 2B - The agent (mixture) is possibly carcinogenic to humans; there is limited evidence of carcinogenicity in humans in the absence of sufficient evidence of carcinogenicity in experimental animals. 3 - The agent (mixture, exposure circumstance) is not classifiable as to its carcinogenicity to humans. 4 - The agent (mixture, exposure circumstance) is probably not carcinogenic to humans.
NTP (N)	National Toxicology Program. 1 - Known to be carcinogens. 2 - Reasonably anticipated to be carcinogens.

Section 16: OTHER INFORMATION

Date of Preparation: July 11, 2014
Expiry Date: July 11, 2017
Version: 1.0
Revision Date: July 11, 2014

Disclaimer: We believe the statements, technical information and recommendations contained herein are reliable, but they are given without warranty or guarantee of any kind. The information contained in this document applies to this specific material as supplied. It may not be valid for this material if it is used in combination with any other materials. It is the user's responsibility to satisfy oneself as to the suitability and completeness of this information for the user's own particular use.

End of Safety Data Sheet

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[PCSBMT2/0-6-2Y](#) [PCSBMT350-10-1Y](#) [PCSBMT600-4-2Y](#) [PCSBMT600-10-1Y](#) [PCSBMT600-4S-2Y](#) [PCSBMT2/0-4S-3Y](#) [PISR1/0-1](#) [PISR350-1](#) [PCSBMT250-8S-2Y](#) [PISR2-1](#) [PISR500-1](#) [PCSBMT250-4-2Y](#) [PCSBMT600-12-1Y](#) [PCSBMT350-8-2Y](#) [PCSBMT250-4S-2Y](#) [PCSBMT350-6S-2Y](#) [PCSBMT600-6-2Y](#) [PCSBMT250-10-2Y](#) [PCSBMT600-8-2Y](#) [PCSBMT600-8S-2Y](#) [PCSBMT350-4S-2Y](#) [PCSBMT250-8-2Y](#) [PCSBMT250-6S-2Y](#) [PCSBMT2/0-8S-2Y](#) [PCSBMT350-8S-2Y](#) [PCSBMT350-6-2Y](#) [PCSBMT250-12-1Y](#) [PCSBMT350-4-2Y](#) [PCSBMT2/0-6S-2Y](#) [PISR250-1](#) [PCSBMT350-12-1Y](#) [PCSBMT600-6S-2Y](#) [PCSBMT250-6-2Y](#) [PCSBMT2/0-4-3Y](#) [PCSBMT2/0-8-2Y](#) [PCSBMT2/0-10-2Y](#) [PCSBMT2/0-12-1Y](#) [PCSBMT250-10S2Y](#) [PCSBMT250-12S1Y](#) [PCSBMT2/0-12S1Y](#) [PCSBMT350-10S1Y](#) [PCSBMT600-10S1Y](#) [PCSBMT350-12S1Y](#) [PCSBMT600-12S1Y](#) [PCSBMT2/0-10S2Y](#)