





THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

Part Number	Width in. (mm) ±.08 [ 2 ]	Length ft. (m) +1.31 [0.4] -.32 [0.1]	Thickness in. (mm) ±.002 [ 0.05 ]	Type Package Style	Description	Insulation Color
ST1755-075-60BK	.75 (19)	60 (18)	.015 (.38)	Roll Cellophane/Label	Friction Tape ST1755 Black, .75" x 60' x .015"	BLACK

NOTES:

1. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
2. ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS (EUROPEAN DIRECTIVE 2011/65/EU ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.
3. MATERIAL: COTTON BACKING WITH RUBBER ADHESIVE
4. TEMPERATURE RATING: 80°C CONTINUOUS
4. USED FOR GENERAL MECHANICAL STRENGTH APPLICATIONS.
5. COMPLIANT TO CALIFORNIA PROP. 65





TITLE					
Stronghold Friction Tape					
CUSTOMER DRAWING					
ITEM REVISION NAME					
00803EBV/00					
DATASET FILE NAME			MATERIAL:		
00803EBV_DC/00					
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [ mm ]			SEE NOTES		
.x ± .1 [ 2.54 ]      .xxx ± .005 [ .127 ]			DRAWING NUMBER:		
.xx ± .01 [ .25 ]      ANGLES ± 1°					
			00803EBV_DC		
THIRD ANGLE PROJECTION					
DRAWN BY	DATE	CHK	SCALE	SIZE	
JHNU	11/13/2020	MCHD	NONE	A	
SHT 1 OF 1					



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

Part Number	Width in. (mm) ±.08 [ 2 ]	Length ft. (m) +1.31 [0.4] -.32 [0.1]	Thickness in. (mm) ±.002 [ 0.05 ]	Type Package Style	Description	Insulation Color
ST1755-075-60BK	.75 (19)	60 (18)	.015 (.38)	Roll Cellophane/Label	Friction Tape ST1755 Black, .75" x 60' x .015"	BLACK

NOTES:

1. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
2. ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS (EUROPEAN DIRECTIVE 2011/65/EU ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.
3. MATERIAL: COTTON BACKING WITH RUBBER ADHESIVE
4. TEMPERATURE RATING: 80°C CONTINUOUS
4. USED FOR GENERAL MECHANICAL STRENGTH APPLICATIONS.
5. COMPLIANT TO CALIFORNIA PROP. 65



TITLE					
Stronghold Friction Tape					
CUSTOMER DRAWING					
ITEM REVISION NAME					
00803EBV/00					
DATASET FILE NAME			MATERIAL:		
00803EBV_DC/00					
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [ mm ]			SEE NOTES		
.x ± .1 [ 2.54 ]      .xxx ± .005 [ .127 ]			DRAWING NUMBER:		
.xx ± .01 [ .25 ]      ANGLES ± 1°					
			00803EBV_DC		
THIRD ANGLE PROJECTION					
DRAWN BY	DATE	CHK	SCALE	SIZE	
JHNU	11/13/2020	MCHD	NONE	A	
SHT 1 OF 1					

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[ST1755-075-60BK](#)