

Insert label - EMT (62X10)R YE - 0800477

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Insert label, for the Inline modules from Phoenix Contact, Roll, yellow, unlabeled, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: snapped into marker carrier, lettering field size: 62 x 10 mm, Number of individual labels: 500

Your advantages

- ✓ EMT ... insert labels for labeling various marking collars
- ✓ Thanks to their special shape, EMT ... insert labels remain securely inside the collar once inserted
- ✓ Quick and inexpensive marking with THERMOMARK ... roll printers from PHOENIX CONTACT
- ✓ When combined with the right ink ribbon, the marking is highly resistant to solvents and mechanical influences. The marking is even suitable for use under harsh industrial conditions.
- ✓ Marking service: Phoenix Contact can custom-mark all EMT ... markers according to your requirements

RoHS

Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 611060
GTIN	4046356611060

Technical data

Dimensions

Length (b)	10 mm
Width (a)	62 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
Recommended storage conditions	23 °C / 50 % relative humidity

General

Color	yellow
Components	free from silicone and halogen
Material	Polyester
RoHS compliant	Yes

Insert label - EMT (62X10)R YE - 0800477

Technical data

General

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	500
Number of individual labels per row	1
Printability	Thermal transfer
Device	5146477 THERMOMARK ROLL
	5145274 THERMOMARK X1.1
	5146231 THERMOMARK X1.2
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Result of weather resistance test	Test passed
Salt spray test specification	DIN EN ISO 9227:2012-09
Test duration	96 h
Salt spray testing result	Test passed
Alternating condensation climate with SO2 test specification	DIN 50018:2013-05
Climate level	AHT 1.0 S
Cycles	2
Condensation test result	Test passed
Foil strength	175 µm
Marking mounting type	snapped into marker carrier

Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Classifications

eCl@ss

eCl@ss 10.0.1	27400629
eCl@ss 4.0	24190200
eCl@ss 4.1	24190200
eCl@ss 5.0	27149100
eCl@ss 5.1	27141100
eCl@ss 6.0	27149100
eCl@ss 7.0	27149129
eCl@ss 8.0	27149129
eCl@ss 9.0	27400629

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761

Insert label - EMT (62X10)R YE - 0800477

Classifications

ETIM

ETIM 4.0	EC001694
ETIM 5.0	EC001288
ETIM 6.0	EC001288
ETIM 7.0	EC001288

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131504
UNSPSC 18.0	39131504
UNSPSC 19.0	39131504
UNSPSC 20.0	39131504
UNSPSC 21.0	39131504

Accessories

Accessories

Ink ribbon

Ink ribbon - THERMOMARK-RIBBON 110-WMTB HF - 5148007



Ink ribbon, for roll printer for printing product groups WMTB HF..., WMS-2 HF..., TMT..., and EMT..., width: 110 mm, color: black

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

0800477