


Technical drawing of a 1/2-18 UNF-2B x 3.16 inch hex bolt. The drawing shows the bolt with its hexagonal head and threaded shank. Dimensions are provided in inches and millimeters:

- Overall length: 3.16 (80.3)
- Head diameter: 0.50 REF (12.7)
- Head height: 1.00 (25.4)
- Head width across flats: 0.69 REF (17.5)
- Thread specification: 1/2-18 UNF-2B
- Thread length: 0.69 REF (17.5)
- Shank diameter: .31 (7.8) DIA. THRU C'BORE
- Shank length: .11 (2.8) DP.
- Head diameter: .14 (3.5) DIA.




ADHESIVE TAPE: PRESSURE SENSITIVE FOAM
0.040 (1.02) THICK WITH RUBBER ADHESIVE
AND PROTECTIVE LINER. MOUNT IS DESIGNED
TO SUPPORT 0.62 lbs. (281g) MAXIMUM
WEIGHT ON A CLEAN, DRY, SMOOTH, GREASE-FREE
SURFACE.

1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PART COLOR.
2. TO APPLY MOUNT: a) REMOVE PROTECTIVE LINER; b) PLACE IN DESIRED LOCATION; c) APPLY PRESSURE TO TOP OF MOUNT.

PANDUIT PART No.	REC'M. SCREW FASTENER	WEIGHT lbs. (g)/100PCS.
FCM1.2-A	N/A	0.96 (436)
FCM1.2-S6	#6(M3) FL.HD. OR BUTTON HD.	0.91 (413)

NO WARRANTY, EXPRESSED OR IMPLIED, IS MADE BY PANDUIT WITH RESPECT TO ADHESIVE BOND PERFORMANCE. AMONG OTHER THINGS, THE CONDITIONS UNDER WHICH THESE MOUNTS MAY BE APPLIED AND/OR THE SURFACE TO WHICH THEY MAY BE APPLIED ARE BEYOND PANDUIT'S CONTROL.



												PANDUIT CORP.	TINLEY PARK, ILLINOIS
												1.2 INCH FLAT CABLE MOUNT FCM1.2	
												UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± NA (.XXX) ± NA (.XX) ± 0.020(.5) ANGLES ± NA	UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.
R	6/22/01	LGG		INITIAL RELEASE REPLACED SS-19058	GB02391F	R				DRAWN BY LGG	MAT'L:	SCALE FULL	
										DATE 6/22/01	NYLON 6/6	DRAWING NO. GB02391F	DWG A
REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP		CHK'D				SIZ

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[FCM1.2-A-C14](#) [FCM1.2-A-T14](#) [FCM1.2-S6-T14](#)