





PANDUIT PART NO. *	BUNDLE DIA.		A	B	C	D	E	F	MIN. LOOP TENSILE lbs. (N)	CROSS SECTION	TIP STYLE	WEIGHT lbs./100 pcs. (g)
	MIN. in (mm)	MAX. in (mm)										
PLT3I	.06 (1.5)	3.00 (76)	.052 (1.3)	.145 (3.7)	.220 (5.6)	.180 (4.6)	.260 (6.6)	11.4 (290)	40 (178)	INTERMEDIATE	CURVED	.32 (145)
PLT4I	.06 (1.5)	4.00 (102)	.052 (1.3)	.145 (3.7)	.220 (5.6)	.180 (4.6)	.260 (6.6)	14.5 (368)	40 (178)	INTERMEDIATE	CURVED	.40 (181)
PLT1S	.06 (1.5)	1.00 (25)	.052 (1.3)	.190 (4.8)	.262 (6.7)	.220 (5.6)	.316 (8.0)	4.8 (122)	50 (222)	STANDARD	CURVED	.13 (58)
PLT1.5S	.06 (1.5)	1.50 (38)	.052 (1.3)	.190 (4.8)	.262 (6.7)	.220 (5.6)	.316 (8.0)	6.2 (157)	50 (222)	STANDARD	CURVED	.26 (118)
PLT2S	.06 (1.5)	1.88 (47.8)	.052 (1.3)	.190 (4.8)	.262 (6.7)	.220 (5.6)	.316 (8.0)	7.4 (188)	50 (222)	STANDARD	CURVED	.29 (132)
PLT2.5S	.06 (1.5)	2.50 (63.5)	.052 (1.3)	.190 (4.8)	.265 (6.7)	.220 (5.6)	.337 (8.6)	9.8 (249)	50 (222)	STANDARD	CURVED	.38 (173)
PLT3S	.06 (1.5)	3.00 (76)	.052 (1.3)	.190 (4.8)	.265 (6.7)	.220 (5.6)	.337 (8.6)	11.5 (292)	50 (222)	STANDARD	CURVED	.45 (204)

NOTES:

*SEE www.panduit.com FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE, PART MATERIAL, PART COLOR AND ANY THIRD PARTY RECOGNITION OR COMPLIANCE.

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS

							TITLE					
							PAN-TY CABLE TIES - PLT SERIES					
							CUSTOMER DRAWING					
							ITEM REVISION NAME		W10001CB/32			
							DATASET FILE NAME		W10001CB/32 SS-5540 SH2-REV32			
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]					
							.X ± - - - .XXX ± .020 [.51] .XX ± .02 [.5] ANGLES ± - - -					
32	10/01/15	BWG	MPH	JADE	REVISED NOTES.		SS-5540/32		 - 		MATERIAL:	
31	8/13/13	BWG	KJM	RTFI	CORRECTED REV NO. REMOVED NOTE 1. SEE ECN FOR DETAILS.		SS-5540/30		THIRD ANGLE PROJECTION		NYLON 6.6	
									DRAWING NUMBER:			
									SS-5540 SHEET 2			
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 1	SIZE
							CEW	12-27-84	HVP	NONE		A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[PLT4I-M](#) [PLT4I-M0](#) [PLT2S-C30](#) [PLT2S-M0](#) [PLT3I-M](#) [PLT3I-C](#) [PLT3I-M3](#) [PLT3I-C0](#) [PLT3I-M0](#) [PLT3S-C](#) [PLT1S-C](#) [PLT1S-M](#) [PLT1S-C0](#) [PLT1S-M0](#) [PLT3I-M8](#) [PLT3S-M0](#) [PLT1.5S-M](#) [PLT2.5S-M](#) [PLT1.5S-M0](#) [PLT2.5S-M0](#) [PLT1.5S-C](#) [PLT1.5S-C0](#) [PLT1.5S-M30](#) [PLT1S-M30](#) [PLT1S-M38](#) [PLT2.5S-C](#) [PLT2.5S-C0](#) [PLT2.5S-M30](#) [PLT2S-C](#) [PLT2S-C0](#) [PLT2S-C1](#) [PLT2S-C10](#) [PLT2S-C2](#) [PLT2S-C20](#) [PLT2S-C3](#) [PLT2S-C4Y](#) [PLT2S-C5](#) [PLT2S-C6](#) [PLT2S-C7](#) [PLT2S-C702Y](#) [PLT2S-C8](#) [PLT2S-MP](#) [PLT2S-M00](#) [PLT2S-M2](#) [PLT2S-M20](#) [PLT2S-M38](#) [PLT2S-M39](#) [PLT2S-M60](#) [PLT3I-M30](#) [PLT3S-C0](#) [PLT3S-C00](#) [PLT3S-C30](#) [PLT3S-M00](#) [PLT3S-M20](#) [PLT3S-M30](#) [PLT3S-M7](#) [PLT4I-C](#) [PLT4I-C0](#) [PLT4I-M20](#) [PLT4I-M30](#) [PLT4I-M5](#) [PLT2S-CO](#) [PLT2S-M3](#) [PLT3I-M20](#) [PLT2S-M7](#) [PLT3I-M10](#) [PLT3S-M8](#) [PLT3S-M10](#) [PLT3S-M2](#) [PLT3I-M14](#) [PLT3S-C20](#) [PLT4I-M14](#) [PLT2S-M6](#) [PLT2S-M1](#) [PLT3S-M6](#) [PLT3I-M4Y](#) [PLT4I-C14](#) [PLT3S-M3](#) [PLT2S-M5](#) [PLT2S-M209](#) [PLT3I-C14](#) [PLT3I-M5](#) [PLT3I-M2](#) [PLT3I-M6](#) [PLT2S-C14](#) [PLT4I-M6](#) [PLT2S-M4Y](#) [PLT3S-C2](#) [PLT3S-M209](#) [PLT2S-MP0](#) [PLT3S-M4Y](#) [PLT2S-C00](#) [PLT3S-M5](#) [PLT3S-M1](#) [PLT2S-M8](#) [PLT2S-M10](#) [PLT4I-M2](#) [PLT3S-M300](#)