


Conductor marker - UCT-WMT (30X4) BU - 0801428

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Conductor marker, Sheet, blue, unlabeled, can be labeled with: TOPMARK NEO, TOPMARK LASER, BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: insert, cable diameter range: 1.5 ... 14 mm, lettering field size: 30 x 4 mm, Number of individual labels: 30



Key Commercial Data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	
GTIN	4046356677042

Technical data

Dimensions

Length (b)	4 mm
Width (a)	30 mm
Cable diameter	1.5 mm ... 14 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.

General

Color	blue
Components	free from silicone and halogen
Flammability rating according to UL 94	V0
Material	PC V0
RoHS compliant	Yes
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	30
Number of individual labels per row	10

Conductor marker - UCT-WMT (30X4) BU - 0801428

Technical data

General

Printability	Thermal transfer
	Inkjet printing
Device	5146464 THERMOMARK CARD
	5147888 BLUEMARK LED
	5147999 BLUEMARK CLED
Ink ribbon	0801734 THERMOMARK CARD-UCT-MAG7
	0801371 THERMOMARK-RIBBON 110-TC
	5147421 BLUEMARK FLUID-CARTRIDGE
	5146662 BLUEMARK CLED-FLUID-CARTR.
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Result of weather resistance test	Test passed
Salt spray test specification	DIN EN 60068-2-11:2000-02
Test duration	96 h
Salt spray testing result	Test passed
Wipe resistance of test specification inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
Result of wipe resistance test	Test passed
Marking mounting type	insert
Result	Test passed
Oxygen index (DIN EN ISO 4589-2)	32.4 %
R22	HL 1 - HL 3
R23	HL 1 - HL 3
R24	HL 1 - HL 3

Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Flammability rating according to UL 94	V0

Classifications

eCl@ss

eCl@ss 10.0.1	27400629
eCl@ss 4.0	27061700
eCl@ss 4.1	27061700
eCl@ss 5.0	27400400
eCl@ss 5.1	27400400
eCl@ss 6.0	27400400
eCl@ss 7.0	27400401
eCl@ss 8.0	27400401

Conductor marker - UCT-WMT (30X4) BU - 0801428

Classifications

eCl@ss

eCl@ss 9.0	27400629
------------	----------

ETIM

ETIM 3.0	EC000761
ETIM 4.0	EC001530
ETIM 5.0	EC001530
ETIM 6.0	EC001288
ETIM 7.0	EC001288

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131504
UNSPSC 18.0	39131504
UNSPSC 19.0	39131504
UNSPSC 20.0	39131504
UNSPSC 21.0	39131504

Accessories

Accessories

Magazine

Magazine - THERMOMARK CARD-UCT-MAG7 - 0801734



Magazine for the THERMOMARK CARD printer, for accommodating UCT sheets (UCT-WMT...)

Magazine - TMP-UCT-MAG7 - 0803349



Magazine, for the THERMOMARK PRIME and the THERMOMARK CARD, for accommodating UCT-WMT..., UCT-EM (7x10)

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

0801428