


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


PANDUIT PART #	TAB SIZE in. [mm]	WIRE RANGE		COLOR	DIMENSIONS in. [mm]				TOOL CHART	
		ENGLISH AWG	METRIC mm ²		MAX. WIRE INSULATION DIAMETER	L ± .03 [0,8]	W ± .01 [0,3]	H ± .01 [0,3]	PRESSES: CP-861, CP-862, CP-871	
									APPLICATOR DIES: CA9, CA-800EZ	
DNF18250FIBX	.250 X .032 [6,3 X 0,8]	22-18	0,5-1,0	RED	.21 [5,4]	.93 [23,6]	.35 [8,9]	.22 [5,5]	CD-800-6 CD9-6B	
DNF18205FIBX	.205/.187 X .032 [5,2/4,8 X 0,8]					.87 [22,1]	.31 [7,9]	.22 [5,5]		
DNF18206FIBX	.205/.187 X .020 [5,2/4,8 X 0,5]					.87 [22,1]	.31 [7,9]	.22 [5,5]		
DNF14250FIBX	.250 X .032 [6,3 X 0,8]	16-14	1,5-2,5	BLUE	.24 [6,1]	.93 [23,6]	.35 [8,9]	.22 [5,5]	CD-800-8 CD9-8B	
DNF14205FIBX	.205/.187 X .032 [5,2/4,8 X 0,8]					.87 [22,1]	.31 [7,9]	.22 [5,5]		
DNF14206FIBX	.205/.187 X .020 [5,2/4,8 X 0,5]					.87 [22,1]	.31 [7,9]	.22 [5,5]		

NOTES:

1. USED FOR:
 - A. STRANDED COPPER WIRE ONLY
 - B. 221°F [105°C] MAX. OPERATING TEMPERATURE
 - C. 600V. MAX. BLDG WIRE
 - D. 6-12 LBS INTIAL INSERTION/WITHDRAWAL FORCE
2. MATERIAL:
 - A. STAMPING: CDA 260 BRASS, TIN PLATED
 - B. HOUSING: TYPE 66 NYLON
3. WIRE STRIP LENGTH: $9/32'' \begin{smallmatrix} +1/32 \\ -0 \end{smallmatrix} [7,1 \begin{smallmatrix} +0,8 \\ -0 \end{smallmatrix}]$
4. SEE www.panduit.com FOR PACKAGE QUANTITIES INDICATED BY PART NUMBER SUFFIX
5. DIMENSIONS IN BRACKETS ARE METRIC EQUIVALENT
6. COLORS ARE TRANSLUCENT



LISTED CERTIFIED
20H3 LR31212
E78522

TITLE		FEMALE DISCONNECTS, NYLON FULLY INSULATED - EXPANDED WIRE ENTRY			
ITEM REVISION NAME		CUSTOMER DRAWING			
N41167BA/05					
DATASET FILE NAME					
N41167BA_DC/05A		MATERIAL:			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± .1 [2.54] .xxx ± .005 [.127] .xx ± .01 [.25] ANGLES ± 5 °		SEE NOTES			
		DRAWING NUMBER:			
THIRD ANGLE PROJECTION		A41167			
DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 1	SIZE
DSM	-	-	N.T.S.		A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[DNF14205FIBX-2K](#) [DNF14250FIBX-2K](#) [DNF18250FIBX-2K](#) [DNF14206FIBX-2K](#) [DNF18205FIBX-2K](#)
[DNF18206FIBX-2K](#)