

A.  
System  
Overview

B1.  
Cable Ties

B2.  
Cable  
Accessories

B3.  
Stainless  
Steel Ties

C1.  
Wiring  
Duct

C2.  
Surface  
Raceway

C3.  
Abrasion  
Protection

C4.  
Cable  
Management

D1.  
Terminals

D2.  
Power  
Connectors

D3.  
Grounding  
Connectors

E1.  
Labeling  
Systems

E2.  
Labels

E3.  
Pre-Printed  
& Write-On  
Markers

E4.  
Permanent  
Identification

E5.  
Lockout/  
Tagout  
& Safety  
Solutions

F.  
Index

## BT2HT Hand Operated Installation Tool for Strapping

- Strap side entry
- Multi-position rear handle provides flexibility for a one or two hand installation
- Adjustable tension control
- Easy removal of excess strap
- Installs (3) sizes: 0.38 inch (9.5mm), 0.50 inch (12.7mm), and 0.63 inch (15.9mm)
- Replacement cutter blade and handle available



| Part Number     | Part Description   | Std. Pkg. Qty. |
|-----------------|--|----------------|
| <b>BT2HT</b>    | Installation tool for use with 0.38" (9.5mm), 0.50" (12.7mm), and 0.63" (15.9mm) widths of Panduit® Pan-Steel® Strapping. Tensions, cuts strapping, and secures the buckle tab. Lever cut off. | 1              |
| <b>KRT2BLD</b>  | Replacement cutter blade for RT2HT and BT2HT.  | 1              |
| <b>KRT2HNDL</b> | Replacement Cutter Handle for RT2HT and BT2HT  | 1              |

**NEW!**

## BT75SDT Hand Operated Installation Tool for MS75 Strapping

- Screw drive tension mechanism provides high tension with minimal effort, reducing operator fatigue
- Heavy duty construction offers a longer service life
- Strapping side entry allows quick side entry of the strap into tool to speed installation



| Part Number    | Part Description   | Std. Pkg. Qty. |
|----------------|--|----------------|
| <b>BT75SDT</b> | Installation tool for use with 0.75" (19.1mm) width strapping only. Tensions and cuts strapping. Screwdriver required for buckle closure (not included). | 1              |

## PCS Cushion Sleeve

- Black neoprene sleeving used with Pan-Steel® Stainless Steel Ties, custom length banding, and MS strap
- Used on applications requiring improved gripping on non-resilient objects
- Can be used indoors or outdoors (excellent ultraviolet resistance, good resistance to petroleum, and many chemicals)
- Isolation between dissimilar metals allows the ties and straps to be used with aluminum cable tray
- Provides full separation between the ties and the bundle
- Operating temperature range -40°F (-40°C) to 200°F (93°C)




| Part Number        | Used with Pan-Steel® Ties/Strapping | Width |      | Length |      | Std. Pkg. Qty† |
|--------------------|-------------------------------------|-------|------|--------|------|----------------|
|                    |                                     | In.   | mm   | Ft.    | m    |                |
| <b>PCSS-B-CR</b>   | MLT/S                               | .33   | 8.4  | 100    | 30.5 | 1              |
| <b>PCSH-B-CR</b>   | MLT/LH/H                            | .47   | 11.9 | 100    | 30.5 | 1              |
| <b>PCSSH-B-CR*</b> | MLT/EH/SH and MS Straps             | .91   | 23.1 | 100    | 30.5 | 1              |

\*Meets MIL-R-6855

†Order in number of reels required.

Pkg. -CR = 100 ft. (30.5m) reel.



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[PCSS-B-CR](#) [PCSH-B-CR](#)