

2



1


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
UICFPHSE2**	.67 LB/10 PCS (306.0 g/10 PCS)

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. DIMENSIONS IN PARENTHESES ARE IN METRIC.
4. PART INCLUDES:
 - 1- FACEPLATE
 - 1- CLEAR SCREW COVER
 - 1- COLOR COORDINATED SCREW COVER
 - 1- CLEAR LABEL COVER
 - 2- MOUNTING SCREW



PART NUMBER		UICFPHSE2**	
TITLE		MINI-COM ULTIMATE ID 2 POSITION HORIZONTAL SLOPED EXECUTIVE SERIES FACEPLATE CUSTOMER DRAWING	
ITEM REVISION NAME		M01288BE/07	
DATASET FILE NAME		M01288BE_DC/07A	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .X ± .XX ± .03 [.8] .XXX ± .010 [.3] ANGLES ±		 THIRD ANGLE PROJECTION	
MATERIAL:		ABS	DRAWING NUMBER: 01288-09
DRAWN BY		JSP	
DATE		7-24-02	SHT 1 OF 1
CHK		JAJP	
SCALE		NONE	SIZE A
REV		1	

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
1	5-14-14	BJN	JSP	MMR	REVISED & REDRAWN PREVIOUS REVISIONS REMVD FOR CLARITY	01288-09

2

1

D10100DA/14

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[UICFPHSE2IW](#) [UICFPHSE2WH](#) [UICFPHSE2EI](#)