

NOTES:

1. MATERIAL:  
BODY - ALUMINUM, TIN PLATED  
SCREW - ALUMINUM, TIN PLATED
2. UL LISTED & CSA CERTIFIED FOR USE UP TO 600V &  
TEMPERATURE RATED 90°C (AL9CU)
3. DUAL RATED FOR USE WITH COPPER OR ALUMINUM  
STRANDED CODE CONDUCTOR
4. THESE PARTS ARE RoHS COMPLIANT
5. USE OF OXIDE INHIBITING JOINT COMPOUND LIKE  
PANDUIT CMP-100 RECOMMENDED FOR PAD TO PAD  
AND CONDUCTOR SURFACES
6. SEE PACKAGING LABEL FOR TIGHTENING TORQUE  
INFORMATION
7. PKG QTY:  
3 = 3



\* HEX SIZE MAY DIFFER FROM CHART. DIFFERENCE IN SIZE WILL NOT AFFECT FIT, FORM, OR FUNCTION OF PART

							TITLE
							LAM2SA SERIES ALUMINUM MECHANICAL LUGS CUSTOMER DRAWING
							ITEM REVISION NAME N41360BB-C41360/04
							DATASET FILE NAME C41360/04.SLDDRW
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .X ± .XXX ± .XX ± ANGLES ±
							MATERIAL SEE NOTES
							DRAWING NUMBER C41360_04
04	2/13	JHNU	JHNU	RGB	REVISED TITLE BLOCK	N41360BB-C41360	THIRD ANGLE PROJECTION
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY CJW DATE 12/02 CHK SCALE NONE SHEET 1 OF 1 SIZE B

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[LAM2SA300-56-3](#) [LAM2SA300-38-3](#)