

Marker for terminal blocks - TMT 6 R - 0816498

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Marker for terminal blocks, Roll, white, unlabeled, can be labeled with: THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMaster 300/600, THERMOMARK X1.2, THERMOMARK S1.1, perforated, mounting type: snap into universal marker groove, snap into flat marker groove, for terminal block width: 6.2 mm, lettering field size: 6.35 x 6.15 mm, Number of individual labels: 16000

Your advantages

- ✓ The TMT labeling range includes markers for all products with tall and flat marker grooves
- ✓ The perforated marking strips are easy to separate and can be easily fitted using the tool supplied
- ✓ Quick and inexpensive marking with THERMOMARK ... roll printers from PHOENIX CONTACT
- ✓ When combined with the right ink ribbon, the marking is highly resistant to solvents and mechanical influences. The marking is even suitable for use under harsh industrial conditions.
- ✓ Labeling service: Phoenix Contact can custom-label all TMT ... markers in accordance with your requirements
- ✓ Labeling service: Phoenix Contact can custom-label all TMT markers according to your requirements



Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 107259
GTIN	4046356107259

Technical data

Dimensions

Length (b)	6.35 mm
Width (a)	6.15 mm
Height (c)	6.4 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
Recommended storage conditions	23 °C / 50 % relative humidity

General

Color	white
Base element material	Polyester foil

Marker for terminal blocks - TMT 6 R - 0816498

Technical data

General

Type	flat
Components	free from silicone and halogen
Material	Polyester
RoHS compliant	Yes
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	16000
Number of individual labels per row	16
Printability	Thermal transfer
Device	5146477 THERMOMARK ROLL
	5146231 THERMOMARK X1.2
Ink ribbon	5145384 THERMOMARK-RIBBON 110
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Result of weather resistance test	Test passed
Salt spray test specification	DIN EN 60068-2-11:2000-02
Test duration	96 h
Salt spray testing result	Test passed
Alternating condensation climate with SO2 test specification	DIN 50018:2013-05
Climate level	AHT 1.0 S
Cycles	2
Condensation test result	Test passed
Wipe resistance of test specification inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
Result of wipe resistance test	Test passed
Foil strength	175 µm
Marking mounting type	snap into universal marker groove

Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Classifications

eCl@ss

eCl@ss 10.0.1	27141137
eCl@ss 4.0	24190200
eCl@ss 4.1	24190200
eCl@ss 5.0	27141100
eCl@ss 5.1	27141100
eCl@ss 6.0	27141100
eCl@ss 7.0	27141137

Marker for terminal blocks - TMT 6 R - 0816498

Classifications

eCl@ss

eCl@ss 8.0	27141137
eCl@ss 9.0	27141137

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761
ETIM 6.0	EC000761
ETIM 7.0	EC000761

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131505
UNSPSC 18.0	39131505
UNSPSC 19.0	39131505
UNSPSC 20.0	39131505
UNSPSC 21.0	39131505

Accessories

Accessories

Ink ribbon

Ink ribbon - THERMOMARK-RIBBON 110-WMTB HF - 5148007



Ink ribbon, for roll printer for printing product groups WMTB HF..., WMS-2 HF..., TMT..., and EMT..., width: 110 mm, color: black

Mounting material

Locking tool - TMT TOOL - 0816650



Locking tool, Roll, orange, mounting type: snap into universal marker groove, snap into flat marker groove

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

0816498