


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NO	PACKAGE QTY	MTRT MAX BUNDLE DIAMETER	PTRT MAX BUNDLE DIAMETER	"L" LENGTH ±.3" [ 7 ]
MRT1.5DS-C4	100	1.5" [ 38 ]	1.9" [ 48 ]	15.4" [ 391 ]
MRT2.5DS-C4	100	2.5" [ 63 ]	2.9" [ 73 ]	21.7" [ 551 ]



NOTES:

1. APPLICATION TOOLS: PTRT, MTRTLS OR MTRTH (WITH KMTRTLS KIT)
2. MINIMUM LOOP TENSILE STRENGTH:  
250 lbs [ 1112 NEWTONS ] WHEN TESTED ON A 1.5" MANDREL
3. BRACKETS [ ] DENOTE DIMENSIONS IN MILLIMETERS, AND  
ARE SHOWN FOR REFERENCE ONLY
4. TOLERANCES:  
.XXX = ±.010 [ .25 ]    .XX = ±.02 [ .5 ]  
.X = ±.03 [ .8 ]    ANGLES = ±2°
5. MATERIAL: 304 STAINLESS STEEL

					TITLE		METAL TIE - STANDARD SERIES DOUBLE LOOP - RETAINED TENSION	
					CUSTOMER DRAWING		<b>PANDUIT</b>	
					ITEM REVISION NAME		N41247BS/09	
					DATASET FILE NAME		N41247BS_DC/09A	
					UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [ mm ]		MATERIAL:	
					.x ± .1 [ 2.54 ]    .xxx ± .005 [ .127 ] .xx ± .01 [ .25 ]    ANGLES ± 5 °		304 STAINLESS STEEL	
					THIRD ANGLE PROJECTION		DRAWING NUMBER:	
							N41247BS_DC	
REV	DATE	BY	CHK	APR	DESCRIPTION		ECN	
09A	4/13	JAMB	MIM	RGRO	UPDATE DRAWING TO NEW GLOBAL PANDUIT TITLE BLOCK WITH PANDUIT LOGO		SSECN01056	
08A	3/12	MIM	RGRO	---	NOTE #3 METRIC DIMENSIONS NOTED AS BEING SHOWN FOR REFERENCE ONLY		-----	
					DRAWN BY		DATE	
					JAMB			
					CHK		SCALE	
					EJD		2:1	
					SHT 1 OF 1		SIZE	
							A	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[MRT1.5DS-C4](#) [MRT2.5DS-C4](#)