

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

| PANDUIT<br>PART # | STUD SIZE |        | DIMENSIONS in. [ mm ]  |                        |                        |                        |                        |
|-------------------|-----------|--------|------------------------|------------------------|------------------------|------------------------|------------------------|
|                   | ENGLISH   | METRIC | $L \pm .03$<br>[ 0,8 ] | $W \pm .01$<br>[ 0,3 ] | $C \pm .02$<br>[ 0,5 ] | $M \pm .03$<br>[ 0,8 ] | $H \pm .01$<br>[ 0,3 ] |
| E14-6FB           | #6        | M3     | .63<br>[ 16,00 ]       | .28<br>[ 7,11 ]        | .20<br>[ 5,08 ]        | .49<br>[ 12,45 ]       | .15<br>[ 3,81 ]        |
| E14-8FB           | #8        | M4     | .69<br>[ 17,53 ]       | .31<br>[ 7,87 ]        | .23<br>[ 5,84 ]        | .53<br>[ 13,46 ]       | .17<br>[ 4,32 ]        |
| E14-10FB          | #10       | M5     | .71<br>[ 18,03 ]       | .34<br>[ 8,64 ]        | .25<br>[ 6,35 ]        | .55<br>[ 13,97 ]       | .20<br>[ 5,08 ]        |

## UL &amp; CSA TOOLS


CT-100A  
CT-200  
CT-600-A (CT-570CH)  
CT-1570  
CT-2500 (CT-2570CH)

## PANDUIT APPROVED TOOLS

CT-160  
CT-260

## NOTES:

- UL LISTED & CSA CERTIFIED FOR:
  - #16-14 AWG [ 1,5-2,5 mm<sup>2</sup> ] SOLID OR STRANDED COPPER WIRE
  - 302°F [ 150°C ] MAX OPERATING TEMPERATURE
  - 2000 VOLTS MAX
- MATERIAL:
  - STAMPING: .032" [ 0,8 ] THK COPPER, TIN PLATED
- WIRE STRIP LENGTH: 9/32"  $\begin{smallmatrix} +1/32 \\ -0 \end{smallmatrix}$  [ 7,1mm  $\begin{smallmatrix} +0,8 \\ -0 \end{smallmatrix}$  ]
- SEE WWW.PANDUIT.COM FOR PACKAGE QUANTITIES
- DIMENSIONS IN BRACKETS ARE METRIC EQUIVALENT



|                                                                      |  |                            |            |
|----------------------------------------------------------------------|--|----------------------------|------------|
| TITLE                                                                |  |                            |            |
| STRONGHOLD FORK TERMINAL<br>NON-INSULATED, BUTTED SEAM #16-14 AWG    |  |                            |            |
| CUSTOMER DRAWING                                                     |  |                            |            |
| ITEM REVISION NAME                                                   |  | 00123SHL/00                |            |
| DATASET FILE NAME                                                    |  | 00123SHL_DC/00             |            |
| UNLESS OTHERWISE SPECIFIED,<br>DIMENSIONAL TOLERANCES ARE: IN [ mm ] |  | MATERIAL:                  |            |
| .X ±<br>.XX ±                                                        |  | .XXX ±<br>ANGLES ±         |            |
| THIRD ANGLE<br>PROJECTION                                            |  | SEE NOTES                  |            |
| DRAWN BY<br>JHNU                                                     |  | DATE<br>2/18               | CHK<br>TMR |
| SCALE<br>NTS                                                         |  | DRAWING NUMBER:<br>SH41255 |            |
| SHEET 1 OF 1                                                         |  | SIZE<br>A                  |            |

| 00  | 2/18 | JHNU | TMR | RGB | RELEASED    | 00123SH |
|-----|------|------|-----|-----|-------------|---------|
| REV | DATE | BY   | CHK | APR | DESCRIPTION | ECN     |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[E14-10FB-L](#) [E14-6FB-L](#) [E14-8FB-L](#) [E14-10FB-Q](#) [E14-6FB-Q](#) [E14-8FB-Q](#)