

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER	STUD SIZE	DIMENSIONS - in.					TOOLS
		L ± .03	W ± .01	C ± .02	M ± .03	H ± .01	
EV14-6LFB	#6	.90 (22.86)	.25 (6.35)	.22 (5.59)	.68 (17.27)	.14 (3.56)	*CT-100A CT-600-A (CT-500CH) CT-600-A (CT-550CH) CT-1550 CT-1551 CT-2500 (CT-2550CH)
EV14-8LFB	#8	.97 (24.64)	.29 (7.37)	.25 (6.35)	.73 (18.54)	.16 (4.06)	
EV14-10LFB	#10	.97 (24.64)	.33 (8.38)	.25 (6.35)	.73 (18.54)	.19 (4.83)	

*CT-100A, 167°F (75°C) MAX TEMP. RATING

NOTES:


- UL LISTED AND CSA CERTIFIED FOR:
 - #16-14 AWG SOLID OR STRANDED COPPER WIRE
 - 221°F (105°C) MAX TEMP. RATING
 - 600V MAX. BLDG WIRE
(1000 V MAX. IN SIGNS, FIXTURES & LUMINARIES)

- MATERIAL:
 - STAMPING - .032" THK, COPPER
TIN PLATED
 - HOUSING - VINYL, BLUE
 - SLEEVE - BRASS, TIN PLATED

3. WIRE STRIP LENGTH: 5/16" $\begin{smallmatrix} +1/32 \\ -0 \end{smallmatrix}$ [7,9mm $\begin{smallmatrix} +0,8 \\ -0 \end{smallmatrix}$]

4. SEE WWW.PANDUIT.COM FOR PACKAGE QUANTITIES

5. DIMENSIONS IN BRACKETS ARE IN MILLIMETERS



00	2/18	JHNU	TMR	RGB	RELEASED		00123SH
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	

TITLE		STRONGHOLD LOCKING FORK TERMINAL VINYL INSULATED, BUTTED SEAM #16-14 AWG	
ITEM REVISION NAME		CUSTOMER DRAWING	
DATASET FILE NAME		00123SHU/00	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		MATERIAL:	
.X ± .XX ±		.XXX ± ANGLES ±	
THIRD ANGLE PROJECTION		SEE NOTES	
DRAWN BY		DRAWING NUMBER:	
JHNU		SH41296	
DATE		SHT 1 OF 1	
2/18		A	
CHK		SCALE	
TMR		NONE	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[EV14-8LFB-Q](#) [EV14-10LFB-Q](#) [EV14-10LFB-L](#) [EV14-6LFB-L](#) [EV14-8LFB-L](#) [EV14-6LFB-Q](#)