

Label - EML (26,5X26,5)R SR - 0816919

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Label, Roll, silver/matt, unlabeled, can be labeled with: THERMOMARK ROLLMaster 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: adhesive, lettering field size: 26.5 x 26.5 mm, Number of individual labels: 1000

Your advantages

- ✓ The EML ... self-adhesive device markers are particularly well suited for marking various types of equipment in control, system, and control cabinet manufacturing.
- ✓ A wide range of marker sizes and colors are available for custom designs
- ✓ When combined with the right ink ribbon, the marking is highly resistant to solvents and mechanical influences. The marking is even suitable for use under harsh industrial conditions.
- ✓ The EML ... materials are UL-listed
- ✓ Labeling service: Phoenix Contact can custom-label all EM ... markers in accordance with your requirements

RoHS

Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 107839
GTIN	4046356107839

Technical data

Dimensions

Length (b)	26.5 mm
Width (a)	26.5 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 150 °C
Ambient temperature (assembly)	> 5 °C
Recommended storage conditions	22 °C / 50 % relative humidity

General

Color	silver/matt
Components	free from silicone and halogen

Label - EML (26,5X26,5)R SR - 0816919

Technical data

General

Material	Polyester
	Polyester
RoHS compliant	Yes
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	1000
Number of individual labels per row	3
Adhesive	Acrylic
Printability	Thermal transfer
Device	5146477 THERMOMARK ROLL
	5146723 THERMOMARK ROLL X1
	5146231 THERMOMARK X1.2
	5146257 THERMOMARK S1.1
Ink ribbon	5145384 THERMOMARK-RIBBON 110
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Result of weather resistance test	Test passed
Salt spray test specification	DIN EN ISO 9227:2012-09
Test duration	96 h
Salt spray testing result	Test passed
Alternating condensation climate with SO2 test specification	DIN 50018:2013-05
Climate level	AHT 1.0 S
Cycles	2
Condensation test result	Test passed
Wipe resistance of test specification inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
Result of wipe resistance test	Test passed
Foil strength	50 µm
Adhesive strength	24 µm
Marking mounting type	adhesive
File number	UL-MH48542 / PC-018

Standards and Regulations

Connection in acc. with standard	UL
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
	DIN EN 61010-1 (VDE 0411-1)

Label - EML (26,5X26,5)R SR - 0816919

Classifications

eCl@ss

eCl@ss 10.0.1	27400629
eCl@ss 4.0	24190200
eCl@ss 4.1	24190200
eCl@ss 5.0	27149100
eCl@ss 5.1	27141100
eCl@ss 6.0	27149100
eCl@ss 7.0	27149129
eCl@ss 8.0	27149129
eCl@ss 9.0	27400629

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC001288
ETIM 6.0	EC001288
ETIM 7.0	EC001288

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131504
UNSPSC 18.0	39131504
UNSPSC 19.0	39131504
UNSPSC 20.0	39131504
UNSPSC 21.0	39131504

Approvals

Approvals

Approvals

UL Recognized / CSA

Ex Approvals

Approval details

Label - EML (26,5X26,5)R SR - 0816919

Approvals

UL Recognized



<http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm>

FILE MH 48542

CSA



<http://www.csagroup.org/services-industries/product-listing/>

70191766

Accessories

Accessories

Ink ribbon

Ink ribbon - THERMOMARK-RIBBON 110 - 5145384



Ink ribbon, for roll printers for printing the product groups TML..., WML..., WML HF..., WML-FLAG..., EML..., EML-ESD..., EML-RM..., EML-HA..., EMLS..., EMLC..., EMLP... and PMM..., width: 110 mm, color: black

Marker carriers

Marker carriers - CARRIER-EMP 22 (27X27) - 0827449



Marker carriers, black, unlabeled, mounting type: screw, rivet, diameter: 22 mm, lettering field size: 27 x 27 mm

Marker carriers - CARRIER-EMLP 22 (27X27) - 0828988



Marker carriers, black, unlabeled, mounting type: screw, rivet, diameter: 22 mm, lettering field size: 27 x 27 mm

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

0816919