


# NetManager™ Horizontal Cable Managers

## specifications

Horizontal cable managers shall be capable of managing copper or fiber cables. They shall be molded out of plastic and incorporate bend radius control throughout the fingers, pass through holes, and transitions between horizontal and vertical pathways. Front hinged cover shall open 180° in up or down position. They shall mount to any standard EIA 19" rack.



## technical information

<b>Dimensions:</b>	Part Number	Height in (mm)	Width in (mm)	Depth in (mm)
	NCMH2	3.47 (88.1)	19.0 (482.6)	9.75 (247.7)
	NCMHF2	3.47 (88.1)	19.0 (482.6)	3.75 (95.3)
	NCMHF1	1.72 (43.7)	19.0 (482.6)	3.75 (95.3)
<b>Mounting options:</b>	Mounts to standard EIA 19" rack or 23" rack with optional extender bracket			
<b>Packaging:</b>	Cable management panels include hinged front cover, snap-on rear cover, and mounting hardware			
<b>Finger spacing:</b>	3/8" spacing between fingers			
<b>Bend radius control:</b>	1/2" bend radius for fingers, transitions, and pass throughs on front 3/8" bend radius for fingers on rear			

## key features and benefits

<b>Integral bend radius</b>	Maintains cable bend radii in all cable pathways for high performance copper and fiber applications
<hr/>	
<b>Curved fingers</b>	Separates and organizes Category 5e and Category 6 cable for simple moves, adds, and changes
<hr/>	
<b>Cable pass through holes</b>	Provides ease of installation and cable maintenance
<hr/>	
<b>Integral wire retainers</b>	Holds cable in place for easy moves, adds, and changes
<hr/>	
<b>Lightweight plastic construction</b>	Provides durability and easy installation
<hr/>	
<b>Hinged front cover</b>	Opens 180° up or down to allow hands-free access to cable

## applications

Designed for Category 5e, Category 6, and fiber cables, the Panduit® NetManager™ Horizontal Cable Managers provide a cost effective solution that organizes, manages, and protects network cabling in telecommunication rooms and data centers. Finger spacing organizes cable as they exit the patch panel and bend radius control helps protect cable

from kinks, snags, and crushing, ensuring system performance and reliability. When used with Panduit® Mini-Com® or QuickNet® Patch Panels, Panduit patch cords, vertical managers, and racks, the user receives a complete end-to-end solution that satisfies functional requirements and showcases the network cabling.

### 2 RU Managers

<b>Front and rear:</b>	NCMH2
<b>Front only:</b>	NCMHF2

### 1 RU Manager

<b>Front only:</b>	NCMHF1
--------------------	--------

### Accessories

<b>Extender bracket, 1 RU:</b>	PEB1
<b>Extender bracket, 2 RU:</b>	PEB2
<b>(for 23" rack mounting)</b>	

### Standard 2 Post Racks

<b>3" channel</b>	
<b>8'H x 19"W:</b>	R2P96
<b>6.5'H x 19"W:</b>	R2P79
<b>7'H x 19"W:</b>	R2P
<b>4'H x 19"W:</b>	R2P48
<b>7'H x 23"W:</b>	R2PW

<b>6" channel</b>	
<b>7'H x 19"W:</b>	R2P6S

### 4 Post Racks, 19" Mount – 7 Foot

<b>23" deep:</b>	R4P23*^
<b>30" deep:</b>	R4P*^
<b>36" deep:</b>	R4P36*^
<b>42" deep:</b>	R4P42*^

### NetRunner™ Vertical Cable Managers

<b>Front and rear</b>	
<b>22 RU, 4" x 5":</b>	WMPV22E
<b>45 RU, 4" x 5":</b>	WMPV45E
<b>45 RU, 6" x 6":</b>	WMPVHC45E
<b>Front only</b>	
<b>22 RU, 4" x 5":</b>	WMPVF22E
<b>45 RU, 4" x 5":</b>	WMPVF45E
<b>45 RU, 6" x 6":</b>	WMPVHCF45E

### NetRunner™ High Capacity Vertical Cable Managers

<b>Front and rear</b>	
<b>45 RU, 6" x 6":</b>	NRV6
<b>45 RU, 10" x 6":</b>	NRV10
<b>45 RU, 12" x 6":</b>	NRV12
<b>Front only</b>	
<b>45 RU, 6" x 6":</b>	NRVF6
<b>45 RU, 10" x 6":</b>	NRVF10
<b>45 RU, 12" x 6":</b>	NRVF12
<b>Doors</b>	
<b>6" wide:</b>	NRD6B1
<b>10" wide:</b>	NRD10B1
<b>12" wide:</b>	NRD12B1






### PatchRunner™ 2 Vertical Cable Managers with Doors - 7 Foot

<b>Front and rear</b>	
<b>45 RU 6" wide:</b>	PR2VD06^
<b>45 RU 8" wide:</b>	PR2VD08^
<b>45 RU 10" wide:</b>	PR2VD10^
<b>45 RU 12" wide:</b>	PR2VD12^
<b>Front only</b>	
<b>45 RU 6" wide:</b>	PR2VFD06^
<b>45 RU 8" wide:</b>	PR2VFD08^
<b>45 RU 10" wide:</b>	PR2VFD10^
<b>45 RU 12" wide:</b>	PR2VFD12^

^Add suffix 96 to the end of the part number for 8 foot versions.

\*Add "CN" for Cage Nut Rails

# NetManager™ Horizontal Cable Managers



**NOTE:** For optimal routing of patch cords left and right of manager, leave middle slot empty.

Dimensions are in inches. [Dimensions in parenthesis are metric].

## WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT US/CANADA  
Phone: 800.777.3300

PANDUIT EUROPE LTD.  
London, UK  
cs-emea@panduit.com  
Phone: 44.20.8601.7200

PANDUIT SINGAPORE PTE. LTD.  
Republic of Singapore  
cs-ap@panduit.com  
Phone: 65.6305.7575

PANDUIT JAPAN  
Tokyo, Japan  
cs-japan@panduit.com  
Phone: 81.3.6863.6000

PANDUIT LATIN AMERICA  
Guadalajara, Mexico  
cs-la@panduit.com  
Phone: 52.33.3777.6000

PANDUIT AUSTRALIA PTY. LTD.  
Victoria, Australia  
cs-aus@panduit.com  
Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to [www.panduit.com/warranty](http://www.panduit.com/warranty)

For more information

Visit us at [www.panduit.com](http://www.panduit.com)

Contact Customer Service by email: [cs@panduit.com](mailto:cs@panduit.com)  
or by phone: 800.777.3300

**PANDUIT®**

©2018 Panduit Corp.  
ALL RIGHTS RESERVED.  
**RKSP147--WW-ENG**  
6/2018

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

NCMHF2