

Vinyl Cloth Letters and Numbers



Material Chart

Material	Print Method	Temperature Range	Features
Vinyl Cloth, (PCL,PCLCP)	Pre-Printed	-50°F to 170°F (-46°C to 77°C)	Indoor/outdoor rated; thin conformable material with repositionable adhesive allows label to be removed and reused or used in temporary applications; provides durability, high temperature resistance, and dimensional stability for rough or textured surfaces.

Part Number	Legend	Legend Height		Height		Width		Color (Legend/Background)	Markers Per Card	Std. Pkg. Card(s)	Std. Ctn. Card(s)
		In.	mm	In.	mm	In.	mm				
PCL037-0	0	0.38	9.7	0.50	12.7	0.34	8.7	Black/Yellow	78	25	100
PCL037-1 thru PCL037-9	1 thru 9									25	100
PCL037-0-9	0 thru 9									25	100
PCL037-A thru PCL037-Z	A thru Z									25	100
PCL037-A-Z	A thru Z									25	100
PCLCP037-A-Z	A thru Z									1	4
PCLCP037-0-9	0 thru 9									1	4
PCL037-DSH	—									25	100
PCL062-0	0	0.63	16.0	0.75	19.1	0.56	14.2	Black/Yellow	32	25	100
PCL062-1 thru PCL062-9	1 thru 9									25	100
PCL062-0-9	0 thru 9									1	4
PCL062-A thru PCL062-Z	A thru Z									25	100
PCL062-A-Z	A thru Z									25	100
PCLCP062-0-9	1 thru 5 6 thru 0									1	4
PCLCP062-A-Z	A thru Z									1	4
PCL062-DSH	—									25	100
PCL100-0	0	1.00	25.4	1.50	38.1	0.88	22.4	Black/Yellow	10	25	100
PCL100-1 thru PCL100-9	1 thru 9									25	100
PCL100-0-9	0 thru 9									25	100
PCL100-A thru PCL100-Z	A thru Z									25	100
PCL100-A-J	A thru J									25	100
PCL100-K-T	K thru T									25	100
PCL100-U-Z	U thru Z									25	100
PCLCP100-0-9	1 thru 5 6 thru 0									1	4
PCLCP100-A-Z	A thru Z									1	4
PCL100-DSH	—									25	100
PCL200-0	0	2.00	50.8	2.25	57.2	0.88	22.4	Black/Yellow	10	25	100
PCL200-1 thru PCL200-9	1 thru 9									25	100
PCL200-0-9	0 thru 9									25	100
PCL200-A thru PCL200-Z	A thru Z									25	100
PCL200-A-J	A thru J									25	100
PCL200-K-T	K thru T									25	100
PCL200-U-Z	UK thru TZ									25	100
PCLCP200-0-9	1 thru 5 6 thru 0									1	4
PCLCP200-A-Z	A thru Z									1	4
PCL200-DSH	—									25	100

Table continues on page E5.38

Order number of pieces required, in multiples of Standard Package Quantity.

Prime items appear in **BOLD**.

A.
System
Overview

B1.
Cable Ties

B2.
Cable
Accessories

B3.
Stainless
Steel Ties

C1.
Wiring
Duct

C2.
Surface
Raceway

C3.
Abrasion
Protection

C4.
Cable
Management

D1.
Terminals

D2.
Power
Connectors

D3.
Grounding
Connectors

E1.
Labeling
Systems

E2.
Labels

E3.
Pre-Printed
& Write-On
Markers

E4.
Permanent
Identification

E5.
Lockout/
Tagout
& Safety
Solutions

F.
Index

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[PCL062-2](#) [PCL100-8](#) [PCL200-M](#) [PCL100-2](#) [PCL062-H](#) [PCL200-7](#) [PCL062-3](#) [PCL062-N](#) [PCL100-N](#) [PCL200-K](#)
[PCL200-4](#) [PCL100-5](#) [PCL200-P](#) [PCL062-6](#) [PCL062-K](#) [PCL062-V](#) [PCL062-Y](#) [PCL200-W](#) [PCL200-H](#) [PCL100-G](#)
[PCL062-W](#) [PCL062-C](#) [PCL100-0-9](#) [PCL200-2](#) [PCL200-X](#) [PCL062-D](#) [PCL062-F](#) [PCL200-I](#) [PCL200-S](#) [PCL100-J](#)
[PCL062-T](#) [PCL100-V](#) [PCL200-T](#) [PCL062-B](#) [PCL100-U](#) [PCL062-U](#) [PCL062-R](#) [PCL100-W](#) [PCL100-O](#) [PCL200-B](#)
[PCL100-R](#) [PCL200-8](#) [PCL062-P](#) [PCL062-O](#) [PCL062-M](#) [PCL200-Q](#) [PCL100-Q](#) [PCL200-N](#) [PCL200-O](#) [PCL100-7](#)
[PCL100-P](#) [PCL062-X](#) [PCL100-H](#) [PCL200-3](#) [PCL062-J](#) [PCL200-V](#) [PCL062-4](#) [PCL200-5](#) [PCL200-U](#) [PCL062-8](#)
[PCL200-C](#) [PCL100-K](#) [PCL100-4](#) [PCL100-X](#) [PCL062-I](#) [PCL100-Y](#) [PCL100-B](#) [PCL100-T](#) [PCL062-Q](#) [PCL100-E](#)
[PCL200-G](#) [PCL100-L](#) [PCL062-L](#) [PCL062-7](#) [PCL100-3](#) [PCL200-R](#) [PCL062-S](#) [PCL062-G](#) [PCL100-M](#) [PCL200-E](#)
[PCL100-F](#) [PCL062-E](#) [PCL100-D](#) [PCL100-I](#) [PCL200-F](#) [PCL200-D](#) [PCL200-Y](#) [PCL100-6](#) [PCL100-S](#) [PCL062-5](#)
[PCL200-L](#) [PCL200-6](#) [PCL200-J](#)