

Marker for terminal blocks - UC-TMF 8 BU - 0818645

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Marker for terminal blocks, Sheet, blue, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: snap into flat marker groove, for terminal block width: 8.2 mm, lettering field size: 7.6 x 5.1 mm, Number of individual labels: 56

Your advantages

- ✓ Labeling service: Phoenix Contact can custom-label all UniCard markers according to your requirements
- ✓ The UC-TMF ... UniCard labeling range includes markers for products with tall and flat marker grooves

RoHS

Key Commercial Data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 046356 136310
GTIN	4046356136310

Technical data

Dimensions

Width (a)	8 mm
-----------	------

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.

General

Color	blue
Type	flat
Components	free from silicone and halogen
Flammability rating according to UL 94	V2
Material	PA
RoHS compliant	Yes
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)

Marker for terminal blocks - UC-TMF 8 BU - 0818645

Technical data

General

Number of individual labels	56
Number of individual labels per row	7
Printability	UV LED technology
Device	5147999 BLUEMARK CLED
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Salt spray test specification	DIN EN 60068-2-11:2000-02
Test duration	96 h
Salt spray testing result	Test passed
Wipe resistance of test specification inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
Result of wipe resistance test	Test passed
Marking mounting type	snap into flat marker groove
Result	Test passed
Oxygen index (DIN EN ISO 4589-2)	28,2%
Class I	3
Class F	2
R22	HL 1 - HL 2
R23	HL 1 - HL 2
R24	HL 1 - HL 2

Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Flammability rating according to UL 94	V2

Classifications

eCl@ss

eCl@ss 10.0.1	27141137
eCl@ss 4.0	24190200
eCl@ss 4.1	24190200
eCl@ss 5.0	27141100
eCl@ss 5.1	27141100
eCl@ss 6.0	27141100
eCl@ss 7.0	27141137
eCl@ss 8.0	27141137
eCl@ss 9.0	27141137

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761

Marker for terminal blocks - UC-TMF 8 BU - 0818645

Classifications

ETIM

ETIM 5.0	EC000761
ETIM 6.0	EC000761
ETIM 7.0	EC000761

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131505
UNSPSC 18.0	39131505
UNSPSC 19.0	39131505
UNSPSC 20.0	39131505
UNSPSC 21.0	39131505

Accessories

Accessories

Magazine

Magazine - P1 UC-MAG 4 - 5146105



Magazine, for CMS-P1-PLOTTER and PLOTMARK, for accommodating UC-TMF..., UC1-TMF..., UC-WMT...

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

0818645