


QuickNet™ PanMPO™ Round Interconnect Cable Assemblies

technical information

MPO Interconnect Round Cable Assemblies are pre-terminated 12-fiber cable assemblies that are used in high-density network applications. These interconnect round cable assemblies are used with pre-terminated cassettes in main and horizontal cabling distribution areas. The QuickNet™ System meets the demands of Gigabit Ethernet, 10 Gigabit Ethernet, and high speed Fibre Channel systems while maintaining compatibility with Ethernet. The high-density modular design fits into rack mount fiber cassette enclosures to ensure efficient use of space and rapid network deployment.



application

Interconnect cables are small in diameter, extremely flexible and intended for shorter cable runs. These small cables minimize waste, optimize cable management, speed deployment, and improve flexibility and manageability.

construction

Cable type:	3.0mm indoor round
Cable jacket ratings:	Optical Fiber Nonconductive Plenum (OFNP) Low Smoke Zero Halogen (LSZH)
Fiber types:	Multimode: OM3 50/125µm OM4 50/125µm
Connector types; end 'A' and end 'B':	PanMPO™ Female or PanMPO™ Male
Fiber count:	12
Jacket color:	OM3: Aqua OM4: Aqua
Connector types; end 'A' and end 'B':	PanMPO™ Female or PanMPO™ Male

optical properties

Maximum cable attenuation:	Multimode: 3.5dB/km at 850nm 1.5dB/km at 1300nm
Maximum connector insertion loss:	Multimode: 0.50dB
Minimum connector return loss:	Multimode: OM3 26dB OM4 26dB

physical properties

Cable outside diameter (OD):	3.0mm
Minimum bend radius:	30mm
Cable retention strength:	50N
Flex:	100 cycles at 4.9N
Twist:	10 cycles at 15N
Gender reversal durability:	50 cycles
Polarity reversal durability:	50 cycles

environmental properties

Storage and shipping temperature:	-40°C to 70°C
Installation temperature:	0°C to 40°C
Operating temperature:	-10°C to 60°C

standards

Meets or exceeds TIA/EIA-568-C.3, TIA-604-5 (FOCIS-5), TIA/EIA-568-C.1, RoHS Compliant


QuickNet™ PanMPO™ Round Interconnect Cable Assemblies

part number

Example: FZTRP7N7NANM001 = Fiber OM4, 12-fibers, 3.0mm, plenum rated, PanMPO™ Female to PanMPO™ Female, polarity method A, no pulling eye, 1 meter.

Character	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15
Example	F	Z	T	R	P	7	N	7	N	A	N	F	0	0	1
1 – Fiber Product F = Fiber					5 – Jacket Type L = Low Smoke Zero Halogen (LSZH) P = Optical Fiber Nonconductive Plenum (OFNP)					10 – Construction/Performance A = Polarity A-Standard IL B = Polarity B-Standard IL X = Multimode Polarity A - Optimized IL Y = Multimode Polarity B - Optimized IL K = Multimode Polarity A - Ultra Low IL L = Multimode Polarity B - Ultra Low IL					
2 – Fiber Type 9 = OS1/2 9/125 X = OM3 50/125 Z = OM4 50/125					6 – Connector Type End ‘A’ 7 = Multimode PanMPO™ Female 8 = Multimode PanMPO™ Male					11 – Other N = No pulling eye					
3 – Fiber Count T = 12-fiber					7 – Connector Variant N = No variant					12 – Unit of Length F = Feet M = Meters					
4 – Cable Type R = 3.0mm round indoor					8 – Connector Type End ‘B’ 7 = Multimode PanMPO™ Female 8 = Multimode PanMPO™ Male					13, 14, 15 – Length 1 - 30m (LSZH) 3 - 100ft (Plenum)					
					9 – Connector Variant N = No variant										

QuickNet™ PanMPO™ Interconnect Round Cable Assembly Detail



Other options are available as follows:

Fiber Types: OM1 62.5/125, OM2 50/125, OM3, OM4

Fiber Counts: 12-fiber

Jacket Type: LSZH and Plenum

Construction/Performance: Standard IL, Optimized and Ultra IL for multimode. Polarity (Method) A and Polarity (Method) B.

Please contact Panduit customer service for information on additional part number options

WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT CANADA
Markham, Ontario
cs-cdn@panduit.com
Phone: 800.777.3300

PANDUIT EUROPE LTD.
London, UK
cs-emea@panduit.com
Phone: 44.20.8601.7200

PANDUIT SINGAPORE PTE. LTD.
Republic of Singapore
cs-ap@panduit.com
Phone: 65.6305.7575

PANDUIT JAPAN
Tokyo, Japan
cs-japan@panduit.com
Phone: 81.3.6863.6000

PANDUIT LATIN AMERICA
Guadalajara, Mexico
cs-la@panduit.com
Phone: 52.33.3777.6000

PANDUIT AUSTRALIA PTY. LTD.
Victoria, Australia
cs-aus@panduit.com
Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

For more information

Visit us at www.panduit.com

Contact Customer Service by email: cs@panduit.com
or by phone: 800.777.3300

PANDUIT®

©2015 Panduit Corp.
ALL RIGHTS RESERVED.
FBSP91--WW-ENG
4/2015

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

FXTRP7N7NXNF052	FZTRP7N7NYNF089	FXTRP7N7NYNF091	FXTRP7N7NXNF098	FXTRP7N7NXNF032
FZTRP7N7NYNF092	FZTRP7N7NYNF071	FXTRP7N7NXNF077	F9TRP7N7NANF099	FXTRP7N7NYNF007
FXTRP7N7NYNF025	F9TRP7N7NANF034	F9TRP7N7NANF031	FXTRP7N7NXNF050	F9TRP7N7NANF068
FZTRP7N7NYNF053	FZTRP7N7NYNF027	FZTRP7N7NYNF056	F9TRL7N7NANM010	FXTRP7N7NXNF017
FXTRP7N7NYNF027	F9TRP7N7NANF032	FXTRP7N7NYNF024	FXTRP7N7NBNF010	FXTRP7N7NYNF028
F9TRP7N7NANF066	FXTRP7N7NYNF073	F9TRL7N7NANM011	FZTRP7N7NYNF054	F9TRL7N7NANM028
FXTRP7N7NXNF079	FXTRP7N7NYNF074	F9TRP7N7NANF067	FXTRP7N7NXNF045	F9TRP7N7NANF084
FXTRP7N7NXNF095	FXTRP7N7NXNF028	F9TRL7N7NANM026	F9TRP7N7NANF015	F9TRP7N7NANF098
F9TRP7N7NANF035	FXTRP7N7NXNF084	FXTRP7N7NYNF053	FZTRP7N7NYNF029	FZTRP7N7NYNF086
FXTRP7N7NXNF072	FZTRP7N7NYNF067	FXTRP7N7NXNF024	F9TRP7N7NANF055	F9TRL7N7NANM006
FXTRP7N7NXNF056	FXTRP7N7NYNF055	FXTRP7N7NBNF080	FZTRP7N7NYNF091	FXTRP7N7NXNF031
F9TRP7N7NANF083	F9TRL7N7NANM029	FXTRP7N7NBNF094	FZTRP7N7NYNF073	FZTRP7N7NYNF074
FZTRP7N7NYNF055	FZTRP7N7NYNF003	F9TRL7N7NANM009	FXTRP7N7NXNF081	FXTRP7N7NYNF056
FXTRP7N7NBNF078	F9TRL7N7NANM012	F9TRP7N7NANF018	FXTRP7N7NYNF006	F9TRL7N7NANM008
FXTRP7N7NXNF007	FXTRP7N7NYNF093	FXTRP7N7NXNF062	FZTRP7N7NBNF006	F9TRP7N7NANF004
F9TRP7N7NANF027	FXTRP7N7NYNF077	FXTRP7N7NYNF080	FXTRP7N7NXNF041	F9TRP7N7NANF080
FZTRP7N7NYNF051	F9TRP7N7NANF087	FXTRP7N7NXNF099	FXTRP7N7NYNF059	FZTRP7N7NXNF096
FXTRP7N7NYNF094	F9TRP7N7NANF085	FXTRP7N7NXNF068	F9TRP7N7NANF058	FZTRP7N7NYNF045
FZTRP7N7NYNF048	FZTRP7N7NYNF023	F9TRP7N7NANF044	FXTRP7N7NXNF013	F9TRL7N7NANM003
FXTRP7N7NXNF092	FZTRP7N7NXNF009	F9TRL7N7NANM015	FXTRP7N7NXNF094	F9TRP7N7NANF011