

QuickNet™ Small Diameter Trunk Cable Assemblies OFNP and LSZH

technical information

Small Diameter Trunk Cable Assemblies allow for rapid deployment of high-density permanent links in a single assembly for data center applications requiring quick infrastructure deployment, such as main, horizontal, and zone distribution areas. These trunk cable assemblies optimize cable routing requirements to ensure efficient use of pathway space and significantly reduce installation time and cost. QuickNet™ Small Diameter Trunk Cable Assemblies are built with modular MPO connectivity and provide compatibility, flexibility and system performance in all permanent link applications. All small diameter trunk cable assemblies are factory terminated and tested to deliver verified optical performance and reliability for improved network integrity. 10Gig versions provide 10 Gb/s network performance up to 300 meters for OM3 and up to 550 meters for OM4 per IEEE 802.3ae 10 GbE standard while maintaining compatibility with legacy systems.



application

Allows system designers to tailor configuration, reach and breakout construction to application requirements; to minimize waste, optimize cable management, speed deployment, improve flexibility and manageability for lower installation costs. Small diameter trunk cable assemblies use 30 – 40% less space which is ideal for high cable density applications.

construction

Cable type:	Indoor Small Diameter Trunk	
Cable jacket ratings:	Plenum (OFNP) NFPA 262 Low Smoke Zero Halogen (LSZH) IEC 60332-1 and IEC 60332-3C	
Fiber types:	Singlemode:	OS1/OS2 9/125µm
	Multimode:	OM3 50/125µm OM4 50/125µm
Connector types end 'A':	MPO Female or MPO Male, LC Duplex (12F only)	
Connector types end 'B':	MPO Female or MPO Male, LC Duplex (12F only)	
Fiber count:	12, 24 and 48	
Jacket color:	OS1/OS2	Yellow
	OM3	Aqua
	OM4	Aqua

physical properties

Cable outside diameter (OD):	12-fiber:	4.5mm
	24-fiber:	5.4mm
	48-fiber:	6.1mm
Cable weight (kg/km) (lb/kft):	12-fiber LSZH:	22.2kg/km (14.9 lb/kft)
	24-fiber LSZH:	29.7kg/km (19.9 lb/kft)
	12-fiber Plenum:	23.6kg/km (15.9 lb/kft)
	24-fiber Plenum:	31.7kg/km (21.3lb/kft)
Minimum bend radius:	Under load:	20 x Cable OD
	Static:	10 x Cable OD
Cable tensile strength:	440N	
Cable compressive load:	10 N/mm	
Connector cable retention:	50N	
Connector durability:	500 mating cycles*	
Breakout outside diameter:	3.0mm	
Transition outside diameter:	12-fiber:	10mm
	24-fiber:	10mm
	48-fiber:	12mm
Pulling eye diameter:	12-fiber:	19mm
	24-fiber:	23mm
	48-fiber:	29mm
Breakout length:	1m	

*With proper cleaning and inspecting.

optical properties

Maximum cable attenuation:	Singlemode:	0.4dB/km at 1310nm 0.3dB/km at 1550nm
	Multimode:	3.0dB/km at 850nm 1.5dB/km at 1300nm
Maximum connector insertion loss:	Standard Singlemode MPO:	0.75dB
	Standard Multimode MPO:	0.50dB
	Optimized Multimode MPO:	0.35dB
	Standard Singlemode LC:	0.35dB
	Standard Multimode LC:	0.25dB
	Optimized Multimode LC:	0.15dB
Minimum connector return loss:	Singlemode:	55dB
	Multimode:	MPO 30dB LC 26dB

environmental properties

Operating temperature:	-20°C to + 70°C (-4°F to 158°F)
Storage and shipping temperature:	-40°C to +70°C (-40°F to 158°F)
Installation temperature:	-10°C to + 60°C (14°F to 140°F)

standards

Meets or exceeds: ISO/IEC 11801, TIA/EIA-568-C.3, TIA-604-5 (FOCIS-5), TIC/EIA-568-C.1, GR-409-CORE, ICEA S-83-596 RoHS Complaint

QuickNet™ Small Diameter Trunk Cable Assemblies OFNP and LSZH

part number

Example: FXUY5E5EAAM030 = OM3, 24-fiber, indoor small diameter trunk cable, plenum, MPO female to MPO female, polarity A, pulling eye, 30 meters.

CHARACTER	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15
EXAMPLE	F	X	U	Y	P	5	E	5	E	A	A	M	0	3	0

1 – Fiber

F = Fiber

2 – Fiber Type

9 = OS1/OS2 9/125µm

X = OM3 50/125µm

Z = OM4 50/125µm

3 – Fiber Count

T = 12 fiber

U = 24 fiber

W = 48 fiber

4 – Cable Type

Y = Indoor small diameter trunk cable

5 – Jacket Type

P = Plenum (OFNP)

L = Low Smoke Zero Halogen (LSZH)

6 – Connector Type (end A)

5 = MPO female connector

6 = MPO male connector

L = LC duplex (12 and 24 fiber only)

7 – Connector Variant

E = (MPO)

2 = 2.0mm upjacket (LC)

5 = 39" Breakout with HD Flex™ Transition

8 – Connector Type (end B)

5 = MPO female connector

6 = MPO male connector

L = LC Duplex (12 and 24 fiber only)

9 – Connector Variant

E = 1m breakout (MPO)

2 = 2.0mm upjacket (LC)

5 = 39" Breakout with HD Flex™ Transition

10–Construction/Performance

A = Polarity Method A, Standard IL (MPO to MPO)

B = Polarity Method B, Standard IL (MPO to MPO)

O = Optimized Performance/Std. Polarity (MPO to LC or LC to LC)

S = Std. Performance/Std. Polarity (MPO to LC or LC to LC)

X = Polarity Method A, Optimized IL (MPO to MPO)

Y = Polarity Method B, Optimized IL (MPO to MPO)

11 – Other

A = Pulling eye end A

N = No pulling eye (lengths less than 20 meters/60 feet only)

12 – Unit of Length

M = Meters


F = Feet

13, 14, 15 – Cable Assembly Length

M = 005 – 100

F = 015 – 300

small diameter trunk cable assembly detail



Please contact Panduit customer service for information on additional part number options.

WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT US/CANADA
Phone: 800.777.3300

PANDUIT EUROPE LTD.
London, UK
cs-emea@panduit.com
Phone: 44.20.8601.7200

PANDUIT SINGAPORE PTE. LTD.
Republic of Singapore
cs-ap@panduit.com
Phone: 65.6305.7575

PANDUIT JAPAN
Tokyo, Japan
cs-japan@panduit.com
Phone: 81.3.6863.6000

PANDUIT LATIN AMERICA
Guadalajara, Mexico
cs-la@panduit.com
Phone: 52.33.3777.6000

PANDUIT AUSTRALIA PTY. LTD.
Victoria, Australia
cs-aus@panduit.com
Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

For more information

Visit us at www.panduit.com

Contact Customer Service by email: cs@panduit.com
or by phone: 800.777.3300

PANDUIT®

©2017 Panduit Corp.
ALL RIGHTS RESERVED.
FBSP74--WW-ENG
11/2017

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

F9WYL5E5EAAM033	F9WYL5E5EAAM050	F9WYL5E5EAAM068	F9WYP5555ANF026	F9WYL5E5EAAM085
F9WYP5555ANF027	F9WYL5E5EAAM049	F9WYP5555ANF044	F9WYL5E5EAAM098	F9WYL5E5EAAM082
F9WYP5555ANF043	F9WYP5555ANF057	F9WYL5E5EAAM039	F9WYP5555ANF041	F9WYP5555ANF024
F9WYL5E5EAAM093	F9WYL5E5EAAM076	F9WYL5E5EAAM083	F9WYP5555ANF040	F9WYP5555ANF025
F9WYP5555ANF020	F9WYL5E5EAAM030	F9WYL5E5EAAM067	F9WYL5E5EAAM096	F9WYP5555ANF042
F9WYP5555ANF031	F9WYP5555ANF028	F9WYL5E5EAAM035	F9WYP5555ANF059	F9WYL5E5EAAM099
F9WYL5E5EAAM057	F9WYP5555ANF015	F9WYL5E5EAAM074	F9WYP5555ANF058	F9WYP5555ANF052
F9WYP5555ANF049	F9WYP5555ANF032	F9WYP5555ANF034	F9WYL5E5EAAM061	F9WYL5E5EAAM021
F9WYL5E5EAAM066	F9WYL5E5EAAM064	F9WYL5E5EAAM044	F9WYP5555ANF022	F9WYL5E5EAAM087
F9WYP5555ANF045	F9WYL5E5EAAM078	F9WYP5555ANF017	F9WYL5E5EAAM043	F9WYL5E5EAAM088
F9WYP5555ANF023	F9WYL5E5EAAM026	F9WYL5E5EAAM037	F9WYL5E5EAAM023	F9WYL5E5EAAM060
F9WYL5E5EAAM094	F9WYL5E5EAAM091	F9WYP5555ANF019	F9WYL5E5EAAM084	F9WYP5555ANF016
F9WYL5E5EAAM042	F9WYP5555ANF055	F9WYL5E5EAAM031	F9WYL5E5EAAM100	F9WYP5555ANF035
F9WYL5E5EAAM097	F9WYL5E5EAAM077	F9WYL5E5EAAM025	F9WYL5E5EAAM054	F9WYL5E5EAAM045
F9WYL5E5EAAM048	F9WYP5555ANF033	F9WYL5E5EAAM071	F9WYP5555ANF039	F9WYL5E5EAAM092
F9WYL5E5EAAM081	F9WYL5E5EAAM063	F9WYP5555ANF037	F9WYL5E5EAAM032	F9WYL5E5EAAM065
F9WYL5E5EAAM079	F9WYL5E5EAAM040	F9WYP5555ANF036	F9WYL5E5EAAM062	F9WYP5555ANF054
F9WYL5E5EAAM080	F9WYL5E5EAAM053	F9WYP5555ANF050	F9WYL5E5EAAM072	F9WYL5E5EAAM075
F9WYL5E5EAAM058	F9WYP5555ANF048	F9WYL5E5EAAM059	F9WYL5E5EAAM047	F9WYL5E5EAAM027
F9WYL5E5EAAM051	F9WYL5E5EAAM089	F9WYP5555ANF018	F9WYL5E5EAAM069	F9WYL5E5EAAM046