


PANDUIT PART NUMBER	ALUMINUM CONDUCTOR SIZE	STUD SIZE	OVERALL LENGTH "A" +/- .12	BARREL LENGTH "B" MIN	BARREL		TONGUE WIDTH "W" +/- .060	TONGUE THICKNESS "T" +/- .04	TONGUE LENGTH "P" MIN	HOLE OFFSET "G" +/- .06	WRENCH CLEARANCE "C" REF	WIRE STRIP LENGTH	PANDUIT CRIMP TOOL PART NUMBERS			
					I.D. +/- .02	O.D. +/- .06							CT-2940, CT-940CH			
LAA900-58-1	900kcmil	5/8"	6.63	3.38	1.13	1.66	1.74	0.59	1.88	0.88	1.00	3-7/16"		CD-940-800A*	GRAY P140	4 CRIMPS

\*CD-940 DIES TO BE USED EXCLUSIVELY WITH CT-940CH AND CT-2940 TOOLS

NOTES:

1. MATERIAL: SEAMLESS ALUMINUM TUBING
2. TIN PLATED
3. BARREL COLOR CODED WITH DIE SET INDEX NUMBER
4. UL LISTED & TEMPERATURE RATED 90°C (AL9)
5. CSA CERTIFIED
6. FOR STRANDED ALUMINUM WIRE ONLY
7. ALL DIMENSIONS IN INCHES



LAA SERIES 900kcmil ALUMINUM LUG CUSTOMER DRAWING											
ITEM REVISION NAME											12J037BF/00
DATASET FILE NAME											12J037BF-DC/00.SLDDRW
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]											
$.X \pm .XXX$ $.XX \pm .XX$ ANGLES $\pm .XX$											
DRAWING RELEASED											
12J037BF-DC											
00	7/14	JHNU	JHNU	RGB	REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
DRAWN BY JHNU DATE 7/14 CHK RGB SCALE NONE											
THIRD ANGLE PROJECTION											
DRAWING NUMBER 12J037BF-DC											
SEE NOTES											
MATERIAL											
SHEET 1 OF 1											
SIZE B											

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit](#):

[LAA900-58-1](#)