



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

TABLE 1

| PLUG PACK   | CUSTOMER DRAWING# |
|-------------|-------------------|
| 6-POSITION  | 02802-19          |
| 8-POSITION  | 02802-25          |
| 12-POSITION | 02802-26          |
| RECESSED    | 03073-06          |

## NOTES:

1. HARNESS IS AVAILABLE IN PLUG PACK/PLUG, AND PLUG/PLUG CONFIGURATIONS. SEE CHART ON SHEET 2 FOR PRODUCT OPTIONS
2. PATCH CORDS ARE BUNDLED USING HLS VELCRO STRAPS AT 12" (305mm) SPACING.
3. EACH PATCH CORD IS SEQUENTIALLY NUMBERED AT BOTH ENDS WITH PORT ID LABELS.
4. PATCH CORD ID LABELS CONTAIN PATCH CORD PERFORMANCE, PART#, LENGTH(L), AND QC#.
5. PLUG PACK ID LABELS AND PLFIMA MARKER TIES ARE INCLUDED FOR CUSTOMER APPLIED SWITCH AND PORT IDENTIFICATION.  
FOR PRINTABLE LABEL OPTIONS, REFER TO PANDUIT C125X030FJJ, C125X030YPT AND C125X030FJC.
6. PATCH CORDS ARE 100% PERFORMANCE TESTED
7. SEE CATALOG FOR OPTIONAL REMOVAL TOOL (QPRT) AND LOCK-IN DEVICE (QPPLD\*)



6-CABLE ASSEMBLY  
PLUG PACK TO  
PLUG SHOWN


|                                                                                                                                                 |                  |                              |               |
|-------------------------------------------------------------------------------------------------------------------------------------------------|------------------|------------------------------|---------------|
| PART NUMBER<br>QPP*****                                                                                                                         |                  | PRODUCT SPEC/PKG SPEC<br>N/A |               |
| I.I. NUMBER<br>N/A                                                                                                                              |                  | WORK INSTRUCTION<br>N/A      |               |
| TITLE<br>QUICKNET SWITCH PATCHING HARNESS                                                                                                       |                  |                              |               |
| CUSTOMER DRAWING                                                                                                                                |                  |                              |               |
| ITEM REVISION NAME<br>M02802EH/01                                                                                                               |                  | <b>PANDUIT</b>               |               |
| DATASET FILE NAME<br>M02802EH_DC31/01E                                                                                                          |                  |                              |               |
| UNLESS OTHERWISE SPECIFIED,<br>DIMENSIONAL TOLERANCES ARE: IN [ mm ]<br>.x ± .1 [ 2.54 ] .xxx ± .005 [ .127 ]<br>.xx ± .01 [ .25 ] ANGLES ± 5 ° |                  | MATERIAL:                    |               |
|                                                                                                                                                 |                  | DRAWING NUMBER:<br>02802-31  |               |
| DRAWN BY<br>MDJr                                                                                                                                | DATE<br>10-25-07 | CHK<br>WFMi                  | SCALE<br>NONE |
| REV                                                                                                                                             |                  | DATE                         |               |
| BY                                                                                                                                              |                  | CHK                          |               |
| APR                                                                                                                                             |                  | DESCRIPTION                  |               |
| ECN                                                                                                                                             |                  | SHT 1 OF 2                   |               |
| SIZE<br>A                                                                                                                                       |                  |                              |               |

|     |          |     |      |      |                                                                                                                                                              |          |
|-----|----------|-----|------|------|--------------------------------------------------------------------------------------------------------------------------------------------------------------|----------|
| 3   | 12-18-13 | BJN | WFMi | TMBA | D. CHANGED DRAWING TITLE E. UPDATED MATRIX ON SH2<br>A. UPDATED NOTE 1. UPDATED NOTE 4 C. UPDATED NOTE 5<br>REVISED & REDRAWN PREVIOUS REVS REVD FOR CLARITY | 02802-31 |
| REV | DATE     | BY  | CHK  | APR  | DESCRIPTION                                                                                                                                                  | ECN      |

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

## QUICKNET SWITCH PATCHING ASSEMBLY MATRIX

| QPP                                     | A                             | C                                        | B                                     | A                                              | B                          | 03                                 |
|-----------------------------------------|-------------------------------|------------------------------------------|---------------------------------------|------------------------------------------------|----------------------------|------------------------------------|
| QUICKNET SWITCH HARNESS TYPE            | PERFORMANCE LEVEL             | FLAME/SMOKE RATING                       | CABLE COLOR                           | PLUG PACK CONFIGURATION                        | PLUG PACK COLOR            | PATCH CORD ASSEMBLY LENGTH IN FT/M |
| QPP<br>QUICKNET PLUG TO<br>PLUG HARNESS | A - CAT 6A (10Gig) UTP        | C - CM                                   | B - BLUE                              | A - 6 PACK                                     | B - BLUE                   | 03=3 FEET                          |
|                                         | C - CAT 6 UTP                 | L - LOW SMOKE ZERO HALOGEN (LSZH)        | W - WHITE                             | B - 12 PACK                                    | W - WHITE                  | 05=5 FEET                          |
|                                         | D - CAT 5e UTP                | D - DUAL RATING (MEETS BOTH CM AND LSZH) | G - INTERNATIONAL GRAY (FOR STP ONLY) | D - 8 PACK                                     | R - RED                    | 07=7 FEET                          |
|                                         | E - CAT 6A (10Gig)/ CAT 6 STP |                                          | N - GREEN CABLE                       | R - RECESSED 6 PACK                            |                            | 10=10 FEET                         |
|                                         | S - CAT 6 SD UTP (28AWG)      |                                          | R - RED                               | P - TWO SIX PACKS ON 12 CABLE HARNESS          | L - BLACK                  | 14=14 FEET                         |
|                                         | T - CAT 5e SD UTP (28AWG)     |                                          | Y - YELLOW                            | S - TWO RECESSED SIX PACKS ON 12 CABLE HARNESS | S - SILVER (RECESSED ONLY) | 1M=1 METER                         |
|                                         | X - CAT 6A UTP MATRIX SD      |                                          | O - ORANGE                            | 6 - 6 CABLES (IF NO PLUG PACK)                 | X - NO PLUG PACK           | 2M=2 METERS                        |
|                                         | Z - CAT 6A UTP MATRIX         |                                          | V - VIOLET                            | 8 - 8 CABLES (IF NO PLUG PACK)                 |                            | 3M=3 METERS                        |
|                                         |                               |                                          | L - BLACK                             | W - 12 CABLES (IF NO PLUG PACK)                |                            | 4M=4 METERS                        |
|                                         |                               |                                          | A - GRAY (FOR UTP SD ONLY)            |                                                |                            | 5M=5 METERS                        |
|                                         |                               |                                          |                                       |                                                |                            | ##= # FEET                         |
|                                         |                               |                                          |                                       |                                                |                            | #M= # METERS                       |

|                                                                                                                                                 |                  |                               |               |
|-------------------------------------------------------------------------------------------------------------------------------------------------|------------------|-------------------------------|---------------|
| PART NUMBER<br>QPP*****                                                                                                                         |                  | PRODUCT SPEC/PKG SPEC<br>N/A  |               |
| I.I. NUMBER<br>N/A                                                                                                                              |                  | WORK INSTRUCTION<br>N/A       |               |
| TITLE<br>QUICKNET SWITCH PATCHING HARNESS                                                                                                       |                  |                               |               |
| CUSTOMER DRAWING                                                                                                                                |                  |                               |               |
| ITEM REVISION NAME<br>M02802EH/01                                                                                                               |                  | <b>PANDUIT</b>                |               |
| DATASET FILE NAME<br>M02802EH_DC31/01E                                                                                                          |                  |                               |               |
| UNLESS OTHERWISE SPECIFIED,<br>DIMENSIONAL TOLERANCES ARE: IN [ mm ]<br>.x ± .1 [ 2.54 ] .xxx ± .005 [ .127 ]<br>.xx ± .01 [ .25 ] ANGLES ± 5 ° |                  | MATERIAL:                     |               |
|  THIRD ANGLE<br>PROJECTION                                 |                  | DRAWING NUMBER:<br>02802 - 31 |               |
| DRAWN BY<br>MDJr                                                                                                                                | DATE<br>10-25-07 | CHK<br>WFMI                   | SCALE<br>NONE |
| SHT 2 OF 2                                                                                                                                      |                  | SIZE<br>A                     |               |

| 3   | 12-18-13 | BJN | WFMI | TMBA | SEE SHEET 1 FOR REVISION HISTORY | 02802-31 |
|-----|----------|-----|------|------|----------------------------------|----------|
| REV | DATE     | BY  | CHK  | APR  | DESCRIPTION                      | ECN      |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Panduit:

[QPPDCBBB03](#) [QPPDCWDW14](#) [QPPDCBDW10](#) [QPPDCBDB05](#) [QPPEDGAW2M](#) [QPPDCWDB10](#) [QPPEDGDB03](#)  
[QPPEDBAB07](#) [QPPSDBBB10](#) [QPPCCBBB10](#) [QPPSDBAB07](#) [QPPCCBBB07](#) [QPPSDBBB05](#) [QPPSDBBB07](#)  
[QPPEDBBB3M](#) [QPPSDBAB05](#) [QPPSDBAB10](#) [QPPSDBAB14](#) [QPPSDBBB14](#) [QPPSDBDB03](#) [QPPSDBDB05](#)  
[QPPSDBRS10](#) [QPPSDBRS14](#) [QPPSDBDB07](#) [QPPSDBDB10](#) [QPPSDBDB14](#) [QPPSDBRS03](#) [QPPSDBRS05](#)  
[QPPSDBRS07](#) [QPPSDBBB03](#)